

Description

STAINLESS STEEL TOP PLATE CASTOR, GREY RUBBER 100MM

Fixed

KF41BA100-325RX



Part Number

Swivel

KP41BA100-325RX




Swivel and brake

KP41BD100-325RX



	Fixed	Swivel	Swivel+brake
Wheel Diameter ØD	100 mm		
Overall Height H	128 mm ±1		
Size of plate A X B	105 x 85 mm±1		
Plate hole centres a x b	80 x 60 mm±0,3		
Plate hole	9 mm		
Offset F ±1	\	36 mm	36 mm
Width of Tread	32 mm±0,5		
Hardness of tread	shore A ± 88		
Load capacity	80 Kg		
Weight	0,57 kg	0,68 kg	0,77 kg
Temperature	- 10 / + 50 °C		



Castor Assembly :

Pressed stainless steel -AISI 304-. Swivel on two rows of balls.
Fastening by top plate.
Total lock. Metal pedal.

Wheel :

Wheel centre made of Grey Polypropylene.
Tread : Thermoplastic rubber, grey non marking.
Hub : Stainless Steel Roller bearing.

Features :

Low starting effort,
Bonded Rubber,
Corrosion resistant, easy to clean
Suited for Food industry, Hospital or Industrial Kitchen equipment.
Medium duty.