



Part Number : [1731120280](#)

Product Description : FCT High Power Contact, Male, Straight, Solder Cup, 0.20µm Gold Mating Plating, 5.00µm Tin Termination Plating, 20.0A, 16-12 AWG

Series Number : 173112

Status : Active

Product Category : D-Sub Contacts

Engineering Number : FMP006P105



Documents & Resources

Drawings

[1731120280_sd.pdf](#)

Specifications

[1731120008-PK-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Contacts
Series	173112
Description	FCT High Power Contact, Male, Straight, Solder Cup, 0.20µm Gold Mating Plating, 5.00µm Tin Termination Plating, 20.0A, 16-12 AWG
Contact Type	High Power
Magnetic	Yes
Product Name	FCT Products
Type	Mixed Layout
UPC	889056722933

Electrical

Current - Maximum per Contact	20.0A
-------------------------------	-------

Physical

Durability (mating cycles min)	200
Gender	Male
Material - Contact	Copper Alloy
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Tin over Nickel
Material - Retaining Clip	Copper Alloy
Net Weight	2.000/g
Orientation	Straight

Packaging Type	Bag
Plating min - Mating	0.200µm
Plating min - Termination	5.000µm
Temperature Range - Operating	-55° to +155°C
Termination Style	Solder Cup
Wire Size (AWG)	12, 14, 16

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	FCT Mixed Layout Connectors

Application Tooling

Global

Description	Part Number
FCT Removal Tool for Size 8 Contacts	<u>1731121747</u>