

Backpack Vacuum Cleaner XGT®

VC008G

40Vmax • 180 mbar • 2,0 L

XGT® Battery powered HEPA Backpack Vacuum Cleaner.

VC008G has Increased suction power and lower noise with Improved operation switch which allows to check battery remaining capacity and operation mode. Comfortable backpack harness for reduced heat built-up. With 4 different suction modes.



Technical specifications

Vacuum hose length	1,0 m
Vacuum hose diameter	32 mm
Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Air volume	2,4 m³/min
Max. sealed suction	180 mbar
Suction power	25 / 55 / 100 / 195 W
Continuous Use XGT® 40V Max / 4.0 Ah	93 / 50 / 26 / 11 min
Continuous use XGT® 40Vmax / 5.0 Ah	110 / 55 / 30 / 14 min
Dust Bag Capacity	1,5 - 2,0 L
Sound Pressure Level (L _{pA})	72 dB(A)
Product net weight	3,4 kg
Noise Uncertainty (K Factor)	2,5 dB(A)

User benefits

- Brushless maintenance-free and long-life motor
- Built-in LED light illuminates the work area
- HEPA Filter is used to capture very fine particles effectively
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Low noise level for pleasant work.

Link to product - www.makita.com



Related products

Other

User manual

Parts drawing