

Product datasheet

Specifications



Schneider Electric Easy UPS SRV 2000VA 230V

Local distributor code:
422503415

SRVS2KI

Overview

Presentation For small to medium businesses, Easy UPS 1 Ph On-Line provides essential power protection for unstable power conditions, ensuring consistent and reliable connectivity at the most critical moments.

Lead time Usually in Stock

Main

Main Input Voltage 230 V

Product or component type Uninterruptible power supply (UPS)

Other Input Voltage 220 V
240 V

Main Output Voltage 230 V

Other Output Voltage 220 V
240 V

Rated power in W 1600 W

rated power in VA 2000 VA

Input Connection Type IEC 60320 C14

output connection type 4 IEC 60320 C13

Cable length 1.50 m

Number of cables 1

Provided equipment 1 IEC 60320 C13 to Schuko power cable
1 IEC 60320 C13 to C14 power cable
1 USB cable
1 RS-232 configuration cable
1 user manual

Range of product Easy UPS 1Ph On-Line

Batteries & Runtime

Run Time [View Runtime Graph](#)

Efficiency [View Efficiency Graph](#)

Battery type Lead-acid battery

Battery voltage 48 V

Extended runtime 0

Number of battery filled slots 0

Number of battery free slots 0

Battery recharge time 4 h

Battery life	3...5 year(s)
Replacement battery	APCRBCV204 
Battery charger power	76 W rated

General

Max runtime	4 min
Number of power module filled slots	0
Number of power module free slots	0
Redundant	No

Physical

Colour	Black (RAL 7010)
Height	23.8 cm
Width	14.5 cm
Depth	40 cm
Net weight	16.8 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable
USB compatible	Yes
Mounting position	Vertical

Input

Input voltage limits	110...285 V half load 160...280 V full load
Network frequency	40...70 Hz auto sensing

Output

Maximum configurable power in VA	2000 VA
Maximum configurable power in W	1600 W
Output frequency	50/60 Hz +/- 3 Hz sync to mains
UPS type	Double conversion online
Wave type	Sine wave
Efficiency	88 % (full load)
Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Bypass type	Internal bypass (automatic and manual)
Crest factor	3 : 1

Conformance

Product certifications	CE UKCA
------------------------	------------

Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
------------------	--

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...3000 m
Ambient air temperature for storage	-20...50 °C
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0...15000 m
Acoustic level	50 dBA
Heat dissipation	745 Btu/h
IP degree of protection	IP20

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Free slots	1
control panel	Multifunction LCD status and control console

Surge Protection and Filtering

Surge energy rate	600 J
--------------------------	-------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24.900 cm
Package 1 Width	32.900 cm
Package 1 Length	36.500 cm
Package 1 Weight	10.600 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	16
Package 2 Height	130.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	169.600 kg

Logistical informations

Country of origin	CN
--------------------------	----

Contractual warranty

Warranty	2 years repair or replace
-----------------	---------------------------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

[Environmental Disclosure](#)

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

[EU RoHS Directive](#)

Compliant

SCIP Number

8c493f2b-82c6-495f-a54a-f7d594e2b537

REACH Regulation

[REACH Declaration](#)

Use Again

Repack and remanufacture

Circularity Profile

[End of Life Information](#)

Take-back

No

WEEE

 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative

