



M710

LABEL PRINTER

The fastest, most advanced portable yet

Get more done in less time



About BRADY



Once you have worked with BRADY, our name will stick with you, (just like our labels) because BRADY is one of the world's leading labelling and identification specialists.

Innovative

At BRADY we continue to improve. We have many customers from all industries, and we strive to be ahead of their needs by continuing to invest in research for even more performant solutions. By developing more user-friendly and efficient concepts, we give our thousands of customers the best in the market.

Strength

At BRADY, we believe our biggest strength is the wide range of identification and safety solutions we can offer our customers, whether it's labelling the smallest component or complete signage for an entire warehouse. We're also proud to offer many products and services - from printers, scanners and software to service contracts and on-site training - that compliment any identification job. And don't forget, our wide network of expert distributors can always offer you a tailor-made solution to meet your specific requirements.

Trust

For over a hundred years, BRADY has been connected with quality, trust and stability. We demand the best for your products and services, because we know, better than anyone, the importance of good and reliable identification. Identification looks like a small detail, but every professional knows that this kind of detail is crucial to any business.

Inform

We also have specialised dealers in your region, who can answer all your identification, safety and labelling questions, specific to your activity. They will be happy to provide you with all kinds of options and solutions with no obligation.

Microsoft is a trademark of Microsoft Corporation, Bluetooth is a trademark of Bluetooth Sig, Inc., Android is a trademark of Google Inc.



Brady products are sold on the condition that the purchaser will test them in actual use and determine for himself/herself their suitability to his/her intended purpose. Brady warrants to the purchaser that Brady products are free from defects in material and workmanship but limits its obligation under this warranty to the replacement of the product which has been shown to Brady's satisfaction to have been defective at the time of its purchase.

The warranty does not extend to any persons who have acquired the product from the purchaser. It is in lieu of any other warranty, including every warranty of sale-ability, marketability or suitability for the intended purpose, and is also in lieu of any other obligation or liability on the part of Brady.

Under no circumstances will Brady be liable for losses, damage, costs or subsequent damage of whatever nature which may arise in connection with the use of, or inability to use, Brady's products.

M710 Label Printer

The Brady Advantage

When it comes to identification, safety and compliance, there's a clear advantage to working with Brady. We put our customers first in everything we do.

Our goal is to give you an unrivalled customer experience. We are relentlessly committed to performance and excellence - in our products, services and people.

Our products and solutions perform in ways that others simply can't match. Our people perform in ways that regularly exceed your expectations. And our focus and discipline work toward solid, long-term performance for our customers.

In short, Brady is the company you trust when performance matters most.

Learn more about the Brady Advantage at:
www.bradyeurope.com

Contents

- 4 MORE SPEED. LESS MESS
- 5 M710 at a glance
- 6 Get the job done right on any jobsite
- 7 Applications
- 10 Advantages of labelling
- 11 RFID labels
- 12 M710 media offering
- 13 Ribbons
- 14 Electrical, voice/datacom identification
- 30 General & industrial identification
- 34 Safety & facility identification
- 38 Electronics identification
- 40 Laboratory identification
- 49 Master material index
- 52 Brady Workstation
- 53 Printer specifications
- 54 M710 Printer and accessories
- 55 Brady Technical Excellent Centre





MORE SPEED. LESS MESS. Print on just anything.

Take on more jobs, and get them done in record time with the all-new M710 Label Printer. Fast and flexible, it's your tool for seamless label creation from the shop to the field. Design and print with a mobile app, software or keyboard and colour touchscreen. Enjoy printing on the toughest materials around, plus extra durability from a Li-ION battery that lasts all day long. Better jobsite performance starts with the M710.



GET MORE DONE WITH:



LIGHTNING-FAST PRINT SPEEDS



SHOP-TO-FIELD FLEXIBILITY



**MORE THAN 60 MATERIAL
OPTIONS**



Watch the How-to-videos
on our Brady YouTube
channel.



Click or scan here

M710 at a glance

Seamless experience for larger applications

Print 76 mm per second. Cut labels automatically. Print 4,500 labels on a single charge.

Get the job done right on any jobsite with the M710. With built-in speed, plus added durability to withstand longer days and tougher work conditions, it's our most advanced printer yet. Connect to your work more ways with software or a mobile app designed for 100s of industrial applications. Then design and print using the keypad, your phone or a PC. When you're ready to take on more, make sure it's with the M710.

**2 YEAR
WARRANTY**



A Prints up to 76 mm per second



B Easy material loading with bulk-size roll option



C USB port to import and save files, lists and graphics



D Rechargeable Li-ion battery prints up to 4,500 labels on a single charge

Get the job done right on any jobsite

Optimise your performance with Brady materials

The M710 works hard behind the scenes so you can maintain high performance and work seamlessly. Driven by smart technology, it communicates with label materials and software for smoother label setup and printing. It recognizes and adjusts to material size, type, colour, quantity and compatibility, plus sets up proper burn settings and print speed. All this is automatic, saving you trial-and-error adjustments.



SMART ROLLS

- ▶ Get the job done with over 50 high-performance materials and 1300+ label options.

BULK ROLLS

- ▶ Save more - buy in bulk: more than 14 materials and 200+ label options.

CUSTOM OPTIONS

- ▶ Have specific needs? Enjoy unlimited custom label options in 70+ different materials.



Enjoy a more premium labelling experience with optimised Brady Authentic materials

Authentic materials work seamlessly with Brady printers to produce enhanced performance and reliability you just don't get with materials from the others. We've got you covered with the widest range of colours, finishes and targeted applications in the industry. Get authentic. Get better with Brady.

Your time and cost-saving benefits include:



DECREASED SETUP TIME



FEWER LABEL ERRORS



COMPLIANT LABEL CREATION



REDUCED MATERIAL WASTE



Watch the How-to-videos on our Brady YouTube channel.



Click or scan here

Applications

Electrical, voice/datacom identification

Wire & Cable Marking for twisted pair data cables (UTP, FTP...), fibre optic cables, conductors, computer wires, electrical installation wires & cables, power & ground cables, energy cables...



Circuit breaker marking



Sleeves



Self-lams



Wrap-around labels



Flags



Tags

Component Marking for patch panels, control panels, punch blocks, terminal blocks, breaker boxes, face-plates...



Raised panels



Terminal block labels



Punch block & patch panel labels

General & industrial identification

Asset & Component Marking to be used on all kind of surfaces (smooth, rough, textured, low energy...).



Rating & name plate labels



Security identification labels



Rating plate labels

Applications

Safety & facility identification



Colour coded marking



Food processing equipment marking



Safety signs



Maintenance labels



Area & pathway marking



Safety labels



Lean warehouse labels



Cold temperature labels



Magnetic labels

Electronics identification

Circuit Board Marking for printed circuit board identification (also static dissipative), PCB SMT – Top/Bottom...



Polyester labels



Polyimide labels



Electrostatic Dissipative

Applications

Laboratory identification

Specimen tracking identification for sample tracking within histology labs: use barcode technology to prevent misdiagnosis.



Straws & rods



Vial top labels



Vial & tube labels



Conical & large tube labels

Specimen process marking supporting microscopic analysis of cells and tissues within pathology and clinical labs.



Centrifuge/microcentrifuge labels



Slide labels

Specimen storage identification supporting specimen collection and handling such as blood samples, cryo-samples etc.



Cryo labels



Tissue cassette labels



Well plate labels

Lean lab identification for general supplies marking.



Bottle tamper seals



Bottles, flasks & dishes



General lab equipment labels

Advantages of labelling

Ever lost time figuring out where each wire goes?

Durable professional labels that remain legible and stay attached in harsh conditions are extremely important to keep power, network, voice and data cables and components organised and running effectively.


Professional identification on wires, cables and components enables you to:

- immediately recognise what needs checking during troubleshooting
- clearly mark parts for upcoming maintenance upgrades
- trace history, lifespan and supplier
- add safety warnings or precautions

Ask yourself how much time or money you lose while trying to trace an unidentified faulty cable, wire or component.

Ask yourself how fast pressure builds when machinery, production lines, servers and services are impacted.

This is when professional labelling pays off big time.



Enable high-speed asset tracking with RFID labels



Print RFID labels on the spot with the M710 for fast, accurate asset identification.

- Create labels anywhere, anytime
- Print durable RFID labels instantly
- Improve asset tracking on the go

In addition to the labels compatible with the M710, we offer a wide range of RFID labels, tailored to your needs, plus readers, software, and full solution support.



FAST PRINTING



RESILIENT LABELS



EASY TO PROGRAM



**Discover our full RFID offering
at bradyeurope.com/rfid**



Click or scan here



Find M710 RFID labels on page 30-31

M710 media offering

We continuously try to improve & extend our label material offering, therefore make sure to check for firmware upgrades regularly, in order to make sure you always have access to the newest materials.

Material	
B-109	Polyethylene
B-342	Heat-shrink Polyolefin
B-348	Polyolefin
B-351	Tamper-resistant Vinyl
B-362	Tamper-resistant Metallised Vinyl
B-412	Polypropylene
B-414	Polyester
B-417	Self-laminating Vinyl
B-422	Polyester
B-423	Polyester
B-424	Paper
B-425A	Polypropylene
B-427	Self-laminating Vinyl
B-428	Metallised Polyester
B-430	Polyester
B-435	Metallised Polyester
B-437	Polyvinylfluoride
B-459	Polyester
B-461	Self-laminating Polyester
B-472	Polyimide
B-473	Static Dissipative Polyester
B-481	StainerBondz™ Polyester
B-483A	Polyester
B-483A/B-634	Polyester with Polyester Overlaminate
B-486B	Metallised Polyester
B-488	Polyester
B-489A	Polyester
B-490	FreezerBondz™ Polyester

Material	
B-492	FreezerBondz™ Polyester
B-498	Vinyl Cloth
B-499	Nylon Cloth
B-509	Magnetic Polyester
B-526	Phosphorescent Polyester
B-529	Polypropylene
B-530	Tamper-resistant Vinyl
B-549	Polyester
B-569	Polyester
B-581	Vinyl
B-582	Phosphorescent Polyester
B-584	Reflective Tape
B-595	Vinyl
B-642	Polyvinylfluoride
B-719	Polyimide
B-724	Polyimide
B-7593	Polyethylene Foam Laminate Polyester
B-7598	Polyester
B-7599	Polyethylene
B-7641	Heat-shrink Polyolefin
B-7643	Thermoplastic Polyether Polyurethane
B-767	Static Dissipative Polyimide
B-768	Static Dissipative Polyimide
B-7696	Vinyl
B-7697	Polyester
B-797	Polyimide
B-854	Metal Detectable Polyester
B-855	Polyester

Compatible consumables



Most of the M610 consumables are compatible with the M710 Label Printer by using the black media guide provided with the M710. Extra media guides are available as an accessory (order ref.: M71-ADAPT-BK)



Bulk packaging for high volume printing



Bulk labels are designed as a cost-effective solution for high volume labelling needs. Order references beginning with 'B' indicate bulk rolls. Bulk Label printing requires the media feeder and smart cell spool which are included in the bulk label material packaging.

▶ Get your custom M710 labels according to your specifications!

Frequently used custom labels include:

- Specific shapes and/or dimensions
- Specific colouring: material appearance through label colouring
- Specific materials to meet your requirements: chemical resistance, UV resistance, scratch resistance
- Specific printing or layout




Click or scan here



Ribbons

All materials in the printer work with a series of M7 ribbons that easily fit into the printer. M710 Series snap-in print ribbons enable 5-second ribbon supply changes. No calibrating, no threading, no waste, no hassles and the ink always faces the right direction! It is recommended to insert the ribbon before loading the consumable.

▶ Watch the how-to videos on our Brady YouTube channel.



Order Reference	Colour	Roll Width (mm)	Roll Length (m)	Formulation	Notes / Details
M7-R10000	Black	50.00	45.72	Resin	M7-R10000 Series: high performing, scratch and solvent resistant black ribbon
M7-R10000-BL	Blue	50.00	45.72	Resin	M7-R10000 Series: high performing, scratch and solvent resistant blue ribbon
M7-R10000-GN	Green	50.00	45.72	Resin	M7-R10000 Series: high performing, scratch and solvent resistant green ribbon
M7-R10000-RD	Red	50.00	45.72	Resin	M7-R10000 Series: high performing, scratch and solvent resistant red ribbon
M7-R10000-WT	White	50.00	45.72	Resin	M7-R10000 Series: high performing, scratch and solvent resistant white ribbon
M7-R10000-YL	Yellow	50.00	45.72	Resin	M7-R10000 Series: high performing, scratch and solvent resistant yellow ribbon
M7-R4400-WT	White	50.00	45.72	Resin	M7 R4400 Series: high heat, scratch and solvent resistant white ribbon
M7-R6000	Black	50.00	45.72	Resin	M7 R6000 Series: high heat, scratch and solvent resistant black ribbon
M7-R6200	Black	50.00	45.72	Resin	M7 R6200 Series: chemical, heat, scratch and smear resistant black ribbon
M7-R6300	Black	50.80	45.72	Resin	M7 R6300 Series : friction and solvent resistant Black Ribbon
M7-R6400	Black	50.00	45.72	Resin	M7 R6400 Series: abrasion and chemical resistant black ribbon
M7-R6600	Black	50.00	45.72	Resin	M7 R6600 Series: friction and solvent resistant black ribbon
M7-R6800-WT	White	50.00	36.58	Resin	M7 R6800 Series: scratch, smudge and solvent resistant white ribbon
M7-R6900-BL	Blue	50.00	45.72	Resin	M7 R6900 Series: fade, scratch and solvent resistant blue ribbon
M7-R6900-GN	Green	50.00	45.72	Resin	M7 R6900 Series: fade, scratch and solvent resistant green ribbon
M7-R6900-MA	Magenta	50.00	45.72	Resin	M7 R6900 Series: fade, scratch and solvent resistant magenta ribbon
M7-R6900-RD	Red	50.00	45.72	Resin	M7 R6900 Series: fade, scratch and solvent resistant red ribbon
M7-R6900-YL	Yellow	50.00	45.72	Resin	M7 R6900 Series: fade, scratch and solvent resistant yellow ribbon
M7-R4300	Black	50.00	45.72	Wax/Resin	M7 R4300 Series: chemical, environmental and smear resistant black ribbon
M7-R6700-WT	White	50.00	45.72	Wax/Resin	M7 R6700 Series: chemical resistant white ribbon

▶ Smart-Cell Technology

Brady Authentic labels have smart cell technology built into them, so labels are formatted automatically, without any guesswork on your part. They have bi-directional communication, which establishes the correct printer and software settings for optimal label performance and creation.



Wire & cable marking



PermaSleeve heat-shrink sleeve markers

- These heat-shrink sleeves are the ultimate in marker identification, protection, durability and aesthetic appearance.
- Fast shrink rate saves time and costs during installation.




Diagram	Order Reference	Shrink Ratio	Colour	Sleeve Width A (mm)	Sleeve Height B (mm)	Sleeve Length B (m)	Min. Wire Diameter (mm)	Max. Wire Diameter (mm)	Sleeves per roll	Printer Ribbon Series
B-342: Heat-shrink Polyolefin										
V	BM-094-1-342-2	3:1	White	12.70	4.62	-	0.58	2.03	5000	R4300, R6600
V	BM-094-175-342-2	3:1	White	22.23	4.62	-	0.58	2.03	5000	R4300, R6600
V	BM-094-1-342	3:1	White	25.40	4.62	-	0.58	2.03	2500	R4300, R6600
V	M7-094-1-342	3:1	White	25.40	4.62	-	0.58	2.03	100	R4300, R6600
V	BM-094-1-342-YL	3:1	Yellow	25.40	4.62	-	0.58	2.03	2500	R4300, R6600, R6700
V	M7-094-1-342-YL	3:1	Yellow	25.40	4.62	-	0.58	2.03	100	R4300, R6600, R6700
V	BM-094-175-342	3:1	White	44.45	4.62	-	0.58	2.03	2500	R4300, R6600
V	M7-094-175-342	3:1	White	44.45	4.62	-	0.58	2.03	100	R4300, R6600
V	BM-094-175-342-YL	3:1	Yellow	44.45	4.62	-	0.58	2.03	2500	R4300, R6600, R6700
V	M7-094-175-342-YL	3:1	Yellow	44.45	4.62	-	0.58	2.03	100	R4300, R6600, R6700
♥	BM7C-125-342	3:1	White	-	5.97	15.24	1.17	2.79	1	R4300, R6600
V	BM-125-1-342-2	3:1	White	12.70	5.97	-	1.17	2.79	2000	R4300, R6600
V	BM-125-175-342-3	3:1	White	14.81	5.97	-	1.17	2.79	3000	R4300, R6600
V	BM-125-175-342-2	3:1	White	22.23	5.97	-	1.17	2.79	2000	R4300, R6600
V	BM-125-1-342	3:1	White	25.40	5.97	-	1.17	2.79	1000	R4300, R6600
V	M7-125-1-342	3:1	White	25.40	5.97	-	1.17	2.79	100	R4300, R6600
V	BM-125-1-342-YL	3:1	Yellow	25.40	5.97	-	1.17	2.79	1000	R4300, R6600, R6700
V	M7-125-1-342-YL	3:1	Yellow	25.40	5.97	-	1.17	2.79	100	R4300, R6600, R6700
V	BM-125-175-342	3:1	White	44.45	5.97	-	1.17	2.79	1000	R4300, R6600
V	M7-125-175-342	3:1	White	44.45	5.97	-	1.17	2.79	100	R4300, R6600
V	BM-125-175-342-YL	3:1	Yellow	44.45	5.97	-	1.17	2.79	1000	R4300, R6600, R6700
V	M7-125-175-342-YL	3:1	Yellow	44.45	5.97	-	1.17	2.79	100	R4300, R6600, R6700
♥	BM7C-187-342	3:1	White	-	8.51	15.24	1.57	3.81	1	R4300, R6600
V	BM-187-175-342-4	3:1	White	11.10	8.51	-	1.57	3.81	4000	R4300, R6600
V	BM-187-175-342-3	3:1	White	14.81	8.51	-	1.57	3.81	3000	R4300, R6600
V	BM-187-175-342-2	3:1	White	22.23	8.51	-	1.57	3.81	2000	R4300, R6600
V	BM-187-1-342	3:1	White	25.40	8.51	-	1.57	3.81	1000	R4300, R6600
V	M7-187-1-342	3:1	White	25.40	8.51	-	1.57	3.81	100	R4300, R6600
V	BM-187-1-342-YL	3:1	Yellow	25.40	8.51	-	1.57	3.81	1000	R4300, R6600, R6700
V	M7-187-1-342-YL	3:1	Yellow	25.40	8.51	-	1.57	3.81	100	R4300, R6600, R6700
V	BM-187-175-342-OR	3:1	Orange	44.45	8.51	-	1.57	3.81	1000	R4300, R6600, R6700
V	BM-187-175-342-RD	3:1	Red	44.45	8.51	-	1.57	3.81	1000	R4300, R6600, R6700
V	BM-187-175-342	3:1	White	44.45	8.51	-	1.57	3.81	1000	R4300, R6600
V	M7-187-175-342	3:1	White	44.45	8.51	-	1.57	3.81	100	R4300, R6600

Order references beginning with "B" indicate bulk rolls.

>>

Wire & cable marking

PermaSleeve heat-shrink sleeve markers (continued)





Diagram	Order Reference	Shrink Ratio	Colour	Sleeve Width A (mm)	Sleeve Height B (mm)	Sleeve Length B (m)	Min. Wire Diameter (mm)	Max. Wire Diameter (mm)	Sleeves per roll	Printer Ribbon Series
B-342: Heat-shrink Polyolefin										
V	BM-187-175-342-YL	3:1	Yellow	44.45	8.51	-	1.57	3.81	1000	R4300, R6600, R6700
V	M7-187-175-342-YL	3:1	Yellow	44.45	8.51	-	1.57	3.81	100	R4300, R6600, R6700
♥	BM7C-250-342	3:1	White	-	11.15	15.24	2.39	5.46	1	R4300, R6600
V	BM-250-1-342	3:1	White	25.40	11.15	-	2.39	5.46	1000	R4300, R6600
V	M7-250-1-342	3:1	White	25.40	11.15	-	2.39	5.46	100	R4300, R6600
V	BM-250-1-342-YL	3:1	Yellow	25.40	11.15	-	2.39	5.46	1000	R4300, R6600, R6700
V	M7-250-1-342-YL	3:1	Yellow	25.40	11.15	-	2.39	5.46	100	R4300, R6600, R6700
V	BM-250-175-342	3:1	White	44.45	11.15	-	2.39	5.46	1000	R4300, R6600
V	M7-250-175-342	3:1	White	44.45	11.15	-	2.39	5.46	100	R4300, R6600
V	BM-250-175-342-YL	3:1	Yellow	44.45	11.15	-	2.39	5.46	1000	R4300, R6600, R6700
V	M7-250-175-342-YL	3:1	Yellow	44.45	11.15	-	2.39	5.46	100	R4300, R6600, R6700
♥	BM7C-375-342	3:1	White	-	16.38	15.24	3.18	8.13	1	R4300, R6600
V	BM-375-1-342-2	3:1	White	12.70	16.38	-	3.18	8.13	2000	R4300, R6600
V	BM-375-175-342-2	3:1	White	22.23	16.38	-	3.18	8.13	2000	R4300, R6600
V	BM-375-1-342	3:1	White	25.40	16.38	-	3.18	8.13	1000	R4300, R6600
V	M7-375-1-342	3:1	White	25.40	16.38	-	3.18	8.13	100	R4300, R6600
V	BM-375-1-342-YL	3:1	Yellow	25.40	16.38	-	3.18	8.13	1000	R4300, R6600, R6700
V	M7-375-1-342-YL	3:1	Yellow	25.40	16.38	-	3.18	8.13	100	R4300, R6600, R6700
V	BM-375-175-342	3:1	White	44.45	16.38	-	3.18	8.13	1000	R4300, R6600
V	M7-375-175-342	3:1	White	44.45	16.38	-	3.18	8.13	100	R4300, R6600
V	BM-375-175-342-YL	3:1	Yellow	44.45	16.38	-	3.18	8.13	1000	R4300, R6600, R6700
V	M7-375-175-342-YL	3:1	Yellow	44.45	16.38	-	3.18	8.13	100	R4300, R6600, R6700
♥	BM7C-500-342	3:1	White	-	21.62	15.24	4.75	11.43	1	R4300, R6600
V	BM-500-175-342-YL-3	3:1	Yellow	14.81	21.62	-	4.75	11.43	3000	R4300, R6600, R6700
V	BM-500-1-342	3:1	White	25.40	21.62	-	4.75	11.43	1000	R4300, R6600
V	M7-500-1-342	3:1	White	25.40	21.62	-	4.75	11.43	100	R4300, R6600
V	BM-500-1-342-YL	3:1	Yellow	25.40	21.62	-	4.75	11.43	1000	R4300, R6600, R6700
V	M7-500-1-342-YL	3:1	Yellow	25.40	21.62	-	4.75	11.43	100	R4300, R6600, R6700
V	BM-500-175-342	3:1	White	44.45	21.62	-	4.75	11.43	1000	R4300, R6600
V	BM-500-175-342-YL	3:1	Yellow	44.45	21.62	-	4.75	11.43	1000	R4300, R6600, R6700
V	M7-500-175-342-YL	3:1	Yellow	44.45	21.62	-	4.75	11.43	100	R4300, R6600, R6700
♥	BM7C-1000-342	3:1	White	-	42.16	15.24	8.46	24.13	1	R4300, R6600
V	M7-1000-1-342	3:1	White	25.40	42.16	-	8.46	24.13	50	R4300, R6600
V	M7-1000-1-342-YL	3:1	Yellow	25.40	42.16	-	8.46	24.13	50	R4300, R6600, R6700
V	BM-1000-175-342	3:1	White	44.45	42.16	-	8.46	24.13	500	R4300, R6600
V	M7-1000-175-342	3:1	White	44.45	42.16	-	8.46	24.13	50	R4300, R6600
V	M7-1000-175-342-YL	3:1	Yellow	44.45	42.16	-	8.46	24.13	50	R4300, R6600, R6700

Order references beginning with "B" indicate bulk rolls.


▶ See pages 49 - 51 for a detailed material index.

Wire & cable marking



PermaSleeve low smoke zero halogen wire marking sleeves, 2:1 shrink ratio

- These heat-shrink sleeves are the ultimate in marker identification, protection, durability and aesthetic appearance.
- These low smoke zero halogen wire marking sleeves offer outstanding fire safety properties and minimal smoke emission.
- Fast shrink rate saves time and costs during installation. Available as individual die-cut markers or continuous cut-to-length tubing.



Sleeves are shown in order of sleeve height and per sleeve width.


Diagram	Order Reference	Shrink Ratio	Colour	Sleeve Width A (mm)	Sleeve Height B (mm)	Min. Wire Diameter (mm)	Max. Wire Diameter (mm)	Sleeves per roll	Printer Ribbon Series
B-7641: Heat-shrink Polyolefin									
V	BM-094-1-7641	2:1	White	25.40	4.62	1.19	2.03	2500	R6000HF, R6600
V	M7-094-1-7641	2:1	White	25.40	4.62	1.19	2.03	100	R6000HF, R6600
V	M7-094-1-7641-YL	2:1	Yellow	25.40	4.62	1.19	2.03	100	R4300, R6000HF, R6600
V	M7-094-175-7641	2:1	White	44.45	4.62	1.19	2.03	100	R6000HF, R6600
V	M7-094-175-7641-YL	2:1	Yellow	44.45	4.62	1.19	2.03	100	R4300, R6000HF, R6600
V	BM-125-1-7641	2:1	White	25.40	5.97	1.57	2.79	1000	R6000HF, R6600
V	M7-125-1-7641	2:1	White	25.40	5.97	1.57	2.79	100	R6000HF, R6600
V	M7-125-1-7641-YL	2:1	Yellow	25.40	5.97	1.57	2.79	100	R4300, R6000HF, R6600
V	BM-125-175-7641	2:1	White	44.45	5.97	1.57	2.79	1000	R6000HF, R6600
V	M7-125-175-7641	2:1	White	44.45	5.97	1.57	2.79	100	R6000HF, R6600
V	M7-125-175-7641-YL	2:1	Yellow	44.45	5.97	1.57	2.79	100	R4300, R6000HF, R6600
V	BM-187-1-7641	2:1	White	25.40	8.51	2.39	3.81	1000	R6000HF, R6600
V	M7-187-1-7641	2:1	White	25.40	8.51	2.39	3.81	100	R6000HF, R6600
V	M7-187-1-7641-YL	2:1	Yellow	25.40	8.51	2.39	3.81	100	R4300, R6000HF, R6600
V	BM-187-175-7641	2:1	White	44.45	8.51	2.39	3.81	1000	R6000HF, R6600
V	M7-187-175-7641	2:1	White	44.45	8.51	2.39	3.81	100	R6000HF, R6600
V	M7-187-175-7641-YL	2:1	Yellow	44.45	8.51	2.39	3.81	100	R4300, R6000HF, R6600
V	BM-250-1-7641	2:1	White	25.40	11.15	3.18	5.46	1000	R6000HF, R6600
V	M7-250-1-7641	2:1	White	25.40	11.15	3.18	5.46	100	R6000HF, R6600

Order references beginning with "B" indicate bulk rolls.

>>

Wire & cable marking

PermaSleeve low smoke zero halogen wire marking sleeves, 2:1 shrink ratio (continued)



Sleeves are shown in order of sleeve height and per sleeve width.



Diagram	Order Reference	Shrink Ratio	Colour	Sleeve Width A (mm)	Sleeve Height B (mm)	Min. Wire Diameter (mm)	Max. Wire Diameter (mm)	Sleeves per roll	Printer Ribbon Series
B-7641: Heat-shrink Polyolefin									
V	M7-250-1-7641-YL	2:1	Yellow	25.40	11.15	3.18	5.46	100	R4300, R6000HF, R6600
V	M7-250-175-7641	2:1	White	44.45	11.15	3.18	5.46	100	R6000HF, R6600
V	M7-250-175-7641-YL	2:1	Yellow	44.45	11.15	3.18	5.46	100	R4300, R6000HF, R6600
V	BM-375-1-7641	2:1	White	25.40	16.38	4.78	8.13	1000	R6000HF, R6600
V	M7-375-1-7641	2:1	White	25.40	16.38	4.78	8.13	100	R6000HF, R6600
V	M7-375-1-7641-YL	2:1	Yellow	25.40	16.38	4.78	8.13	100	R4300, R6000HF, R6600
V	BM-375-175-7641	2:1	White	44.45	16.38	4.78	8.13	1000	R6000HF, R6600
V	M7-375-175-7641	2:1	White	44.45	16.38	4.78	8.13	100	R6000HF, R6600
V	M7-375-175-7641-YL	2:1	Yellow	44.45	16.38	4.78	8.13	100	R4300, R6000HF, R6600
V	M7-500-1-7641	2:1	White	25.40	21.62	6.35	11.43	100	R6000HF, R6600
V	M7-500-1-7641-YL	2:1	Yellow	25.40	21.62	6.35	11.43	100	R4300, R6000HF, R6600
V	M7-500-175-7641	2:1	White	44.45	21.62	6.35	11.43	100	R6000HF, R6600
V	M7-500-175-7641-YL	2:1	Yellow	44.45	21.62	6.35	11.43	100	R4300, R6000HF, R6600
V	M7-750-1-7641	2:1	White	25.40	31.75	9.53	17.78	75	R6000HF, R6600
V	M7-750-1-7641-YL	2:1	Yellow	25.40	31.75	9.53	17.78	75	R4300, R6000HF, R6600
V	M7-750-175-7641	2:1	White	44.45	31.75	9.53	17.78	75	R6000HF, R6600
V	M7-750-175-7641-YL	2:1	Yellow	44.45	31.75	9.53	17.78	75	R4300, R6000HF, R6600

Order references beginning with "B" indicate bulk rolls.

▶ See pages 49 - 51 for a detailed material index.

Wire & cable marking



Self-laminating labels

- Features a clear, non-printable area that wraps around the cable and serves as an overlaminate to the printed text.
- Offers superior resistance to abrasion, dirt, oils, solvents and water.




Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Printable Area Width PW (mm)	Printable Area Height PH (mm)	Vertical Repeat D (mm)	Min. Wire Diameter (mm)	Max. Wire Diameter (mm)	Labels per Roll	Printer Ribbon Series
B-417: Self-laminating Vinyl											
▶	M7-11-417	White	12.70	19.05	12.70	9.53	15.88	1.52	3.02	500	R4300, R6900
▶	M7-29-417	White	12.70	38.10	12.70	12.70	15.88	2.03	4.04	500	R4300, R6900
▶	M7-96-417	White	25.40	19.05	25.40	9.53	22.23	1.52	3.02	250	R4300, R6900
▶	M7-19-417	White	25.40	25.40	25.40	9.53	28.58	1.52	3.02	250	R4300, R6900
▶	M7-103-417	White	25.40	31.75	25.40	12.70	34.93	3.40	6.10	250	R4300, R6900
▶	M7-31-417	White	25.40	38.10	25.40	12.70	28.58	3.99	8.10	250	R4300, R6900
▶	M7-21-417	White	25.40	63.50	25.40	19.05	66.68	6.71	14.20	100	R4300, R6900
▶	M7-32-417	White	38.10	38.10	38.10	12.70	41.28	2.03	4.04	250	R4300, R6900
▶	M7-109-417	White	38.10	101.60	38.10	38.10	104.78	6.10	12.14	100	R4300, R6900
▶	M7-66-417	White	49.23	80.00	49.23	25.40	83.57	4.06	8.08	100	R4300, R6900
B-427: Self-laminating Vinyl											
▶	M7-10-427	White	6.35	19.05	6.35	9.53	9.53	2.01	3.00	750	R4300, R6900
▶	M7-28-427	White	6.35	38.10	6.35	12.70	9.53	3.99	8.10	750	R4300, R6900
▶	M7-11-427	White	12.70	19.05	12.70	9.53	15.88	2.01	3.00	500	R4300, R6900
▶	BM-11-427	White	12.70	19.05	12.70	9.53	15.88	2.01	3.00	5000	R4300
▶	M7-17-427	White	12.70	25.40	12.70	9.53	15.88	2.69	5.11	500	R4300, R6900
▶	BM-17-427	White	12.70	25.40	12.70	9.53	15.88	2.69	5.11	5000	R4300
▶	M7-29-427	White	12.70	38.10	12.70	12.70	15.88	3.99	8.10	500	R4300, R6900
▶	BM-29-427	White	12.70	38.10	12.70	12.70	15.88	3.99	8.10	5000	R4300
▶	M7-18-427	White	19.05	25.40	19.05	9.53	22.23	2.69	5.11	250	R4300, R6900
▶	BM-18-427	White	19.05	25.40	19.05	9.53	22.23	2.69	5.11	2500	R4300
▶	M7-30-427	White	19.05	38.10	19.05	12.70	22.23	3.99	8.10	250	R4300, R6900
▶	BM-30-427	White	19.05	38.10	19.05	12.70	22.23	3.99	8.10	2500	R4300
▶	M7-30-427-BL	Blue	19.05	38.10	19.05	12.70	22.23	3.99	8.10	250	R4300, R6700, R6900
▶	M7-30-427-PL	Purple	19.05	38.10	19.05	12.70	22.23	3.99	8.10	250	R4300, R6700, R6900
▶	M7-30-427-RD	Red	19.05	38.10	19.05	12.70	22.23	3.99	8.10	250	R4300, R6700, R6900
▶	M7-96-427	White	25.40	19.05	25.40	9.53	22.23	2.01	3.00	250	R4300, R6900
▶	M7-19-427	White	25.40	25.40	25.40	9.53	28.58	2.69	5.11	250	R4300, R6900
▶	BM-19-427	White	25.40	25.40	25.40	9.53	28.58	2.69	5.11	2500	R4300

>>

Wire & cable marking

Self-laminating labels (continued)




Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Printable Area Width (mm)	Printable Area Height PH (mm)	Vertical Repeat D (mm)	Min. Wire Diameter (mm)	Max. Wire Diameter (mm)	Labels per Roll	Printer Ribbon Series
▶	M7-19-427-YL	Yellow	25.40	25.40	25.40	9.53	28.58	2.69	5.11	250	R4300, R6700, R6900
▶	M7-103-427	White	25.40	31.75	25.40	12.70	34.93	3.40	6.10	250	R4300, R6900
▶	M7-31-427-YL	Yellow	25.40	38.10	25.40	12.70	28.58	3.99	8.10	250	R4300, R6700, R6900
▶	M7-31-427	White	25.40	38.10	25.40	12.70	28.58	3.99	8.10	250	R4300, R6900
▶	BM-31-427	White	25.40	38.10	25.40	12.70	28.58	3.99	8.10	2500	R4300
▶	M7-31-427-GN	Green	25.40	38.10	25.40	12.70	28.58	3.99	8.10	250	R4300, R6700, R6900
▶	M7-31-427-RD	Red	25.40	38.10	25.40	12.70	28.58	3.99	8.10	250	R4300, R6700, R6900
▶	M7-21-427	White	25.40	63.50	25.40	19.05	66.68	6.71	14.20	100	R4300, R6900
▶	BM-21-427	White	25.40	63.50	25.40	19.05	66.68	6.71	14.20	1000	R4300
▶	M7-21-427-YL	Yellow	25.40	63.50	25.40	19.05	66.68	6.71	14.20	100	R4300, R6700, R6900
★	M7-64-427	White	25.40	85.73	25.40	28.58	88.90	9.09	18.21	100	R4300, R6900
★	BM-64-427	White	25.40	85.73	25.40	28.58	88.90	9.09	18.21	1000	R4300
▶	M7-23-427	White	25.40	101.60	25.40	25.40	104.78	10.80	24.31	100	R4300, R6900
▶	BM-23-427	White	25.40	101.60	25.40	25.40	104.78	10.80	24.31	1000	R4300
▲	M7-30-427-AW	White	38.10	19.05	-	-	22.23	3.99	8.00	250	R4300, R6900
▶	M7-104-427	White	38.10	25.40	38.10	9.53	28.58	2.69	5.11	250	R4300, R6900
▶	M7-32-427	White	38.10	38.10	38.10	12.70	41.28	3.99	8.10	250	R4300, R6900
▶	BM-32-427	White	38.10	38.10	38.10	12.70	41.28	3.99	8.10	1000	R4300
▶	M7-32-427-YL	Yellow	38.10	38.10	38.10	12.70	41.28	3.99	8.10	250	R4300, R6700, R6900
▶	M7-33-427-YL	Yellow	38.10	101.60	38.10	25.40	104.78	10.80	24.31	100	R4300, R6700, R6900
▶	M7-33-427	White	38.10	101.60	38.10	25.40	104.78	10.80	24.31	100	R4300, R6900
▶	BM-33-427	White	38.10	101.60	38.10	25.40	104.78	10.80	24.31	500	R4300
▶	BM-109-427	White	38.10	101.60	38.10	38.10	104.78	10.80	20.19	500	R4300
▶	M7-109-427	White	38.10	101.60	38.10	38.10	104.78	10.80	20.19	100	R4300, R6900
▶	M7-34-427	White	38.10	152.40	38.10	38.10	155.58	16.21	36.40	50	R4300, R6900
▶	BM-34-427	White	38.10	152.40	38.10	38.10	155.58	16.21	36.40	500	R4300
▶	M7-88-427	White	44.45	38.10	44.45	12.70	41.28	3.99	8.10	250	R4300, R6900
▶	M7-66-427	White	49.23	80.00	49.23	25.40	83.57	8.50	17.40	100	R4300, R6900
▶	BM-107-427	White	50.80	38.10	50.80	12.70	53.98	3.99	8.10	1000	R4300
▶	M7-107-427	White	50.80	38.10	50.80	12.70	53.98	3.99	8.10	100	R4300, R6900
B-642: Polyvinylfluoride											
▶	M7-19-642	White, Transparent	25.40	25.40	25.40	9.53	28.58	3.00	5.05	250	R4300, R6200
▶	M7-31-642	White, Transparent	25.40	38.10	25.40	12.70	28.58	3.99	8.10	250	R4300, R6200
▶	M7-21-642	White, Transparent	25.40	63.50	25.40	19.05	66.68	6.71	14.20	100	R4300, R6200

Order references beginning with "B" indicate bulk rolls. *Order references ending with "AW" indicate all white labels with no clear area.

Wire & cable marking



Wrap around labels

- These durable cloth wrap around labels are available with either an adhesive that allows the markers to be removed cleanly and reapplied if necessary (B-498) or with a permanent adhesive (B-437, B-499).
- A 3 mm overlap is recommended with these materials for an ideal, long lasting solution.




Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Label Length B (m)	Vertical Repeat D (mm)	Max. Wire Diameter (mm)	Labels per Roll	Printer Ribbon Series
B-472: Polyimide									
⊙	M7C-1000-472-YL	Yellow	25.40	-	15.24	-	-	1	R4300, R6200
⊙	M7C-1000-472	White	25.40	-	15.24	-	-	1	R4300, R6200
▲	M7-17-472	White	25.40	12.70	-	15.88	-	500	R4300, R6200
⊙	M7C-1500-472-YL	Yellow	38.10	-	15.24	-	-	1	R4300, R6200
⊙	M7C-1500-472	White	38.10	-	15.24	-	-	1	R4300, R6200
▲	M7-30-472	White	38.10	19.05	-	22.23	-	250	R4300, R6200
⊙	M7C-2000-472-YL	Yellow	50.80	-	15.24	-	-	1	R4300, R6200
⊙	M7C-2000-472	White	50.80	-	15.24	-	-	1	R4300, R6200
B-498: Vinyl Cloth									
∞	M7C-240-498	White	6.10	-	9.14	-	-	1	R4300, R6000HF, R6200, R6900
∞	BM7C-240-498	White	6.10	-	83.82	-	-	1	R4300, R6000HF, R6200, R6900
▲	M7-10-498	White	6.35	19.05	-	9.53	4.55	750	R4300, R6000HF, R6200, R6900
∞	M7C-318-498	White	8.08	-	9.14	-	-	1	R4300, R6000HF, R6200, R6900
∞	M7C-375-498	White	9.53	-	9.14	-	-	1	R4300, R6000HF, R6200, R6900
∞	BMC-375-498	White	9.53	-	83.82	-	-	1	R4300, R6200, R6600
∞	M7C-500-498	White	12.70	-	9.14	-	-	1	R4300, R6000HF, R6200, R6900
▲	M7-7-498	White	12.70	12.70	-	15.88	3.02	500	R4300, R6000HF, R6200, R6900
▲	M7-11-498	White	12.70	19.05	-	15.88	4.55	500	R4300, R6000HF, R6200, R6900
▲	BM-29-498	White	12.70	38.10	-	15.88	9.09	5000	R4300, R6200, R6600
▲	BM-11-498	White	19.05	12.70	-	15.88	4.55	5000	R4300, R6200, R6600
▲	M7-18-498	White	19.05	25.40	-	22.23	6.07	250	R4300, R6000HF, R6200, R6900
▲	BM-18-498	White	19.05	25.40	-	22.23	6.07	2500	R4300, R6200, R6600
⊙	M7C-1000-498	White	25.40	-	9.14	-	-	1	R4300, R6000HF, R6200, R6900
▲	M7-17-498	White	25.40	12.70	-	15.88	6.07	500	R4300, R6000HF, R6200, R6900
▲	M7-19-498	White	25.40	25.40	-	28.58	6.07	250	R4300, R6000HF, R6200, R6900
▲	BM-19-498	White	25.40	25.40	-	28.58	6.07	2500	R4300, R6200, R6600
▲	M7-21-498	White	25.40	63.50	-	66.68	15.60	100	R4300, R6000HF, R6200, R6900
▲	M7-16-498	White	25.40	9.53	-	12.70	6.07	500	R4300, R6000HF, R6200, R6900
▲	M7-33-498	White	38.10	101.60	-	104.78	24.26	100	R4300, R6000HF, R6200, R6900
▲	M7-29-498	White	38.10	12.70	-	15.88	9.09	500	R4300, R6000HF, R6200, R6900
▲	M7-30-498	White	38.10	19.05	-	22.23	9.09	250	R4300, R6000HF, R6200, R6900
▲	M7-31-498	White	38.10	25.40	-	28.58	9.09	250	R4300, R6000HF, R6200, R6900
▲	M7-32-498	White	38.10	38.10	-	41.28	9.09	250	R4300, R6000HF, R6200, R6900
⊙	M7C-1900-498	White	48.26	-	9.14	-	-	1	R4300, R6000HF, R6200, R6900

Order references beginning with "B" indicate bulk rolls.

>>

▶ See pages 49 - 51 for a detailed material index.

Wire & cable marking

Wrap around labels (continued)




Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Label Length B (m)	Vertical Repeat D (mm)	Max. Wire Diameter (mm)	Labels per Roll	Printer Ribbon Series
B-499: Nylon Cloth									
⊙	M7C-500-499	White	12.70	-	9.14	-	-	1	R4300, R6000HF, R6200, R6900
▲	M7-7-499	White	12.70	12.70	-	15.88	3.02	500	R4300, R6000HF, R6200, R6900
▲	M7-11-499	White	12.70	19.05	-	15.88	4.55	500	R4300, R6000HF, R6200, R6900
▲	M7-29-499	White	12.70	38.10	-	15.88	9.09	500	R4300, R6000HF, R6200, R6900
▲	M7-67-499-YL	Yellow	15.00	9.00	-	-	-	750	R4300, R6000HF, R6200, R6900
▲	M7-41-499-YL	Yellow	16.00	5.00	-	-	-	750	R4300, R6000HF, R6200, R6900
▲	BM-11-499	White	19.05	12.70	-	15.88	4.55	5000	R4300, R6200
▲	M7-18-499	White	19.05	25.40	-	22.23	6.07	250	R4300, R6000HF, R6200, R6900
▲	M7-84-499	White	22.86	12.70	-	15.88	6.07	500	R4300, R6000HF, R6200, R6900
⊙	M7C-1000-499	White	25.40	-	9.14	-	-	1	R4300, R6000HF, R6200, R6900
▲	M7-21-499	White	25.40	63.50	-	66.68	15.60	100	R4300, R6000HF, R6200, R6900
▲	M7-16-499	White	25.40	9.53	-	12.70	6.07	500	R4300, R6000HF, R6200, R6900
▲	M7-30-499	White	38.10	19.05	-	22.23	9.09	250	R4300, R6000HF, R6200, R6900
▲	M7-31-499	White	38.10	25.40	-	28.58	9.09	250	R4300, R6000HF, R6200, R6900
▲	M7-28-499	White	38.10	6.35	-	9.53	9.09	750	R4300, R6000HF, R6200, R6900
⊙	M7C-1900-499	White	48.26	-	9.14	-	-	1	R4300, R6000HF, R6200, R6900
▲	M7-78-499	White	48.26	25.40	-	28.58	10.01	250	R4300, R6000HF, R6200, R6900
▲	M7-81-499	White	48.26	6.35	-	9.53	10.01	750	R4300, R6000HF, R6200, R6900

Order references beginning with "B" indicate bulk rolls.



Fibre optic labels/flags

These fibre optic flags allow more legible information to be printed on smaller diameter wires and permit you to handle and view labels without touching the wires.




Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Printable Area Height PH (mm)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
B-425A: Polypropylene								
TL	M7-1-425-FT	White	29.97	20.02	9.91	43.56	250	R4300, R6200, R6900
L	M7-1-425-FP	White	29.97	20.02	-	23.50	250	R4300, R6200, R6900
F	M7-2-425-FP	White	44.45	25.40	-	66.68	100	R4300, R6200, R6900
B-483A: Polyester								
U	M7-214-483	White	25.40	50.80	-	53.98	250	R6000HF, R6300, R6900

Electrical, voice/datacom identification

Wire & cable marking



RAPIDO plastic wiremarkers

- Yellow coated polyethylene tag suitable for durable wire marking for electrical devices and fibre installations.




Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Max. Lines of Text	Max. Characters per Line	Vertical Repeat D (mm)	Min. Wire Diameter (mm)	Max. Wire Diameter (mm)	Labels per Roll	Printer Ribbon Series
B-7599: Polyethylene											
	BM-1-7599-YL-R	Yellow	23.00	5.20	1	11	8.38	-	-	2500	R6200
	BM-2-7599-YL-R	Yellow	23.00	5.20	1	8	8.38	-	-	2500	R6200
	BM-3-7599-YL-R	Yellow	25.00	5.70	2	7	8.89	-	-	2500	R6200
	BM-4-7599-YL-R	Yellow	26.00	7.00	2	7	12.01	-	-	2500	R6200
	BM-5-7599-YL-R	Yellow	41.00	11.00	3	17	14.20	-	-	2500	R6200

Order references beginning with "B" indicate bulk rolls.



Tear resistant cable markers

- These extremely tear resistant cable markers can be used for a variety of applications including identification of multiconductor cables, inventory and equipment.




Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Printable Area Width PW (mm)	Printable Area Height PH (mm)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
B-109: Polyethylene									
	BM-60-109	White	12.00	50.00	12.00	33.00	50.17	1000	R4300, R6200
	M7-12-109	White	19.05	76.20	12.45	52.07	76.20	100	R4300, R6200
	BM-12-109	White	19.05	76.20	12.45	52.07	76.20	1000	R4300, R6200
	M7-36-109	White	44.45	28.58	44.45	28.58	28.56	250	R4300, R6200

Order references beginning with "B" indicate bulk rolls.

Coloured Nylon Ties

- Perfect for colour coded applications.

Order Reference	Colour	Width (mm)	Length (mm)	Quantity
196283	Black	3.50	200.00	100
196311	White	3.50	200.00	100
196352	Yellow	3.50	200.00	100
196349	Blue	3.60	200.00	100
196350	Green	3.60	200.00	100
196351	Red	3.60	200.00	100




Wire & cable marking



B-7598 Polyester cable tag

The B-7598 polyester tag is a general identification tag for cables exposed to extreme conditions. It requires cable ties to apply to cables with various diameters. Common applications for this cable tag material are:




- Identification of multi-conductor cables
- Identification of cables in mobile phone towers
- Identification of datacom or telecom cables in general
- General cable identification that must be extremely resistant

Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
B-7598: Polyester							
◇	BM-10X60-7598-BK	Black	10.00	60.00	65.09	500	R4400
◇	BM-10X60-7598-BL	Blue	10.00	60.00	65.09	500	R4400, R6000HF
◇	BM-10X60-7598-GN	Green	10.00	60.00	65.09	500	R4400, R6000HF
◇	BM-10X60-7598-RD	Red	10.00	60.00	65.09	500	R4400, R6000HF
◇	BM-10X60-7598-SV	Silver	10.00	60.00	65.09	500	R4400, R6000HF
◇	BM-10X60-7598-WT	White	10.00	60.00	65.09	500	R4400, R6000HF
◇	BM-10X60-7598-YL	Yellow	10.00	60.00	65.09	500	R4400, R6000HF
◇	BM-10X75-7598-BK	Black	10.00	75.00	80.43	250	R4400
◇	BM-10X75-7598-BL	Blue	10.00	75.00	80.43	250	R4400, R6000HF
◇	BM-10X75-7598-GN	Green	10.00	75.00	80.43	250	R4400, R6000HF
◇	BM-10X75-7598-RD	Red	10.00	75.00	80.43	250	R4400, R6000HF
◇	BM-10X75-7598-SV	Silver	10.00	75.00	80.43	250	R4400, R6000HF
◇	BM-10X75-7598-WT	White	10.00	75.00	80.43	250	R4400, R6000HF
◇	BM-10X75-7598-YL	Yellow	10.00	75.00	80.43	250	R4400, R6000HF
◇	BM-15X75-7598-BK	Black	15.00	75.00	80.43	250	R4400
◇	BM-15X75-7598-BL	Blue	15.00	75.00	80.43	250	R4400, R6000HF
◇	BM-15X75-7598-GN	Green	15.00	75.00	80.43	250	R4400, R6000HF
◇	BM-15X75-7598-RD	Red	15.00	75.00	80.43	250	R4400, R6000HF
◇	BM-15X75-7598-SV	Silver	15.00	75.00	80.43	250	R4400, R6000HF
◇	BM-15X75-7598-WT	White	15.00	75.00	80.43	250	R4400, R6000HF
◇	BM-15X75-7598-YL	Yellow	15.00	75.00	80.43	250	R4400, R6000HF
◇	BM-25X75-7598-BK	Black	25.00	75.00	80.43	250	R4400
◇	BM-25X75-7598-BL	Blue	25.00	75.00	80.43	250	R4400, R6000HF
◇	BM-25X75-7598-GN	Green	25.00	75.00	80.43	250	R4400, R6000HF
◇	BM-25X75-7598-RD	Red	25.00	75.00	80.43	250	R4400, R6000HF
◇	BM-25X75-7598-SV	Silver	25.00	75.00	80.43	250	R4400, R6000HF
◇	BM-25X75-7598-WT	White	25.00	75.00	80.43	250	R4400, R6000HF
◇	BM-25X75-7598-YL	Yellow	25.00	75.00	80.43	250	R4400, R6000HF

Order references beginning with "B" indicate bulk rolls.

▶ See pages 49 - 51 for a detailed material index.

Wire & cable marking




B-7643 Halogen-free cable tag

- These cable markers are made of halogen-free polyurethane material.
- The markers are tough, imperishable and with a very high degree of mark permanence in almost any environment.

Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
B-7643: Thermoplastic Polyether Polyurethane							
◇	BM-10x60-7643-BK	Black	10.00	60.00	65.09	250	R4400
◇	BM-10x60-7643-BL	Blue	10.00	60.00	65.09	250	R4400, R6000HF
◇	BM-10x60-7643-GN	Green	10.00	60.00	65.09	250	R4400, R6000HF
◇	BM-10x60-7643-OR	Orange	10.00	60.00	65.09	250	R4400, R6000HF
◇	BM-10x60-7643-RD	Red	10.00	60.00	65.09	250	R4400, R6000HF
◇	BM-10x60-7643-WT	White	10.00	60.00	65.09	250	R6000HF
▽	BM-10x60-7643-WT-L	White	10.00	60.00	65.88	250	R6000HF
◇	BM-10x60-7643-YL	Yellow	10.00	60.00	65.09	250	R4400, R6000HF
▽	BM-10x60-7643-YL-L	Yellow	10.00	60.00	65.88	250	R4400, R6000HF
◇	BM-10x75-7643-BK	Black	10.00	75.00	80.43	250	R4400
◇	BM-10x75-7643-BL	Blue	10.00	75.00	80.43	250	R4400, R6000HF
◇	BM-10x75-7643-GN	Green	10.00	75.00	80.43	250	R4400, R6000HF
◇	BM-10x75-7643-OR	Orange	10.00	75.00	80.43	250	R4400, R6000HF
◇	BM-10x75-7643-RD	Red	10.00	75.00	80.43	250	R4400, R6000HF
◇	BM-10x75-7643-WT	White	10.00	75.00	80.43	250	R6000HF
▽	BM-10x75-7643-WT-L	White	10.00	75.00	81.17	250	R6000HF
◇	BM-10x75-7643-YL	Yellow	10.00	75.00	80.43	250	R4400, R6000HF
▽	BM-10x75-7643-YL-L	Yellow	10.00	75.00	81.17	250	R4400, R6000HF
◇	BM-15x75-7643-BK	Black	15.00	75.00	80.43	250	R4400
◇	BM-15x75-7643-BL	Blue	15.00	75.00	80.43	250	R4400, R6000HF
◇	BM-15x75-7643-GN	Green	15.00	75.00	80.43	250	R4400, R6000HF
◇	BM-15x75-7643-OR	Orange	15.00	75.00	80.43	250	R4400, R6000HF
◇	BM-15x75-7643-RD	Red	15.00	75.00	80.43	250	R4400, R6000HF
◇	BM-15x75-7643-WT	White	15.00	75.00	80.43	250	R6000HF
◇	BM-15x75-7643-YL	Yellow	15.00	75.00	80.43	250	R4400, R6000HF
◇	BM-25x75-7643-BK	Black	25.00	75.00	80.43	250	R4400
◇	BM-25x75-7643-BL	Blue	25.00	75.00	80.43	250	R4400, R6000HF
◇	BM-25x75-7643-GN	Green	25.00	75.00	80.43	250	R4400, R6000HF
◇	BM-25x75-7643-OR	Orange	25.00	75.00	80.43	250	R4400, R6000HF
◇	BM-25x75-7643-RD	Red	25.00	75.00	80.43	250	R4400, R6000HF
◇	BM-25x75-7643-WT	White	25.00	75.00	80.43	250	R6000HF
▽	BM-25x75-7643-WT-L	White	25.00	75.00	82.55	250	R6000HF
◇	BM-25x75-7643-YL	Yellow	25.00	75.00	80.43	250	R4400, R6000HF
▽	BM-25x75-7643-YL-L	Yellow	25.00	75.00	82.55	250	R4400, R6000HF

Order references beginning with "B" indicate bulk rolls.

Wire & cable marking



B-348 tag

- Brady's B-348 High Performance Tag complies with minimal smoke and halogen emission requirements of the most strict underground norms for High Performance vehicles.
- Printable both on-site and in the field, the tag is a practical solution to identify thick cables and cable bundles.
- This tag has excellent UV resistancy.

Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
B-348: Polyolefin							
◇	BM-10x60-348-WT	White	10.00	60.00	65.09	250	R6000HF
◇	BM-10x60-348-YL	Yellow	10.00	60.00	65.09	250	R4400, R6000HF
◇	BM-10x75-348-WT	White	10.00	75.00	80.43	250	R6000HF
◇	BM-10x75-348-YL	Yellow	10.00	75.00	80.43	250	R4400, R6000HF
◇	BM-15x75-348-WT	White	15.00	75.00	80.43	250	R6000HF
◇	BM-15x75-348-YL	Yellow	15.00	75.00	80.43	250	R4400, R6000HF
◇	BM-25x75-348-WT	White	25.00	75.00	80.43	250	R6000HF
◇	BM-25x75-348-YL	Yellow	25.00	75.00	80.43	250	R4400, R6000HF




BradyGrip™ print-on hook material

BradyGrip™ Print-on Hook Material is a one-of-a-kind solution that allows identification to be easily printed and placed on bundles. A grippy backing makes it easy to reposition or remove, so no need for costly rework. Just print on and place - it's that simple.

- Maximises your uptime with faster, printable ID for cable bundles.
- Apply, reposition and remove with exclusive, print-and-place material.
- Offers a non-damaging alternative to nylon cable ties.
- Customise labels to fit big or small jobs by printing on different-width material.

Diagram	Order Reference	Colour	Label Width A (mm)	Label Length B (m)
B-414: Polyester				
⊙	M7C-250-414	White	6.35	6.10 m
⊙	M7C-500-414	White	12.70	6.10 m
⊙	M7C-750-414	White	19.05	6.10 m
⊙	M7C-1000-414	White	25.40	6.10 m
⊙	M7C-1500-414	White	38.10	6.10 m



▶ See pages 49 - 51 for a detailed material index.

Wire & cable marking



DuraSleeve inserts

- Brady DuraSleeve printable inserts create a durable legend.
- Tags and inserts easily slide into the clear carriers.
- The legend can be changed before or after termination.




Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
B-7696: Vinyl							
⊗	M7-10x4.4-7696-WT	White	10.00	4.40	7.58	500	R6000HF, R6200, R6900
⊗	M7-10x4.4-7696-YL	Yellow	10.00	4.40	7.58	500	R6000HF, R6200
⊗	BM-10x4.4-7696-WT	White	10.00	4.40	7.56	2500	R6000HF, R6200
⊗	BM-10x4.4-7696-YL	Yellow	10.00	4.40	7.56	2500	R6000HF, R6200
⊗	M7-12x4.4-7696-WT	White	12.00	4.40	7.58	500	R6000HF, R6200, R6900
⊗	M7-12x4.4-7696-YL	Yellow	12.00	4.40	7.58	500	R6000HF, R6200
⊗	BM-12x4.4-7696-WT	White	12.00	4.40	7.56	2500	R6000HF, R6200
⊗	BM-12x4.4-7696-YL	Yellow	12.00	4.40	7.56	2500	R6000HF, R6200
⊗	M7-16x4.4-7696-WT	White	16.00	4.40	7.58	500	R6000HF, R6200, R6900
⊗	BM-16x4.4-7696-WT	White	16.00	4.40	7.56	2500	R6000HF, R6200
⊗	BM-16x4.4-7696-YL	Yellow	16.00	4.40	7.56	5000	R6000HF, R6200
⊗	M7-23x4.4-7696-WT	White	23.00	4.40	7.58	500	R6000HF, R6200, R6900
⊗	M7-23x4.4-7696-YL	Yellow	23.00	4.40	7.58	500	R6000HF, R6200
⊗	BM-23x4.4-7696-WT	White	23.00	4.40	7.56	2500	R6000HF, R6200
⊗	BM-23x4.4-7696-YL	Yellow	23.00	4.40	7.56	2500	R6000HF, R6200
⊗	M7-30x4.4-7696-WT	White	30.00	4.40	7.58	500	R6000HF, R6200, R6900
⊗	BM-30x4.4-7696-WT	White	30.00	4.40	7.56	2500	R6000HF, R6200
⊗	BM-30x4.4-7696-YL	Yellow	30.00	4.40	7.56	5000	R6000HF, R6200
B-7697: Polyester							
⊗	M7-10x4.4-7697-WT	White	10.00	4.40	7.58	500	R4300, R6200
⊗	M7-12x4.4-7697-WT	White	12.00	4.40	7.58	500	R4300, R6200
⊗	M7-16x4.4-7697-WT	White	16.00	4.40	7.58	500	R4300, R6200
⊗	M7-23x4.4-7697-WT	White	23.00	4.40	7.58	500	R4300, R6200
⊗	M7-30x4.4-7697-WT	White	30.63	4.40	7.58	500	R4300, R6200

Order references beginning with "B" indicate bulk rolls.

DuraSleeve tag carrier

DuraSleeve tag carriers are produced in transparent PVC. The special shape of the carrier allows it to adapt to cables of various diameters. There are several sizes of carriers which cater for cables with external diameters from 1.50 mm up to 14 mm.

- Temperature range: -40 °C to 60 °C
- Material: PVC

Please contact your local Brady representative to identify and select the most appropriate carrier for your individual application.



Order Reference	Colour	Carrier Length	Min. Wire Diameter (mm)	Max. Wire Diameter (mm)	Carriers per Box
PVC					
DMC-1.5/2.5-10	Transparent	10.00	1.50	2.50	1000
DMC-2/4-10	Transparent	10.00	2.00	4.00	1000
DMC-4/7-10	Transparent	10.00	4.00	7.00	500
DMC-6/10-10	Transparent	10.00	6.00	10.00	500
DMC-10/14-10	Transparent	10.00	10.00	14.00	200
DMC-1.5/2.5-12	Transparent	12.00	1.50	2.50	1000
DMC-2/4-12	Transparent	12.00	2.00	4.00	1000
DMC-4/7-12	Transparent	12.00	4.00	7.00	500
DMC-6/10-12	Transparent	12.00	6.00	10.00	500
DMC-10/14-12	Transparent	12.00	10.00	14.00	200
DMC-10/14-16	Transparent	16.00	10.00	14.00	200
DMC-1.5/2.5-16	Transparent	16.00	1.50	2.50	1000

Order Reference	Colour	Carrier Length	Min. Wire Diameter (mm)	Max. Wire Diameter (mm)	Carriers per Box
DMC-2/4-16	Transparent	16.00	2.00	4.00	1000
DMC-4/7-16	Transparent	16.00	4.00	7.00	500
DMC-6/10-16	Transparent	16.00	6.00	10.00	500
DMC-1.5/2.5-23	Transparent	23.00	1.50	2.50	500
DMC-2/4-23	Transparent	23.00	2.00	4.00	500
DMC-4/7-23	Transparent	23.00	4.00	7.00	500
DMC-6/10-23	Transparent	23.00	6.00	10.00	200
DMC-10/14-23	Transparent	23.00	10.00	14.00	200
DMC-1.5/2.5-30	Transparent	30.00	1.50	2.50	500
DMC-2/4-30	Transparent	30.00	2.00	4.00	500
DMC-4/7-30	Transparent	30.00	4.00	7.00	200
DMC-6/10-30	Transparent	30.00	6.00	10.00	200
DMC-10/14-30	Transparent	30.00	10.00	14.00	200

Component & equipment marking

EPREP: Engraved Plate REplacement Labels

Brady EPREP labels are innovative labels specifically designed to replace engraved and plotted plates for identification of electrical components, electrical cabinets, push buttons, patch panels etc.





Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Hole Diameter C (mm)	Vertical Repeat D (mm)	Labels per Roll	Layout	Printer Ribbon Series
B-7593: Polyethylene Foam Laminate Polyester									
▲	M7-1-7593-SL	Silver	27.00	7.95	-	11.18	250	Individual on a Roll	R4400, R6000HF, R6900
▲	M7-1-7593-WT	White	27.00	7.95	-	11.18	250	Individual on a Roll	R6000HF, R6900
▲	M7-2-7593-SL	Silver	27.00	12.45	-	15.63	250	Individual on a Roll	R4400, R6000HF, R6900
▲	M7-2-7593-WT	White	27.00	12.45	-	15.63	250	Individual on a Roll	R6000HF, R6900
▲	M7-3-7593-SL	Silver	27.00	15.00	-	18.14	150	Individual on a Roll	R4400, R6000HF, R6900
▲	M7-3-7593-WT	White	27.00	15.00	-	18.14	150	Individual on a Roll	R6000HF, R6900
▲	M7-4-7593-SL	Silver	27.00	18.00	-	21.25	150	Individual on a Roll	R4400, R6000HF, R6900
▲	M7-4-7593-WT	White	27.00	18.00	-	21.25	150	Individual on a Roll	R6000HF, R6900
△	M7-5-7593-BK	Black	30.00	40.00	24.00	50.80	100	Fan-folded	R4400-WT
△	M7-5-7593-GN	Green	30.00	40.00	24.00	50.80	100	Fan-folded	R4400, R6000HF, R6900
△	M7-5-7593-RD	Red	30.00	40.00	24.00	50.80	100	Fan-folded	R4400, R6000HF, R6900
△	M7-5-7593-SL	Silver	30.00	40.00	24.00	50.80	100	Fan-folded	R4400, R6000HF, R6900
△	M7-5-7593-WT	White	30.00	40.00	24.00	50.80	100	Fan-folded	R6000HF, R6900
△	M7-5-7593-YL	Yellow	30.00	40.00	24.00	50.80	100	Fan-folded	R4400, R6000HF, R6900
▲	M7-7-7593-SL	Silver	35.00	18.00	-	21.49	100	Individual on a Roll	R4400, R6000HF, R6900
▲	M7-7-7593-WT	White	35.00	18.00	-	21.49	100	Individual on a Roll	R6000HF, R6900
▲	M7-7-7593-YL	Yellow	35.00	18.00	-	21.49	100	Individual on a Roll	R4400, R6000HF, R6900
▲	M7-6-7593-BK	Black	45.00	15.00	-	40.37	100	Fan-folded	R4400-WT
▲	M7-6-7593-RD	Red	45.00	15.00	-	40.37	100	Fan-folded	R4400, R6000HF, R6900
▲	BM-06-7593-SL	Silver	45.00	15.00	-	18.26	450	Individual on a Roll	R4400, R6000HF
▲	BM-06-7593-WT	White	45.00	15.00	-	18.26	450	Individual on a Roll	R4400, R6000HF
▲	M7-6-7593-WT	White	45.00	15.00	-	40.37	100	Fan-folded	R6000HF, R6900
▲	M7-6-7593-YL	Yellow	45.00	15.00	-	40.37	100	Fan-folded	R4400, R6000HF, R6900
▲	M7-8-7593-SL	Silver	48.00	19.00	-	22.46	125	Individual on a Roll	R4400, R6000HF, R6900
▲	M7-8-7593-WT	White	48.00	19.00	-	22.46	125	Individual on a Roll	R6000HF, R6900

Order references beginning with "B" indicate bulk rolls.

Circuit breaker marking

Labels that neatly fit the most commonly used circuit breakers

Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Label Length B (m)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
B-423: Polyester								
▲	M7-220-423	White	15.00	6.00	-	9.20	750	R6000HF, R6200, R6900
▲	M7-220-423-YL	Yellow	15.00	6.00	-	9.20	750	R4400, R6000HF, R6900
▲	M7-219-423	White	17.00	6.00	-	9.20	750	R6000HF, R6200, R6900
▲	M7-219-423-YL	Yellow	17.00	6.00	-	9.20	750	R4400, R6000HF, R6900
B-499: Nylon Cloth								
▲	M7-220-499	White	15.00	6.00	-	9.20	750	R4300, R6000HF, R6200, R6900
▲	M7-220-499-YL	Yellow	15.00	6.00	-	9.20	750	R4300, R6000HF, R6200, R6900
▲	M7-219-499	White	17.00	6.00	-	9.20	750	R4300, R6000HF, R6200, R6900
▲	M7-219-499-YL	Yellow	17.00	6.00	-	9.20	750	R4300, R6000HF, R6200, R6900



Order references beginning with "B" indicate bulk rolls.

▶ See pages 49 - 51 for a detailed material index.

Component & equipment marking



Punch block and patch panel labels

- Create a fully-formatted serialised punch block label to fit your equipment.
- Label your ports, jack and outlets with adhesive labels or slide-in strips.





Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Label Length B (m)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
B-412: Polypropylene								
⊙	M7C-230-412	White	5.84	-	15.24	-	1	R4300, R6200
⊙	M7C-375-412	White	9.53	-	15.24	-	1	R4300, R6200
⊙	M7C-475-412	White	12.07	-	15.24	-	1	R4300, R6200
⊙	M7C-785-412	White	19.94	-	15.24	-	1	R4300, R6200
B-422: Polyester								
▲	M7-45-422	White	38.10	9.53	-	12.70	500	R6000HF, R6900
▲	M7-30-422	White	38.10	19.05	-	22.23	250	R6000HF, R6900
⊙	M7C-375-422	White	9.53	-	15.24	-	1	R6000HF, R6900
⊙	M7C-475-422	White	12.07	-	15.24	-	1	R6000HF, R6900
⊙	M7C-500-422	White	12.70	-	15.24	-	1	R6000HF, R6900
⊙	M7C-625-422	White	15.88	-	15.24	-	1	R6000HF, R6900
⊙	M7C-1000-422	White	25.40	-	15.24	-	1	R6000HF, R6900
B-423: Polyester								
▲	M7-1-423	White	6.35	6.35	-	9.53	750	R6000HF, R6200, R6900
▲	M7-3-423	White	9.53	9.53	-	12.70	500	R6000HF, R6200, R6900
▲	M7-4-423	White	10.16	10.16	-	13.34	500	R6000HF, R6200, R6900
▲	M7-7-423	White	12.70	12.70	-	15.88	500	R6000HF, R6200, R6900
▲	M7-6-423	White	12.70	6.99	-	10.16	750	R6000HF, R6200, R6900
▲	M7-5-423	White	12.70	5.08	-	8.26	750	R6000HF, R6200, R6900
▲	BM-7-423	White	12.70	12.70	-	15.88	5000	R4400, R6000HF, R6200
▲	M7-9-423	White	16.51	5.08	-	8.26	750	R6000HF, R6200, R6900
▲	M7-10-423	White	19.05	6.35	-	9.53	750	R6000HF, R6200, R6900
▲	M7-13-423	White	22.86	6.35	-	9.53	750	R6000HF, R6200, R6900
▲	M7-19-423	White	25.40	25.40	-	28.58	250	R6000HF, R6200, R6900
▲	M7-17-423	White	25.40	12.70	-	15.88	500	R6000HF, R6200, R6900
▲	M7-16-423	White	25.40	9.53	-	12.70	500	R6000HF, R6200, R6900
▲	M7-15-423	White	25.40	6.99	-	10.16	750	R6000HF, R6200, R6900
▲	M7-14-423	White	25.40	4.75	-	8.26	750	R6000HF, R6200, R6900
▲	BM-17-423	White	25.40	12.70	-	15.88	5000	R4400, R6000HF, R6200
▲	BM-16-423	White	25.40	9.53	-	12.70	5000	R4400, R6000HF, R6200
▲	BM-19-423	White	25.40	25.40	-	28.58	2500	R4400, R6000HF, R6200
▲	M7-25-423	White	31.75	6.35	-	9.53	750	R6000HF, R6200, R6900
▲	M7-32-423	White	38.10	38.10	-	41.28	250	R6000HF, R6200, R6900
▲	M7-31-423	White	38.10	25.40	-	28.58	250	R6000HF, R6200, R6900
▲	M7-29-423	White	38.10	12.70	-	15.88	500	R6000HF, R6200, R6900
▲	M7-28-423	White	38.10	6.35	-	9.53	750	R6000HF, R6200, R6900
▲	M7-27-423	White	38.10	3.18	-	6.35	750	R6000HF, R6200, R6900
▲	BM-29-423	White	38.10	12.70	-	15.88	5000	R4400, R6000HF, R6200
⊙	M7C-500-423	White	12.70	-	15.24	-	1	R6000HF, R6200, R6900
B-428: Metallised Polyester								
▲	M7-17-428	Light Grey	25.40	12.70	-	15.88	500	R4300, R6200
▲	M7-15-428	Light Grey	25.40	6.99	-	10.16	750	R4300, R6200
▲	BM-17-428	Light Grey	25.40	12.70	-	15.88	5000	R4300
▲	M7-29-428	Light Grey	38.10	12.70	-	15.88	500	R4300, R6200
⊙	M7C-500-428	Light Grey	12.70	-	15.24	-	1	R4300, R6200
B-430: Polyester								
▲	M7-71-430	Transparent	8.89	5.08	-	9.53	750	R4400, R6000HF, R6200, R6900
▲	M7-17-430	Transparent	25.40	12.70	-	15.88	500	R4400, R6000HF, R6200, R6900

Order references beginning with "B" indicate bulk rolls.

>>

Component & equipment marking



Punch block and patch panel labels (continued)

Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Label Length B (m)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
▲	M7-16-430	Transparent	25.40	9.53	-	12.70	500	R4400, R6000HF, R6200, R6900
▲	M7-45-430	Transparent	38.10	9.53	-	12.70	500	R4400, R6000HF, R6200, R6900
◎	M7C-375-430	Transparent	9.53	-	15.24	-	1	R4400, R6000HF, R6200, R6900
◎	M7C-500-430	Transparent	12.70	-	15.24	-	1	R4400, R6000HF, R6200, R6900
◎	M7C-1000-430	Transparent	25.40	-	15.24	-	1	R4400, R6000HF, R6200, R6900
B-483A: Polyester								
▲	M7-19-483	White	25.40	25.40	-	28.58	250	R6000HF, R6300, R6900
▲	M7-17-483	White	25.40	12.70	-	15.88	500	R6000HF, R6300, R6900
▲	M7-16-483	White	25.40	9.53	-	12.70	500	R6000HF, R6300, R6900
▲	M7-65-483	White	34.93	25.40	-	28.58	250	R6000HF, R6300, R6900
▲	M7-31-483	White	38.10	25.40	-	28.58	250	R6000HF, R6300, R6900
▲	M7-30-483	White	38.10	19.05	-	22.23	250	R6000HF, R6300, R6900
▲	M7-29-483	White	38.10	12.70	-	15.88	500	R6000HF, R6300, R6900
◎	M7C-500-483	White	12.70	-	15.24	-	1	R6000HF, R6300, R6900
◎	M7C-1000-483	White	25.40	-	15.24	-	1	R6000HF, R6300, R6900


Order references beginning with "B" indicate bulk rolls.

Terminal block markers

The repositionable vinyl cloth marker fits any terminal block and combines strong adhesion with easy removal and reapplication. The semi-rigid B-7696 label is precisely sized to slide into or click onto Wago terminal blocks.




Diagram	Order Reference	Colour	Label Width A (mm)	Label Length B (m)	Labels per Roll	Printer Ribbon Series
B-498: Vinyl Cloth						
∞	M7C-240-498	White	6.10	9.14	1	R4300, R6000HF, R6200, R6900
∞	M7C-318-498	White	8.08	9.14	1	R4300, R6000HF, R6200, R6900
∞	M7C-375-498	White	9.53	9.14	1	R4300, R6000HF, R6200, R6900
∞	M7C-500-498	White	12.70	9.14	1	R4300, R6000HF, R6200, R6900
∞	BM7C-240-498	White	6.10	83.82	1	R4300, R6000HF, R6200, R6900
∞	BMC-375-498	White	9.53	83.82	1	R4300, R6200, R6600
B-7696: Vinyl						
◆	M7C-433-7696	White	11.00	10.00	1	R6000HF, R6200, R6900



Faceplate labels

A variety of durable and resistant materials to label your workstation.

Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Vertical Repeat D (mm)	Labels per Roll	For Data Cables Sized to Fit	Printer Ribbon Series
B-412: Polypropylene								
⊞	M7-40-412	White	49.23	9.53	9.53	750	DesiStrip	R4300, R6200
⊞	BM-40-412	White	49.23	9.53	9.53	5000	DesiStrip	R4300, R6200
B-422: Polyester								
▲	M7-45-422	White	38.10	9.53	12.70	500	Location Identification	R6000HF, R6900
B-430: Polyester								
▲	M7-71-430	Transparent	8.89	5.08	9.53	750	Faceplates & Outlets	R4400, R6000HF, R6200, R6900
▲	M7-17-430	Transparent	25.40	12.70	15.88	500	1-4 Outlet Faceplates, Location Identification	R4400, R6000HF, R6200, R6900
▲	M7-16-430	Transparent	25.40	9.53	12.70	500		R4400, R6000HF, R6200, R6900
▲	M7-45-430	Transparent	38.10	9.53	12.70	500	Location Identification, 1-4 Outlet Faceplates	R4400, R6000HF, R6200, R6900



Order references beginning with "B" indicate bulk rolls.


▶ See pages 49 - 51 for a detailed material index.

Asset & component marking



Asset and equipment labels

Suitable for rough, textured, low and high energy surfaces – for lasting identification on all types of equipment and materials.



For rough surfaces

Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Label Length B (m)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
B-483A: Polyester								
▲	M7-61-483	White	12.70	50.80	-	53.98	100	R6000HF, R6300, R6900
▲	M7-20-483	White	25.40	50.80	-	53.98	100	R6000HF, R6300, R6900
▲	M7-19-483	White	25.40	25.40	-	28.58	250	R6000HF, R6300, R6900
▲	M7-17-483	White	25.40	12.70	-	15.88	500	R6000HF, R6300, R6900
▲	M7-16-483	White	25.40	9.53	-	12.70	500	R6000HF, R6300, R6900
▲	M7-65-483	White	34.93	25.40	-	28.58	250	R6000HF, R6300, R6900
▲	M7-31-483	White	38.10	25.40	-	28.58	250	R6000HF, R6300, R6900
▲	M7-30-483	White	38.10	19.05	-	22.23	250	R6000HF, R6300, R6900
▲	M7-29-483	White	38.10	12.70	-	15.88	500	R6000HF, R6300, R6900
▲	M7-37-483	White	76.20	48.26	-	79.38	100	R6000HF, R6300, R6900
▲	M7-38-483	White	101.60	48.26	-	104.78	100	R6000HF, R6300, R6900
▲	M7-23-483	White	101.60	25.40	-	104.78	100	R6000HF, R6300, R6900
⊙	M7C-500-483	White	12.70	-	15.24	-	1	R6000HF, R6300, R6900
⊙	M7C-1000-483	White	25.40	-	15.24	-	1	R6000HF, R6300, R6900
⊙	M7C-1900-483	White	50.80	-	15.24	-	1	R6000HF, R6300, R6900
B-489A: Polyester								
▲	M7-17-489	White	25.40	12.70	-	15.88	500	R4300, R6200
▲	M7-32-489	White	38.10	38.10	-	41.28	250	R4300, R6200
▲	M7-29-489	White	38.10	12.70	-	15.88	500	R4300, R6200
▲	M7-38-489	White	101.60	48.26	-	104.78	100	R4300, R6200

For low energy and textured surfaces

Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Label Length B (m)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
B-422: Polyester								
▲	M7-45-422	White	38.10	9.53	-	12.70	500	R6000HF, R6900
▲	M7-30-422	White	38.10	19.05	-	22.23	250	R6000HF, R6900
▲	BM-20-422	White	50.80	25.40	-	53.98	1000	R4400, R6000HF, R6200
▲	M7-37-422	White	76.20	48.26	-	79.38	100	R6000HF, R6900
⊙	M7C-375-422	White	9.53	-	15.24	-	1	R6000HF, R6900
⊙	M7C-475-422	White	12.07	-	15.24	-	1	R6000HF, R6900
⊙	M7C-500-422	White	12.70	-	15.24	-	1	R6000HF, R6900
⊙	M7C-625-422	White	15.88	-	15.24	-	1	R6000HF, R6900
⊙	M7C-1000-422	White	25.40	-	15.24	-	1	R6000HF, R6900
⊙	M7C-1900-422	White	50.80	-	15.24	-	1	R6000HF, R6900
B-499: Nylon Cloth								
▲	M7-7-499	White	12.70	12.70	-	15.88	500	R4300, R6000HF, R6200, R6900
▲	M7-29-499	White	12.70	38.10	-	15.88	500	R4300, R6000HF, R6200, R6900
▲	M7-11-499	White	12.70	19.05	-	15.88	500	R4300, R6000HF, R6200, R6900
▲	M7-67-499-YL	Yellow	15.00	9.00	-	-	750	R4300, R6000HF, R6200, R6900
▲	M7-41-499-YL	Yellow	16.00	5.00	-	-	750	R4300, R6000HF, R6200, R6900
▲	M7-18-499	White	19.05	25.40	-	22.23	250	R4300, R6000HF, R6200, R6900
▲	BM-11-499	White	19.05	12.70	-	15.88	5000	R4300, R6200
▲	M7-84-499	White	22.86	12.70	-	15.88	500	R4300, R6000HF, R6200, R6900
▲	M7-19-499	White	25.40	25.40	-	28.58	250	R4300, R6000HF, R6200, R6900
▲	M7-16-499	White	25.40	9.53	-	12.70	500	R4300, R6000HF, R6200, R6900
▲	M7-21-499	White	25.40	63.50	-	66.68	100	R4300, R6000HF, R6200, R6900
▲	M7-31-499	White	38.10	25.40	-	28.58	250	R4300, R6000HF, R6200, R6900
▲	M7-30-499	White	38.10	19.05	-	22.23	250	R4300, R6000HF, R6200, R6900
▲	M7-28-499	White	38.10	6.35	-	9.53	750	R4300, R6000HF, R6200, R6900

▶ See pages 49, 51 - 51 for a detailed material index.

>>

Asset & component marking

Asset and equipment labels (continued)




Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Label Length B (m)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
▲	M7-81-499	White	48.26	6.35	-	9.53	750	R4300, R6000HF, R6200, R6900
▲	M7-78-499	White	48.26	25.40	-	28.58	250	R4300, R6000HF, R6200, R6900
⊙	M7C-500-499	White	12.70	-	9.14	-	1	R4300, R6000HF, R6200, R6900
⊙	M7C-1000-499	White	25.40	-	9.14	-	1	R4300, R6000HF, R6200, R6900
⊙	M7C-1900-499	White	48.26	-	9.14	-	1	R4300, R6000HF, R6200, R6900
B-595: Vinyl								
∞	M7C-250-595-WT	White	6.35	-	15.24	-	1	R6000HF, R6900, R10000
∞	M7C-250-595-YL	Yellow	6.35	-	15.24	-	1	R4400, R6000HF, R6900, R10000
∞	M7C-500-595-BK	Black	12.70	-	15.24	-	1	R4400, R6700, R6900, R10000
∞	M7C-500-595-BL	Blue	12.70	-	15.24	-	1	R4400, R6000HF, R6900, R10000
∞	M7C-500-595-GN	Green	12.70	-	15.24	-	1	R4400, R6000HF, R6900, R10000
∞	M7C-500-595-OR	Orange	12.70	-	15.24	-	1	R4400, R6000HF, R6900, R10000
∞	M7C-500-595-RD	Red	12.70	-	15.24	-	1	R4400, R6000HF, R6900, R10000
∞	M7C-500-595-CL	Transparent	12.70	-	15.24	-	1	R4400, R6000HF, R6900, R10000
∞	M7C-500-595-WT	White	12.70	-	15.24	-	1	R6000HF, R6900, R10000
∞	M7C-500-595-YL	Yellow	12.70	-	15.24	-	1	R4400, R6000HF, R6900, R10000
∞	M7C-1000-595-BK	Black	25.40	-	15.24	-	1	R4400, R6700, R6900, R10000
∞	M7C-1000-595-BL	Blue	25.40	-	15.24	-	1	R4400, R6000HF, R6900, R10000
∞	M7C-1000-595-GN	Green	25.40	-	15.24	-	1	R4400, R6000HF, R6900, R10000
∞	M7C-1000-595-OR	Orange	25.40	-	15.24	-	1	R4400, R6000HF, R6900, R10000
∞	M7C-1000-595-RD	Red	25.40	-	15.24	-	1	R4400, R6000HF, R6900, R10000
∞	M7C-1000-595-CL	Transparent	25.40	-	15.24	-	1	R4400, R6000HF, R6900, R10000
∞	M7C-1000-595-WT	White	25.40	-	15.24	-	1	R6000HF, R6900, R10000
∞	M7C-1000-595-YL	Yellow	25.40	-	15.24	-	1	R4400, R6000HF, R6900, R10000
∞	M7C-2000-595-BK	Black	50.80	-	15.24	-	1	R4400, R6700, R6900, R10000
∞	M7C-2000-595-BL	Blue	50.80	-	15.24	-	1	R4400, R6000HF, R6900, R10000
∞	M7C-2000-595-GN	Green	50.80	-	15.24	-	1	R4400, R6000HF, R6900, R10000
∞	M7C-2000-595-OR	Orange	50.80	-	15.24	-	1	R4400, R6000HF, R6900, R10000
∞	M7C-2000-595-RD	Red	50.80	-	15.24	-	1	R4400, R6000HF, R6900, R10000
∞	M7C-2000-595-CL	Transparent	50.80	-	15.24	-	1	R4400, R6000HF, R6900, R10000
∞	M7C-2000-595-WT	White	50.80	-	15.24	-	1	R6000HF, R6900, R10000
∞	M7C-2000-595-YL	Yellow	50.80	-	15.24	-	1	R4400, R6000HF, R6900, R10000

For smooth, high energy surfaces

Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Label Length B (m)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
B-430: Polyester								
▲	M7-71-430	Transparent	8.89	5.08	-	9.53	750	R4400, R6000HF, R6200, R6900
▲	M7-17-430	Transparent	25.40	12.70	-	15.88	500	R4400, R6000HF, R6200, R6900
▲	M7-16-430	Transparent	25.40	9.53	-	12.70	500	R4400, R6000HF, R6200, R6900
▲	M7-45-430	Transparent	38.10	9.53	-	12.70	500	R4400, R6000HF, R6200, R6900
⊙	M7C-375-430	Transparent	9.53	-	15.24	-	1	R4400, R6000HF, R6200, R6900
⊙	M7C-500-430	Transparent	12.70	-	15.24	-	1	R4400, R6000HF, R6200, R6900
⊙	M7C-1000-430	Transparent	25.40	-	15.24	-	1	R4400, R6000HF, R6200, R6900
⊙	M7C-1900-430	Transparent	50.80	-	15.24	-	1	R4400, R6000HF, R6200, R6900
B-488: Polyester								
▲	M7-80-488	White	19.05	22.86	-	28.58	250	R4300, R6200
▲	M7-97-488	White	22.86	22.86	-	28.58	250	R4300, R6200
▲	M7-81-488	White	48.26	6.35	-	9.53	750	R4300, R6200
B-529: Polypropylene								
⊙	M7C-1000-529	White	25.40	-	15.24	-	1	R6000HF
⊙	M7C-2000-529	White	50.80	-	15.24	-	1	R6000HF
L-2588-53B: Polyester								
▲	M7-221-483-UHF	White	45.00	18.00	-	22.23	100	R6000HF




Asset & component marking



Rating and name plate labels

Choose from several materials with aggressive adhesives for use in commercial/industrial applications, including low surface energy and textured surfaces.



For rough surfaces

Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Label Length B (m)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
B-486B: Metallised Polyester								
▲	M7-20-486	Light Grey	25.40	50.80	-	53.98	100	R4300, R6200
▲	M7-17-486	Light Grey	25.40	12.70	-	15.88	500	R4300, R6200
▲	M7-30-486	Light Grey	38.10	19.05	-	22.23	250	R4300, R6200
▲	M7-29-486	Light Grey	38.10	12.70	-	15.88	500	R4300, R6200
▲	M7-37-486	Light Grey	76.20	48.26	-	79.38	100	R4300, R6200

For low energy and textured surfaces

Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Label Length B (m)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
B-435A: Metallised Polyester								
▲	M7-20-435	Silver	25.40	50.80	-	53.98	100	R6000HF
▲	M7-17-435	Silver	25.40	12.70	-	15.88	500	R6000HF
▲	M7-31-435	Silver	38.10	25.40	-	28.58	250	R6000HF
▲	M7-30-435	Silver	38.10	19.05	-	22.23	250	R6000HF
▲	M7-37-435	Silver	76.20	48.26	-	79.38	100	R6000HF

For smooth, high energy surfaces

Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Label Length B (m)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
B-423: Polyester								
▲	M7-1-423	White	6.35	6.35	-	9.53	750	R6000HF, R6200, R6900
▲	M7-3-423	White	9.53	9.53	-	12.70	500	R6000HF, R6200, R6900
▲	M7-4-423	White	10.16	10.16	-	13.34	500	R6000HF, R6200, R6900
▲	M7-7-423	White	12.70	12.70	-	15.88	500	R6000HF, R6200, R6900
▲	M7-6-423	White	12.70	6.99	-	10.16	750	R6000HF, R6200, R6900
▲	M7-5-423	White	12.70	5.08	-	8.26	750	R6000HF, R6200, R6900
▲	BM-7-423	White	12.70	12.70	-	15.88	5000	R6000HF, R6200, R6900
▲	M7-9-423	White	16.51	5.08	-	8.26	750	R6000HF, R6200, R6900
▲	M7-10-423	White	19.05	6.35	-	9.53	750	R6000HF, R6200, R6900
▲	M7-13-423	White	22.86	6.35	-	9.53	750	R6000HF, R6200, R6900
▲	M7-20-423	White	25.40	50.80	-	53.98	100	R6000HF, R6200, R6900
▲	M7-19-423	White	25.40	25.40	-	28.58	250	R6000HF, R6200, R6900
▲	M7-17-423	White	25.40	12.70	-	15.88	500	R6000HF, R6200, R6900
▲	M7-16-423	White	25.40	9.53	-	12.70	500	R6000HF, R6200, R6900
▲	M7-15-423	White	25.40	6.99	-	10.16	750	R6000HF, R6200, R6900
▲	M7-14-423	White	25.40	4.75	-	8.26	750	R6000HF, R6200, R6900
▲	BM-17-423	White	25.40	12.70	-	15.88	5000	R6000HF, R6200, R6900
▲	BM-20-423	White	25.40	50.80	-	53.98	1000	R6000HF, R6200, R6900
▲	BM-16-423	White	25.40	9.53	-	12.70	5000	R6000HF, R6200, R6900
▲	BM-19-423	White	25.40	25.40	-	28.58	2500	R6000HF, R6200, R6900
▲	M7-24-423-BK	White	28.70	12.70	-	15.88	500	R6000HF, R6200, R6900
▲	M7-25-423	White	31.75	6.35	-	9.53	750	R6000HF, R6200, R6900
▲	M7-32-423	White	38.10	38.10	-	41.28	250	R6000HF, R6200, R6900
▲	M7-31-423	White	38.10	25.40	-	28.58	250	R6000HF, R6200, R6900
▲	M7-29-423	White	38.10	12.70	-	15.88	500	R6000HF, R6200, R6900
▲	M7-28-423	White	38.10	6.35	-	9.53	750	R6000HF, R6200, R6900
▲	M7-27-423	White	38.10	3.18	-	6.35	750	R6000HF, R6200, R6900
▲	BM-29-423	White	38.10	12.70	-	15.88	5000	R6000HF, R6200, R6900

Order references beginning with "B" indicate bulk rolls.

>>

▶ See pages 49 - 51 for a detailed material index.

Asset & component marking

Rating and name plate labels (continued)





Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Label Length B (m)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
▲	M7-2-423	White	50.80	6.35	-	53.98	100	R6000HF, R6200, R6900
▲	M7-26-423	White	69.85	31.75	-	73.03	100	R6000HF, R6200, R6900
▲	M7-37-423	White	76.20	48.26	-	79.38	100	R6000HF, R6200, R6900
▲	M7-22-423	White	76.20	25.40	-	79.38	100	R6000HF, R6200, R6900
▲	M7-38-423	White	101.60	48.26	-	104.78	100	R6000HF, R6200, R6900
▲	M7-23-423	White	101.60	25.40	-	104.78	100	R6000HF, R6200, R6900
⊙	M7C-500-423	White	12.70	-	15.24	-	1	R6000HF, R6200, R6900
B-428: Metallised Polyester								
▲	M7-20-428	Light Grey	25.40	50.80	-	53.98	100	R4300, R6200
▲	M7-17-428	Light Grey	25.40	12.70	-	15.88	500	R4300, R6200
▲	M7-15-428	Light Grey	25.40	6.99	-	10.16	750	R4300, R6200
▲	BM-17-428	Light Grey	25.40	12.70	-	15.88	5000	R4300, R6200
▲	M7-29-428	Light Grey	38.10	12.70	-	15.88	500	R4300, R6200
▲	BM-20-428	Light Grey	50.80	25.40	-	53.98	1000	R4300, R6200
▲	M7-26-428	Light Grey	69.85	31.75	-	73.03	100	R4300, R6200
▲	M7-22-428	Light Grey	76.20	25.40	-	79.38	100	R4300, R6200
▲	M7-38-428	Light Grey	101.60	48.26	-	104.78	100	R4300, R6200
⊙	M7C-500-428	Light Grey	12.70	-	15.24	-	1	R4300, R6200

Order references beginning with "B" indicate bulk rolls.



Security identification labels

Tamper-resistant tape destructs into tiny fragments when being removed, makes any attempts to remove the label very difficult and time consuming.

Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Label Length B (m)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
B-351: Tamper-resistant Vinyl								
▲	M7-20-351	White	25.40	50.80	-	53.98	100	R6000HF, R6200
▲	M7-17-351	White	25.40	12.70	-	15.88	500	R6000HF, R6200
▲	M7-31-351	White	38.10	25.40	-	28.58	250	R6000HF, R6200
▲	M7-37-351	White	76.20	48.26	-	79.38	100	R6000HF, R6200
B-362: Tamper-resistant Metallised Vinyl								
▲	M7-17-362	Silver	25.40	12.70	-	15.88	500	R6000HF, R6900
▲	M7-31-362	Silver	38.10	25.40	-	28.58	250	R6000HF, R6900
▲	M7-20-362	Silver	50.80	25.40	-	53.98	100	R6000HF, R6900
▲	M7-37-362	Silver	76.20	48.26	-	79.38	100	R6000HF, R6900
B-530: Tamper-resistant Vinyl								
⊙	M7C-500-530	White	12.70	-	15.24	-	1	R6000HF, R6900
⊙	M7C-1000-530	White	25.40	-	15.24	-	1	R6000HF, R6900
⊙	M7C-2000-530	White	50.80	-	15.24	-	1	R6000HF, R6900

5S Colour coded marking / Safety signage



High performance indoor/outdoor vinyl

- Adheres to difficult low surface energy items, including: PVC piping, blow-molded equipment cases, ABS plastics, powder-coated surfaces and equipment made from recycled plastics.
- Excels at sticking to highly textured surfaces such as painted cinder block walls, finished uneven wood, textured plastics, rough-pipes and paper-jacketed pipes.
- 8 to 10** year outdoor durability average in temperatures from -40°C to 82°C, can be applied as low as -18 °C

Diagram	Order Reference	Colour	Finish	Label Width A (mm)	Label Length B (m)	Labels per Roll	Printer Ribbon Series
B-595: Vinyl							
∞	M7C-250-595-WT	White	Gloss	6.35	15.24 m	1	R6000HF, R6900, R10000
∞	M7C-250-595-YL	Yellow	Gloss	6.35	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-375-595-BL	Blue	Gloss	9.53	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-375-595-GN	Green	Gloss	9.53	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-375-595-OR	Orange	Gloss	9.53	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-375-595-RD	Red	Gloss	9.53	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-375-595-WT	White	Gloss	9.53	15.24 m	1	R6000HF, R6900, R10000
∞	M7C-375-595-YL	Yellow	Gloss	9.53	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-500-595-BK	Black	Gloss	12.70	15.24 m	1	R4400, R6700, R6900, R10000
∞	M7C-500-595-BL	Blue	Gloss	12.70	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-500-595-BR	Brown	Gloss	12.70	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-500-595-GD	Gold	Gloss	12.70	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-500-595-GN	Green	Gloss	12.70	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-500-595-GY	Grey	Gloss	12.70	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-500-595-LB	Light Blue	Gloss	12.70	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-500-595-OC	Ochre	Gloss	12.70	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-500-595-OR	Orange	Gloss	12.70	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-500-595-PK	Pink	Gloss	12.70	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-500-595-PL	Purple	Gloss	12.70	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-500-595-RD	Red	Gloss	12.70	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-500-595-SB	Sky Blue	Gloss	12.70	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-500-595-TN	Tan	Gloss	12.70	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-500-595-CL	Transparent	Gloss	12.70	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-500-595-WT	White	Gloss	12.70	15.24 m	1	R6000HF, R6900, R10000
∞	M7C-500-595-YL	Yellow	Gloss	12.70	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-750-595-BL	Blue	Gloss	19.05	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-750-595-GN	Green	Gloss	19.05	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-750-595-OR	Orange	Gloss	19.05	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-750-595-RD	Red	Gloss	19.05	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-750-595-WT	White	Gloss	19.05	15.24 m	1	R6000HF, R6900, R10000
∞	M7C-750-595-YL	Yellow	Gloss	19.05	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-1000-595-BK	Black	Gloss	25.40	15.24 m	1	R4400, R6700, R6900, R10000
∞	M7C-1000-595-BL	Blue	Gloss	25.40	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-1000-595-BR	Brown	Gloss	25.40	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-1000-595-GD	Gold	Gloss	25.40	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-1000-595-GN	Green	Gloss	25.40	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-1000-595-GY	Grey	Gloss	25.40	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-1000-595-LB	Light Blue	Gloss	25.40	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-1000-595-OC	Ochre	Gloss	25.40	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-1000-595-OR	Orange	Gloss	25.40	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-1000-595-PK	Pink	Gloss	25.40	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-1000-595-PL	Purple	Gloss	25.40	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-1000-595-RD	Red	Gloss	25.40	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-1000-595-SB	Sky Blue	Gloss	25.40	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-1000-595-TN	Tan	Gloss	25.40	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-1000-595-CL	Transparent	Gloss	25.40	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-1000-595-WT	White	Gloss	25.40	15.24 m	1	R6000HF, R6900, R10000
∞	M7C-1000-595-YL	Yellow	Gloss	25.40	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-2000-595-BK	Black	Gloss	50.80	15.24 m	1	R4400, R6700, R6900, R10000
∞	M7C-2000-595-BL	Blue	Gloss	50.80	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-2000-595-BR	Brown	Gloss	50.80	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-2000-595-GD	Gold	Gloss	50.80	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-2000-595-GN	Green	Gloss	50.80	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-2000-595-GY	Grey	Gloss	50.80	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-2000-595-LB	Light Blue	Gloss	50.80	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-2000-595-OC	Ochre	Gloss	50.80	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-2000-595-OR	Orange	Gloss	50.80	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-2000-595-PK	Pink	Gloss	50.80	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-2000-595-PL	Purple	Gloss	50.80	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-2000-595-RD	Red	Gloss	50.80	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-2000-595-SB	Sky Blue	Gloss	50.80	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-2000-595-TN	Tan	Gloss	50.80	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-2000-595-CL	Transparent	Gloss	50.80	15.24 m	1	R4400, R6000HF, R6900, R10000
∞	M7C-2000-595-WT	White	Gloss	50.80	15.24 m	1	R6000HF, R6900, R10000
∞	M7C-2000-595-YL	Yellow	Gloss	50.80	15.24 m	1	R4400, R6000HF, R6900, R10000

**Average expected outdoor life of product will depend on user definition of failure, climatic conditions, mounting techniques and material colour. The up to 8 to 10 year outdoor durability applies to the vinyl label stock only; ribbon durability will vary. A polyester overlaminate is recommended for harsh environments - long term exposure to wind and rain.


Safety signage

Cold temperature application material

- Special adhesive permanently adheres to extremely cold surfaces
- Ideal for cold storage warehouses, fridges, freezers and short-term outdoor use in winter
- Service temp: -40 °C to 100 °C
- Application temp: -23 °C to 100 °C



Diagram	Order Reference	Colour	Finish	Label Width A (mm)	Label Length B (m)	Printer Ribbon Series
B-549: Polyester						
∞	M7C-1000-549-WT	White	Gloss	25.40	15.24 m	R6000HF, R10000
∞	M7C-1000-549-YL	Yellow	Gloss	25.40	15.24 m	R6000HF, R10000
∞	M7C-2000-549-WT	White	Gloss	50.80	15.24 m	R6000HF, R10000
∞	M7C-2000-549-YL	Yellow	Gloss	50.80	15.24 m	R6000HF, R10000




High performance polyester tape

- Recommended for low-halide labeling onto stainless steel pipes and surfaces in harsh environments.
- Applies best to very smooth surfaces and ideal for mounting to rigid panels.



Diagram	Order Reference	Colour	Finish	Label Width A (mm)	Label Length B (m)	Labels per Roll	Printer Ribbon Series
B-569: Polyester							
∞	M7C-1000-569-BL	Blue	Gloss	25.40	15.24 m	1	R6000HF, R10000
∞	M7C-1000-569-GN	Green	Gloss	25.40	15.24 m	1	R6000HF, R10000
∞	M7C-1000-569-RD	Red	Gloss	25.40	15.24 m	1	R6000HF, R10000
∞	M7C-1000-569-WT	White	Gloss	25.40	15.24 m	1	R6000HF, R10000
∞	M7C-1000-569-YL	Yellow	Gloss	25.40	15.24 m	1	R6000HF, R10000
∞	M7C-2000-569-BL	Blue	Gloss	50.80	15.24 m	1	R6000HF, R10000
∞	M7C-2000-569-GN	Green	Gloss	50.80	15.24 m	1	R6000HF, R10000
∞	M7C-2000-569-RD	Red	Gloss	50.80	15.24 m	1	R6000HF, R10000
∞	M7C-2000-569-WT	White	Gloss	50.80	15.24 m	1	R6000HF, R10000
∞	M7C-2000-569-YL	Yellow	Gloss	50.80	15.24 m	1	R6000HF, R10000




Food processing equipment marking

ToughWash series labels

- Durable label construction resists harsh washdown environments and has been tested at washdown temperatures up to 80°C (175° F) and pressures up to 1500 PSI.
- B-854 is a metal detectable version, capable of being detected by commercially available metal detectors.



Diagram	Order Reference	Colour	Finish	Label Width A (mm)	Label Length B (m)	Printer Ribbon Series
B-854: Metal Detectable Polyester						
∞	BM7C-1000-854-WT	White	Matt	25.40	22.86 m	R6000HF
∞	BM7C-1000-854-YL	Yellow	Matt	25.40	22.86 m	R6000HF
∞	BM7C-2000-854-WT	White	Matt	50.80	22.86 m	R6000HF
∞	BM7C-2000-854-YL	Yellow	Matt	50.80	22.86 m	R6000HF
B-855: Polyester						
∞	BM7C-1000-855-WT	White	Matt	25.40	22.86 m	R6000HF
∞	BM7C-1000-855-YL	Yellow	Matt	25.40	22.86 m	R6000HF
∞	BM7C-2000-855-WT	White	Matt	50.80	22.86 m	R6000HF
∞	BM7C-2000-855-YL	Yellow	Matt	50.80	22.86 m	R6000HF




Exit & directional signs

Photoluminescent polyester tapes

Glow-in-the-dark material. Ideal for exit and directional signs, identification of fire alarms and extinguishers, low location egress pathway markings, and directional systems for escape or evacuation routes.



Diagram	Order Reference	Colour	Finish	Label Width A (mm)	Label Length B (m)	Printer Ribbon Series
B-526: Phosphorescent Polyester						
∞	BM7C-1000-526	White	Gloss	25.40	22.86 m	R6000HF, R10000
∞	BM7C-2000-526	White	Gloss	50.80	22.86 m	R6000HF, R10000
B-582: Phosphorescent Polyester						
⊙	BM7C-1000-582	Photoluminescent Green	Gloss	25.40	22.86 m	R4400, R6000HF, R6900
⊙	BM7C-2000-582	Photoluminescent Green	Gloss	50.80	22.86 m	R4400, R6000HF, R6900




Order references beginning with "B" indicate bulk rolls.

▶ See pages 49 - 51 for a detailed material index.

Safety & facility identification

Maintenance



Pre-printed maintenance labels

- M710 printable maintenance labels with pre-printed text allow customers to print variable information next to relevant pre-printed titles.

Order Reference	Legend	Colour	Finish	Label Width A (mm)	Label Height B (mm)	Repeat (mm)	Labels per Roll	Printer Ribbon Series
B-428: Metallised Polyester								
M7-30-428-CALI	CALIBRATION	Green on Grey	Matt	38.10	19.05	22.23	250	R4300, R6200
B-423: Polyester								
M7-30-423-TEST	TESTED	Green on White	Gloss	38.10	19.05	22.23	250	R6000HF, R6200, R6900


Area and pathway marking




ToughStripe area marking tape

- Create custom-printed floor labels, with easy 3-step process: print label, position on floor, apply overlaminates.
- Each kit includes 1 roll of B-483 tape and 1 roll of B-634 overlaminates.

Diagram	Order Reference	Colour	Finish	Label Width A (mm)	Label Length B (m)	Printer Ribbon Series
B-483A/B-634: Polyester with Polyester Overlaminates						
⊙	M7-1000-483-BK-KT	Black	Gloss	25.40	15.24 m	R4400
⊙	M7-1000-483-BL-KT	Blue	Gloss	25.40	15.24 m	R4400, R6000HF
⊙	M7-1000-483-GN-KT	Green	Gloss	25.40	15.24 m	R4400, R6000HF
⊙	M7-1000-483-OR-KT	Orange	Gloss	25.40	15.24 m	R4400, R6000HF
⊙	M7-1000-483-RD-KT	Red	Gloss	25.40	15.24 m	R4400, R6000HF
⊙	M7-1000-483-WT-KT	White	Gloss	25.40	15.24 m	R6000HF, R6300, R6900
⊙	M7-1000-483-YL-KT	Yellow	Gloss	25.40	15.24 m	R4400, R6000HF, R6300
⊙	M7-2000-483-BK-KT	Black	Gloss	50.80	15.24 m	R4400
⊙	M7-2000-483-BL-KT	Blue	Gloss	50.80	15.24 m	R4400, R6000HF
⊙	M7-2000-483-GN-KT	Green	Gloss	50.80	15.24 m	R4400, R6000HF
⊙	M7-2000-483-OR-KT	Orange	Gloss	50.80	15.24 m	R4400, R6000HF
⊙	M7-2000-483-RD-KT	Red	Gloss	50.80	15.24 m	R4400, R6000HF
⊙	M7-2000-483-WT-KT	White	Gloss	50.80	15.24 m	R6000HF, R6300, R6900
⊙	M7-2000-483-YL-KT	Yellow	Gloss	50.80	15.24 m	R4400, R6000HF, R6300



Safety signs and labels



Pre-printed safety labels

M710 printable safety labels with pre-printed headers allow customers to print variable information next to highly visible titles.

Order Reference	Legend	Colour	Finish	Label Width A (mm)	Label Height B (mm)	Repeat (mm)	Labels per Roll	Printer Ribbon Series
B-483A: Polyester								
M7-38-483-CAUTION	CAUTION	Black, Yellow on White	Gloss	101.60	48.26	104.78	100	R6000HF, R6300, R6900
M7-38-483-DANGER	DANGER	Red on White	Gloss	101.60	48.26	104.78	100	R6000HF, R6300, R6900
M7-38-483-NOTICE	NOTICE	Blue on White	Gloss	101.60	48.26	104.78	100	R6000HF, R6300, R6900
M7-38-483-WARNING	WARNING	Black, Orange on White	Gloss	101.60	48.26	104.78	100	R6000HF, R6300, R6900


Safety signs and labels

Reflective tapes

The reflective quality of this material makes it ideal for reading labels in low light conditions (with flashlights). Brady B-584 can be used for applications such as outdoor pole, cabinet or pedestal identification and indoor long distance scanning of racks and shelves where high visibility is critical.



Diagram	Order Reference	Colour	Finish	Label Width A (mm)	Label Length B (m)	Printer Ribbon Series
B-584: Reflective Tape						
∞	M7C-1000-584-OR	Orange	Gloss	25.40	9.14 m	R10000
∞	M7C-1000-584-WT	White	Gloss	25.40	9.14 m	R10000
∞	M7C-1000-584-YL	Yellow	Gloss	25.40	9.14 m	R10000
∞	M7C-2000-584-OR	Orange	Gloss	50.80	9.14 m	R10000
∞	M7C-2000-584-WT	White	Gloss	50.80	9.14 m	R10000
∞	M7C-2000-584-YL	Yellow	Gloss	50.80	9.14 m	R10000
∞	BMC-1000-584-OR	Orange	Gloss	25.40	22.86 m	R4400, R6000HF, R6900, R10000
∞	BMC-1000-584-WT	White	Gloss	25.40	22.86 m	R4400, R6000HF, R6900, R10000
∞	BMC-1000-584-YL	Yellow	Gloss	25.40	22.86 m	R4400, R6000HF, R6900, R10000
∞	BMC-2000-584-OR	Orange	Gloss	50.80	22.86 m	R4400, R6000HF, R6900, R10000
∞	BMC-2000-584-WT	White	Gloss	50.80	22.86 m	R4400, R6000HF, R6900, R10000
∞	BMC-2000-584-YL	Yellow	Gloss	50.80	22.86 m	R4400, R6000HF, R6900, R10000



Order references with "C" (e.g. M71C) indicate continuous. Order references beginning with "B" indicate bulk rolls.


Lean warehouse labels

Printable magnetic supply

- Non-adhesive magnetic material that can be printed on directly
- Ideal for reusable and repositionable identification applications



Diagram	Order Reference	Colour	Finish	Label Width A (mm)	Label Length B (m)	Printer Ribbon Series
B-509: Magnetic Polyester						
∞	BM7C-1000-509-WT	White	Matt	25.40	7.62	R6000HF, R10000
∞	BM7C-1000-509-YL	Yellow	Matt	25.40	7.62	R6000HF, R10000
∞	BM7C-1800-509-WT	White	Matt	45.72	7.62	R6000HF, R10000
∞	BM7C-1800-509-YL	Yellow	Matt	45.72	7.62	R6000HF, R10000




Paper labels

- Economical choice for light duty general id.
- White finish and mattx topcoat.
- Excellent contrast and smear resistance for barcode printing.



Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
B-424: Paper							
▲	M7-20-424	White	25.40	50.80	53.98	100	R4300, R6900
▲	BM-20-424	White	50.80	25.40	53.98	1000	R4300, R6900




Order references beginning with "B" indicate bulk rolls.

Repositionable vinyl

Best choice for indoor marking where frequent repositioning is required, such as shelves. Special adhesive allows easy removal of label to re-apply again and again.




Diagram	Order Reference	Colour	Finish	Label Width A (mm)	Label Length B (m)	Printer Ribbon Series
B-581: Vinyl						
⊙	M7C-500-581-WT	White	Gloss	12.70	15.24 m	R6000HF, R6900, R10000
⊙	M7C-500-581-YL	Yellow	Gloss	12.70	15.24 m	R6000HF, R6900, R10000
⊙	M7C-1000-581-WT	White	Gloss	25.40	15.24 m	R6000HF, R6900, R10000
⊙	M7C-1000-581-YL	Yellow	Gloss	25.40	15.24 m	R6000HF, R6900, R10000
⊙	M7C-2000-581-WT	White	Gloss	50.80	15.24 m	R6000HF, R6900, R10000
⊙	M7C-2000-581-YL	Yellow	Gloss	50.80	15.24 m	R6000HF, R6900, R10000



▶ See pages 49 - 51 for a detailed material index.

Circuit board marking

Thermal transfer printable products circuit board process chart



	Through Hole Technology		Surface Mount Technology (SMT)	
	Top	Bottom	Top or Bottom	After Process
B-719, B-724, B-767, B-768, B-797	Yes	Yes	Yes	Yes
B-422, B-423, B-430, B-437, B-459, B-473, B-488	Yes*	No	No	Yes

*In extreme high temperature, testing of these materials is recommended



Polyester labels

Various types of high resistant polyester materials for relays, solenoids, PCB's, electronic components and more.




Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
B-422: Polyester							
▲	M7-45-422	White	38.10	9.53	12.70	500	R6000HF, R6900
B-423: Polyester							
▲	M7-1-423	White	6.35	6.35	9.53	750	R6000HF, R6200, R6900
▲	M7-3-423	White	9.53	9.53	12.70	500	R6000HF, R6200, R6900
▲	M7-4-423	White	10.16	10.16	13.34	500	R6000HF, R6200, R6900
▲	M7-7-423	White	12.70	12.70	15.88	500	R6000HF, R6200, R6900
▲	M7-6-423	White	12.70	6.99	10.16	750	R6000HF, R6200, R6900
▲	M7-5-423	White	12.70	5.08	8.26	750	R6000HF, R6200, R6900
▲	M7-9-423	White	16.51	5.08	8.26	750	R6000HF, R6200, R6900
▲	M7-10-423	White	19.05	6.35	9.53	750	R6000HF, R6200, R6900
▲	M7-13-423	White	22.86	6.35	9.53	750	R6000HF, R6200, R6900
▲	M7-16-423	White	25.40	9.53	12.70	500	R6000HF, R6200, R6900
▲	M7-15-423	White	25.40	6.99	10.16	750	R6000HF, R6200, R6900
▲	M7-14-423	White	25.40	4.75	8.26	750	R6000HF, R6200, R6900
▲	BM-16-423	White	25.40	9.53	12.70	5000	R4400, R6000HF, R6200
▲	M7-25-423	White	31.75	6.35	9.53	750	R6000HF, R6200, R6900
▲	M7-28-423	White	38.10	6.35	9.53	750	R6000HF, R6200, R6900
▲	M7-27-423	White	38.10	3.18	6.35	750	R6000HF, R6200, R6900
B-430: Polyester							
▲	M7-71-430	Transparent	8.89	5.08	9.53	750	R4400, R6000HF, R6200, R6900
▲	M7-16-430	Transparent	25.40	9.53	12.70	500	R4400, R6000HF, R6200, R6900
▲	M7-45-430	Transparent	38.10	9.53	12.70	500	R4400, R6000HF, R6200, R6900
B-459: Polyester							
▲	M7-20-459	White	25.40	50.80	53.98	100	R6000HF, R6900
▲	M7-30-459	White	38.10	19.05	22.23	250	R6000HF, R6900
▲	M7-29-459	White	38.10	12.70	15.88	500	R6000HF, R6900

Order references beginning with "B" indicate bulk rolls.

>>

Circuit board marking

Polyester labels (continued)




Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
B-473: Static Dissipative Polyester							
▲	M7-6-473	White	12.70	6.99	10.16	750	R6000HF
▲	M7-9-473	White	16.51	5.08	8.26	750	R6000HF
▲	M7-10-473	White	19.05	6.35	9.53	750	R6000HF
▲	M7-17-473	White	25.40	12.70	15.88	500	R6000HF
▲	M7-16-473	White	25.40	9.53	12.70	500	R6000HF
◐	M7-28-473	White	38.10	6.35	9.53	750	R6000HF
B-488: Polyester							
▲	M7-81-488	White	48.26	6.35	9.53	750	R4300, R6200

Polyimide labels

Various types of high resistant polyimide materials for relays, solenoids, PCB's and electronic components.




Diagram	Order Reference	Colour	Label Width A (mm)	Label Height B (mm)	Vertical Repeat D (mm)	Labels per Roll	Printer Ribbon Series
B-724: Polyimide							
▲	M7-9-724	Amber	16.51	5.08	8.26	750	R4300
▲	M7-13-724	Amber	22.86	6.35	9.53	750	R4300
▲	M7-17-724	Amber	25.40	12.70	15.88	500	R4300
▲	M7-16-724	Amber	25.40	9.53	12.70	500	R4300
▲	M7-28-724	Amber	38.10	6.35	9.53	750	R4300
B-767: Static Dissipative Polyimide							
▲	M7-2-767	White	50.80	6.35	53.98	100	R6000HF, R6300
B-768: Static Dissipative Polyimide							
▲	M7-4-768	White	10.16	10.16	13.34	500	R6000HF, R6300
▲	M7-9-768	White	16.51	5.08	8.26	750	R6000HF, R6300
▲	M7-25-768	White	31.75	6.35	9.53	750	R6000HF, R6300
B-797: Polyimide							
▲	M7-10-797	White	6.35	19.05	9.53	750	R6000HF, R6300
▲	M7-16-797	White	25.40	9.53	12.70	500	R6000HF, R6300


▶ See pages 49 - 51 for a detailed material index.

Specimen tracking identification



Straw & rod labelling

Brady offers a range of labels designed to fit the small surface area of straws and rods and will withstand long-term storage.



Labels are shown per vial / tube size and in order of label width.

The background colours in the Order Reference column represent the material colour.

Diagram	Material	Special Properties	Label Width A (mm)	Label Height B (mm)	Printable Area Width PW (mm)	Printable Area Height PH (mm)	Order Reference	Printer Ribbon Series	Labels per Roll
0.25 mL Straw									
▶	B-427	F N S	25.40	25.40	25.40	9.53	BM-19-427	R4300	2500
▶	B-427	F N S	25.40	25.40	25.40	9.53	M7-19-427	R4300, R6900	250
▶	B-427	F N S	25.40	25.40	25.40	9.53	M7-19-427-YL	R4300, R6700, R6900	250
0.5 mL									
▶	B-427	F N S	25.40	63.50	25.40	19.05	BM-21-427	R4300	1000
▶	B-427	F N S	25.40	63.50	25.40	19.05	M7-21-427	R4300, R6900	100
▶	B-427	F N S	25.40	63.50	25.40	19.05	M7-21-427-YL	R4300, R6700, R6900	100
1.5 mL									
▶	B-461	F N A H S L	25.40	25.40	25.40	9.53	M7-19-461	R4300, R6200, R6900	250
2.0 mL									
▲	B-492	F N H L	25.40	25.40	-	-	M7-19-492	R4300, R6400	250

Order references beginning with "B" indicate bulk rolls.



Vial tops

Save time by using the Vial and Vial top combination labels - print your information in one go.




Diagram	Material	Special Properties	Label Width A (mm)	Label Height B (mm)	Diameter C (mm)	Printable Area Width PW (mm)	Printable Area Height PH (mm)	Order Reference	Printer Ribbon Series	Labels per Roll
0.5 mL										
⊠	B-499	F A	22.86	12.70	12.70	-	-	M7-126-499	R4300, R6000HF, R6200, R6900	500
⊠	B-492	F F L	25.40	12.70	9.53	-	-	M7-118-492	R4300, R6400	500
1.5 mL										
⊠	B-499	F A	-	-	9.53	-	-	M7-82-499	R4300, R6000HF, R6200, R6900	500
2.0 mL										
⊠	B-499	F A	-	-	12.70	-	-	M7-83-499	R4300, R6000HF, R6200, R6900	500
◇	B-461	F A H S L	40.00	15.00	9.53	29.97	15.00	M7-101-461	R4300, R6200, R6900	250
4.0 mL										
◇	B-461	F A H S L	15.24	41.28	12.70	15.24	30.00	M7-116-461	R4300, R6200, R6900	150


F Freezer environment N Liquid nitrogen environment A Autoclave environment H Hot water bath (100°C) S Self-laminating label L Low-profile (extremely thin) label R Removable

▶ See pages 49 - 51 for a detailed material index.

Specimen tracking identification

Vial / tube labels

Brady's vial and test tube labels are designed to withstand extreme laboratory solvents like Xylene, Ethanol, Alcohol and DMSO, ensuring that the specimen identification is always legible - and will not smear, fade or fall off.



Labels are shown per vial / tube size and in order of label width.

The background colours in the Order Reference column represent the material colour.

Diagram	Material	Special Properties	Label Width A (mm)	Label Height B (mm)	Label Length B (mm)	Diameter C (mm)	Printable Area Width PW (mm)	Printable Area Height PH (mm)	Order Reference	Printer Ribbon Series	Labels per Roll
0.5 mL											
▷	B-461	F N A H S L	9.53	45.72	-	-	9.53	19.05	M7-73-461	R4300, R6200, R6900	250
▲	B-498	F R	19.05	12.70	-	-	-	-	BM-11-498	R4300, R6200, R6600	5000
✘	B-499	F A	22.86	12.70	-	12.70	-	-	M7-126-499	R4300, R6000HF, R6200, R6900	500
▲	B-492	F N H L	25.40	9.53	-	-	-	-	M7-16-492	R4300, R6400	500
▲	B-498	F R	25.40	9.53	-	-	-	-	M7-16-498	R4300, R6000HF, R6200, R6900	500
✘	B-499	F A	25.40	9.53	-	9.53	-	-	M7-98-499	R4300, R6000HF, R6200, R6900	500
✘	B-492	F H L	25.40	12.70	-	9.53	-	-	M7-118-492	R4300, R6400	500
1.5 mL											
✘	B-499	F A	-	-	-	9.53	-	-	M7-82-499	R4300, R6000HF, R6200, R6900	500
▷	B-461	F N A H S L	15.24	41.28	-	-	15.24	25.40	M7-76-461	R4300, R6200, R6900	500
2.0 mL											
✘	B-499	F A	-	-	-	12.70	-	-	M7-83-499	R4300, R6000HF, R6200, R6900	500
▷	B-461	F N A H S L	15.24	38.10	-	-	15.24	33.00	M7-100-461	R4300, R6200, R6900	500
▷	B-461	F N A H S L	25.40	44.45	-	-	25.40	25.40	M7-106-461	R4300, R6200, R6900	250
▷	B-461	F N A H S L	25.40	66.68	-	-	25.40	25.40	M7-115-461	R4300, R6200, R6900	100
◆	B-461	F A H S L	40.00	15.00	-	9.53	29.97	15.00	M7-101-461	R4300, R6200, R6900	250
4.0 mL											
◇	B-461	F A H S L	15.24	41.28	-	12.70	15.24	30.00	M7-116-461	R4300, R6200, R6900	150
▷	B-461	F N A H S L	15.24	48.26	-	-	15.24	40.00	M7-119-461	R4300, R6200, R6900	500
▲	B-490	F N H L	41.28	15.24	-	-	-	-	M7-76-490	R4300	500
8.0 mL											
▷	B-461	F N A H S L	15.24	66.68	-	-	15.24	25.40	M7-86-461	R4300, R6200, R6900	100
▲	B-492	F N H L	48.26	25.40	-	-	-	-	M7-78-492	R4300, R6400	250
25.0 mL											
▲	B-498	F R	12.70	38.10	-	-	-	-	BM-29-498	R4300, R6200, R6600	5000
▲	B-498	F R	38.10	12.70	-	-	-	-	M7-29-498	R4300, R6000HF, R6200, R6900	500
50.0 mL											
▷	B-427	F N S	19.05	38.10	-	-	19.05	12.70	BM-30-427	R4300	2500
▲	B-498	F R	25.40	12.70	-	-	-	-	M7-17-498	R4300, R6000HF, R6200, R6900	500
▲	B-427	F N S	38.10	19.05	-	-	-	-	M7-30-427-AW	R4300, R6900	250
▲	B-498	F R	38.10	25.40	-	-	-	-	M7-31-498	R4300, R6000HF, R6200, R6900	250

Order references beginning with "B" indicate bulk rolls. *AW = All White / no transparent area.

F Freezer environment N Liquid nitrogen environment A Autoclave environment H Hot water bath (100°C) S Self-laminating label L Low-profile (extremely thin) label R Removable


Laboratory identification

Specimen tracking identification



Conical & large tube labelling

Brady offers several sample identification labels which are perfect to identify conicals. They are easy to handle, have great flexibility and easily wrap around curved sample containers. Your sample identification label will remain attached and legible, even when the sample is stored in a freezer, in liquid nitrogen or heated in an autoclave.



Labels are shown per vial / tube size and in order of label width.

The background colours in the Order Reference column represent the material colour.

Diagram	Material	Special Properties	Label Width A (mm)	Label Height B (mm)	Label Length B (m)	Printable Area Width PW (mm)	Printable Area Height PH (mm)	Order Reference	Printer Ribbon Series	Labels per Roll
0.5 mL										
▲	B-423	F A H	12.70	12.70	-	-	-	BM-7-423	R4400, R6000HF, R6200	5000
▲	B-423	F A H	12.70	12.70	-	-	-	M7-7-423	R6000HF, R6200, R6900	500
▲	B-492	F N H L	25.40	12.70	-	-	-	M7-17-492	R4300, R6400	500
▲	B-423	F A H	25.40	12.70	-	-	-	M7-17-423	R6000HF, R6200, R6900	500
1.5 mL										
⊙	B-430	F A H	12.70	-	15.24	-	-	M7C-500-430	R4400, R6000HF, R6200, R6900	1
▲	B-423	F A H	25.40	4.75	-	-	-	M7-14-423	R6000HF, R6200, R6900	750
▲	B-423	F A H	25.40	6.99	-	-	-	M7-15-423	R6000HF, R6200, R6900	750
4.0 mL										
▲	B-499	F N A	12.70	38.10	-	-	-	M7-29-499	R4300, R6000HF, R6200, R6900	500
▲	B-499	F N A	38.10	19.05	-	-	-	M7-30-499	R4300, R6000HF, R6200, R6900	250
▲	B-499	F N A	38.10	25.40	-	-	-	M7-31-499	R4300, R6000HF, R6200, R6900	250
▲	B-423	F A H	38.10	25.40	-	-	-	M7-31-423	R6000HF, R6200, R6900	250
8.0 mL										
▲	B-423	F A H	25.40	50.80	-	-	-	BM-20-423	R4400, R6000HF, R6200	1000
▲	B-499	F N A	48.26	25.40	-	-	-	M7-78-499	R4300, R6000HF, R6200, R6900	250
15.0 mL										
▲	B-423	F A H	25.40	50.80	-	-	-	M7-20-423	R6000HF, R6200, R6900	100
▲	B-423	F A H	76.20	25.40	-	-	-	M7-22-423	R6000HF, R6200, R6900	100
25.0 mL										
▲	B-498	F R	12.70	38.10	-	-	-	BM-29-498	R4300, R6200, R6600	5000
▲	B-498	F R	38.10	12.70	-	-	-	M7-29-498	R4300, R6000HF, R6200, R6900	500
50.0 mL										
▶	B-427	F N S	19.05	38.10	-	19.05	12.70	BM-30-427	R4300	2500
▲	B-498	F R	25.40	12.70	-	-	-	M7-17-498	R4300, R6000HF, R6200, R6900	500
▲	B-427	F N S	38.10	19.05	-	-	-	M7-30-427-AW	R4300, R6900	250
▲	B-498	F R	38.10	25.40	-	-	-	M7-31-498	R4300, R6000HF, R6200, R6900	250

Order references beginning with "B" indicate bulk rolls. *AW = All White / no transparent area.


F Freezer environment N Liquid nitrogen environment A Autoclave environment H Hot water bath (100°C) S Self-laminating label L Low-profile (extremely thin) label R Removable

▶ See pages 49 - 51 for a detailed material index.

Specimen process marking

Centrifuge / microcentrifuge labels

- Brady offers a wide range of Centrifuge, Eppendorf and PCR Labels.
- When applying a self-laminating label, we recommend you avoid touching the adhesive side of the label when wrapping it around a vial or tube, to ensure maximum adhesion.



The background colours in the Order Reference column represent the material colour.

Labels are shown per vial / tube size and in order of label width.

Diagram	Material	Special Properties	Label Width A (mm)	Label Height B (mm)	Diameter C (mm)	Printable Area Width PW (mm)	Printable Area Height PH (mm)	Order Reference	Printer Ribbon Series	Labels per Roll
0.5 mL										
▷	B-461	F N A H S L	9.53	45.72	-	9.53	19.05	M7-73-461	R4300, R6200, R6900	250
▲	B-499	F N A	12.70	19.05	-	-	-	M7-11-499	R4300, R6000HF, R6200, R6900	500
▲	B-498	F	12.70	19.05	-	-	-	M7-11-498	R4300, R6000HF, R6200, R6900	500
▲	B-498	F	19.05	12.70	-	-	-	BM-11-498	R4300, R6200, R6600	5000
▲	B-499	F N A	22.86	12.70	-	-	-	M7-84-499	R4300, R6000HF, R6200, R6900	500
▲	B-499	F N A	25.40	9.53	-	-	-	M7-16-499	R4300, R6000HF, R6200, R6900	500
▲	B-498	F	25.40	9.53	-	-	-	M7-16-498	R4300, R6000HF, R6200, R6900	500
✱	B-499	F A	25.40	9.53	9.53	-	-	M7-98-499	R4300, R6000HF, R6200, R6900	500
1.5 mL										
▷	B-461	F N A H S L	15.24	41.28	-	15.24	25.40	M7-76-461	R4300, R6200, R6900	500
2.0 mL										
▷	B-461	F N A H S L	15.24	38.10	-	15.24	33.00	M7-100-461	R4300, R6200, R6900	500
▷	B-461	F N A H S L	25.40	44.45	-	25.40	25.40	M7-106-461	R4300, R6200, R6900	250
▷	B-461	F N A H S L	25.40	66.68	-	25.40	25.40	M7-115-461	R4300, R6200, R6900	100
◆	B-461	F A H S L	40.00	15.00	9.53	29.97	15.00	M7-101-461	R4300, R6200, R6900	250
4.0 mL										
◇	B-461	F A H S L	15.24	41.28	12.70	15.24	30.00	M7-116-461	R4300, R6200, R6900	150
▷	B-461	F N A H S L	15.24	48.26	-	15.24	40.00	M7-119-461	R4300, R6200, R6900	500
▲	B-490	F N H L	41.28	15.24	-	-	-	M7-76-490	R4300	500
▷	B-461	F N A H S L	66.68	25.40	-	25.40	25.40	BM-75-461	R4300, R6200	1000
8.0 mL										
▷	B-461	F N A H S L	15.24	66.68	-	15.24	25.40	M7-86-461	R4300, R6200, R6900	100
50.0 mL										
▷	B-427	F N S	19.05	38.10	-	19.05	12.70	BM-30-427	R4300	2500
▲	B-427	F N S	38.10	19.05	-	-	-	M7-30-427-AW	R4300, R6900	250

Order references beginning with "B" indicate bulk rolls. *AW = All White / no transparent area.

Slide labels

Brady offers labels specifically designed to identify slides and to resist exposure to harsh chemicals during the slide staining process. They perform well in the hematoxylin and eosin slide staining process and offer superior chemical resistance also useful in other laboratory contexts.




Diagram	Material	Special Properties	Label Width A (mm)	Label Height B (mm)	Order Reference	Printer Ribbon Series	Labels per Roll
▲	B-488	F A	19.05	22.86	M7-80-488	R4300, R6200	250
▲	B-488	F A	22.86	22.86	M7-97-488	R4300, R6200	250
▲	B-481	F H	22.86	22.86	M7-97-481	R6400	250


Laboratory identification

Specimen storage identification

Cryo tubes & vials



- Brady offers a range of labels designed specifically to identify laboratory samples for cryo storage.
- These labels can be applied to room temperature or to already frozen samples, albeit with a small overlap.
- The label will remain legible and will stick to the sample container during processing, even when exposed to extreme heat or chemicals like DMSO, Xylene and Ethanol, ensuring secure sample identification in the most challenging laboratory conditions.



Labels are shown per vial / tube size and in order of label width.

Diagram	Material	Special Properties	Label Width A (mm)	Label Height B (mm)	Diameter C (mm)	Printable Area Width PW (mm)	Printable Area Height PH (mm)	Order Reference	Printer Ribbon Series	Labels per Roll
0.5 mL										
▲	B-499	F N A	12.70	19.05	-	-	-	M7-11-499	R4300, R6000HF, R6200, R6900	500
▲	B-499	F N A	22.86	12.70	-	-	-	M7-84-499	R4300, R6000HF, R6200, R6900	500
▲	B-492	F N H L	25.40	9.53	-	-	-	M7-16-492	R4300, R6400	500
⊗	B-499	F A	25.40	9.53	9.53	-	-	M7-98-499	R4300, R6000HF, R6200, R6900	500
▲	B-492	F N H L	25.40	12.70	-	-	-	M7-17-492	R4300, R6400	500
⊗	B-492	F H L	25.40	12.70	9.53	-	-	M7-118-492	R4300, R6400	500
2.0 mL										
▲	B-492	F N H L	25.40	25.40	-	-	-	M7-19-492	R4300, R6400	250
4.0 mL										
▲	B-499	F N A	12.70	38.10	-	-	-	M7-29-499	R4300, R6000HF, R6200, R6900	500
▲	B-490	F N H L	41.28	15.24	-	-	-	M7-76-490	R4300	500
▾	B-461	F N A H S L	66.68	25.40	-	25.40	25.40	BM-75-461	R4300, R6200	1000
8.0 mL										
▲	B-492	F N H L	48.26	25.40	-	-	-	M7-78-492	R4300, R6400	250
25.0 mL										
▲	B-498	F	R 12.70	38.10	-	-	-	BM-29-498	R4300, R6200, R6600	5000
▲	B-498	F	R 38.10	12.70	-	-	-	M7-29-498	R4300, R6000HF, R6200, R6900	500


Order references beginning with "B" indicate bulk rolls.



Tissue cassette labels

- Tissue cassettes are often re-identified when labs collect samples from various biorepositories. Typically, each laboratory has its own unique way of identifying samples, which creates a need to re-identify samples in a common way.
- Brady B-498 post-process labels offer customers the optimal way to organise these specimens and conduct further studies. These labels can be applied directly onto the cassettes, on pure paraffin wax and on top of another label or identifier.

Diagram	Material	Special Properties	Label Width A (mm)	Label Height B (mm)	Order Reference	Printer Ribbon Series	Labels per Roll
∞	B-498	F	6.10	-	M7C-240-498	R4300, R6000HF, R6200, R6900	1
▲	B-498	F R	6.35	19.05	M7-10-498	R4300, R6000HF, R6200, R6900	750
∞	B-498	F	8.08	-	M7C-318-498	R4300, R6000HF, R6200, R6900	1
∞	B-498	F	9.53	-	M7C-375-498	R4300, R6000HF, R6200, R6900	1
∞	B-498	F R	12.70	-	M7C-500-498	R4300, R6000HF, R6200, R6900	1
▲	B-498	F R	12.70	12.70	M7-7-498	R4300, R6000HF, R6200, R6900	500
▲	B-498	F R	12.70	19.05	M7-11-498	R4300, R6000HF, R6200, R6900	500
▲	B-498	F R	19.05	12.70	BM-11-498	R4300, R6200, R6600	5000
▲	B-498	F R	19.05	25.40	BM-18-498	R4300, R6200, R6600	2500
▲	B-498	F R	19.05	25.40	M7-18-498	R4300, R6000HF, R6200, R6900	250
▲	B-498	F R	25.40	12.70	M7-17-498	R4300, R6000HF, R6200, R6900	500




Order references beginning with "B" indicate bulk rolls.

F Freezer environment N Liquid nitrogen environment A Autoclave environment H Hot water bath (100°C) S Self-laminating label L Low-profile (extremely thin) label R Removable

Specimen storage identification

Well plate labels

When total tracking of all sample collections is required then Brady has a solution for Well plate identification. Our well plate labels guarantee crystal clear text and barcoding for most lab environments.



Labels are shown in order of label width.

The background colours in the Order Reference column represent the material colour.





Diagram	Material	Special Properties	Label Width A (mm)	Label Height B (mm)	Label Length B (m)	Order Reference	Printer Ribbon Series	Labels per Roll
∞	B-498	F	6.10	-	9.14	M7C-240-498	R4300, R6000HF, R6200, R6900	1
∞	B-498	F	6.10	-	83.82	BM7C-240-498	R4300, R6000HF, R6200, R6900	1
∞	B-595	F	6.35	-	15.24	M7C-250-595-WT	R6000HF, R6900, R10000	1
∞	B-595	F	6.35	-	15.24	M7C-250-595-YL	R4400, R6000HF, R6900, R10000	1
▲	B-498	F R	6.35	19.05	-	M7-10-498	R4300, R6000HF, R6200, R6900	750
∞	B-498	F	8.08	-	9.14	M7C-318-498	R4300, R6000HF, R6200, R6900	1
∞	B-498	F	9.53	-	9.14	M7C-375-498	R4300, R6000HF, R6200, R6900	1
∞	B-498	F	9.53	-	83.82	BMC-375-498	R4300, R6000HF, R6200, R6900	1
∞	B-498	F R	12.70	-	9.14	M7C-500-498	R4300, R6000HF, R6200, R6900	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-BK	R4400, R6700, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-BL	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-BR	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-CL	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-GD	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-GN	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-GY	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-LB	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-OC	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-OR	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-PK	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-PL	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-RD	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-SB	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-TN	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-WT	R6000HF, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-YL	R4400, R6000HF, R6900, R10000	1
⊙	B-430	F A H	12.70	-	15.24	M7C-500-430	R4400, R6000HF, R6200, R6900	1
▲	B-423	F A H	12.70	12.70	-	BM-7-423	R6000HF, R6200, R6900	5000
▲	B-499	F N A	12.70	12.70	-	M7-7-499	R4300, R6000HF, R6200, R6900	500
▲	B-498	F R	12.70	12.70	-	M7-7-498	R4300, R6000HF, R6200, R6900	500
▲	B-423	F A H	12.70	12.70	-	M7-7-423	R6000HF, R6200, R6900	500
▲	B-498	F R	12.70	38.10	-	BM-29-498	R4300, R6000HF, R6200, R6900	5000
▲	B-499	F N A	12.70	38.10	-	M7-29-499	R4300, R6000HF, R6200, R6900	500
▲	B-499	F N A	15.00	9.00	-	M7-67-499-YL	R4300, R6000HF, R6200, R6900	750
▲	B-499	F N A	16.00	5.00	-	M7-41-499-YL	R4300, R6000HF, R6200, R6900	750
▲	B-499	F N A	19.05	12.70	-	BM-11-499	R4300, R6000HF, R6200, R6900	5000
▲	B-498	F R	19.05	25.40	-	BM-18-498	R4300, R6000HF, R6200, R6900	2500
▲	B-499	F N A	19.05	25.40	-	M7-18-499	R4300, R6000HF, R6200, R6900	250
▲	B-498	F R	19.05	25.40	-	M7-18-498	R4300, R6000HF, R6200, R6900	250
⊙	B-499	F N A	25.40	-	9.14	M7C-1000-499	R4300, R6000HF, R6200, R6900	1
⊙	B-498	F	25.40	-	9.14	M7C-1000-498	R4300, R6000HF, R6200, R6900	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-BK	R4400, R6700, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-BL	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-BR	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-CL	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-GD	R4400, R6000HF, R6900, R10000	1

Order references beginning with "B" indicate bulk rolls.


>>

Laboratory identification

Specimen storage identification



Well plate labels (Continued)



Labels are shown in order of label width.

The background colours in the Order Reference column represent the material colour.

Diagram	Material	Special Properties	Label Width A (mm)	Label Height B (mm)	Label Length B (m)	Order Reference	Printer Ribbon Series	Labels per Roll
∞	B-595	F	25.40	-	15.24	M7C-1000-595-GN	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-GY	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-LB	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-OC	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-OR	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-PK	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-PL	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-RD	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-SB	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-TN	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-WT	R6000HF, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-YL	R4400, R6000HF, R6900, R10000	1
▲	B-423	F A H	25.40	4.75	-	M7-14-423	R6000HF, R6200, R6900	750
▲	B-423	F A H	25.40	6.99	-	M7-15-423	R6000HF, R6200, R6900	750
▲	B-498	F R	25.40	12.70	-	M7-17-498	R4300, R6000HF, R6200, R6900	500
▲	B-430	F A H	25.40	12.70	-	M7-17-430	R4400, R6000HF, R6200, R6900	500
▲	B-423	F A H	25.40	12.70	-	M7-17-423	R6000HF, R6200, R6900	500
▲	B-498	F	25.40	25.40	-	BM-19-498	R4300, R6000HF, R6200, R6900	2500
▲	B-499	F N A	25.40	25.40	-	M7-19-499	R4300, R6000HF, R6200, R6900	250
▲	B-498	F R	25.40	25.40	-	M7-19-498	R4300, R6000HF, R6200, R6900	250
▲	B-423	F A H	25.40	50.80	-	BM-20-423	R6000HF, R6200, R6900	1000
▲	B-423	F A H	25.40	50.80	-	M7-20-423	R6000HF, R6200, R6900	100
▲	B-499	F N A	38.10	6.35	-	M7-28-499	R4300, R6000HF, R6200, R6900	750
▲	B-498	F R	38.10	12.70	-	M7-29-498	R4300, R6000HF, R6200, R6900	500
▲	B-499	F N A	38.10	19.05	-	M7-30-499	R4300, R6000HF, R6200, R6900	250
▲	B-498	F R	38.10	19.05	-	M7-30-498	R4300, R6000HF, R6200, R6900	250
▲	B-499	F N A	38.10	25.40	-	M7-31-499	R4300, R6000HF, R6200, R6900	250
▲	B-498	F R	38.10	25.40	-	M7-31-498	R4300, R6000HF, R6200, R6900	250
▲	B-423	F A H	38.10	25.40	-	M7-31-423	R6000HF, R6200, R6900	250
▲	B-498	F R	38.10	38.10	-	M7-32-498	R4300, R6000HF, R6200, R6900	250
⊙	B-499	F N A	48.26	-	9.14	M7C-1900-499	R4300, R6000HF, R6200, R6900	1
⊙	B-498	F	48.26	-	9.14	M7C-1900-498	R4300, R6000HF, R6200, R6900	1
▲	B-499	F N A	48.26	6.35	-	M7-81-499	R4300, R6000HF, R6200, R6900	750
▲	B-488	F A	48.26	6.35	-	M7-81-488	R4300, R6200	750
▲	B-499	F N A	48.26	25.40	-	M7-78-499	R4300, R6000HF, R6200, R6900	250
▲	B-423	F A H	50.80	6.35	-	M7-2-423	R6000HF, R6200, R6900	100
▲	B-423	F A H	76.20	25.40	-	M7-22-423	R6000HF, R6200, R6900	100


Order references beginning with "B" indicate bulk rolls.

Bottle tamper seal labels

Brady's bottle seal identification provides tracking information with the added feature of security. These labelling materials are designed to fracture easily in order to show signs of sample tampering and to prevent one-piece label removal.




Diagram	Material	Special Properties	Label Width A (mm)	Label Height B (mm)	Order Reference	Printer Ribbon Series	Labels per Roll
▲	B-351	F	25.40	12.70	M7-17-351	R6000HF, R6200	500
▲	B-351	F	25.40	50.80	M7-20-351	R6000HF, R6200	100
▲	B-351	F	38.10	25.40	M7-31-351	R6000HF, R6200	250
▲	B-351	F	76.20	48.26	M7-37-351	R6000HF, R6200	100



Lean lab identification

Bottles / flasks & dishes

Brady's labels for bottles, flasks and dishes are flexible, which makes them easy to apply to curved containers and remain attached and legible, even after being subjected to freezing, liquid nitrogen and heat.



Labels are shown in order of label width.

The background colours in the Order Reference column represent the material colour.

Diagram	Material	Special Properties	Label Width		Label Length	Diameter	Order Reference	Printer Ribbon Series	Labels per Roll
			A (mm)	B (mm)					
⊙	B-430	F A H	12.70	-	15.24	-	M7C-500-430	R4400, R6000HF, R6200, R6900	1
▲	B-423	F A H	12.70	12.70	-	-	BM-7-423	R4400, R6000HF, R6200	5000
▲	B-423	F A H	12.70	12.70	-	-	M7-7-423	R6000HF, R6200, R6900	500
▲	B-498	F R	12.70	38.10	-	-	BM-29-498	R4300, R6200, R6600	5000
▲	B-499	F N A	12.70	38.10	-	-	M7-29-499	R4300, R6000HF, R6200, R6900	500
▲	B-423	F A H	25.40	4.75	-	-	M7-14-423	R6000HF, R6200, R6900	750
▲	B-423	F A H	25.40	6.99	-	-	M7-15-423	R6000HF, R6200, R6900	750
▲	B-492	F N H L	25.40	9.53	-	-	M7-16-492	R4300, R6400	500
▲	B-498	F R	25.40	12.70	-	-	M7-17-498	R4300, R6000HF, R6200, R6900	500
▲	B-492	F N H L	25.40	12.70	-	-	M7-17-492	R4300, R6400	500
▲	B-430	F A H	25.40	12.70	-	-	M7-17-430	R4400, R6000HF, R6200, R6900	500
▲	B-423	F A H	25.40	12.70	-	-	M7-17-423	R6000HF, R6200, R6900	500
⊕	B-492	F H L	25.40	12.70	-	9.53	M7-118-492	R4300, R6400	500
▲	B-492	F N H L	25.40	25.40	-	-	M7-19-492	R4300, R6400	250
▲	B-423	F A H	25.40	50.80	-	-	BM-20-423	R4400, R6000HF, R6200	1000
▲	B-423	F A H	25.40	50.80	-	-	M7-20-423	R6000HF, R6200, R6900	100
▲	B-498	F R	38.10	12.70	-	-	M7-29-498	R4300, R6000HF, R6200, R6900	500
▲	B-499	F N A	38.10	19.05	-	-	M7-30-499	R4300, R6000HF, R6200, R6900	250
▲	B-427	F N S	38.10	19.05	-	-	M7-30-427-AW	R4300, R6900	250
▲	B-490	F N H L	41.28	15.24	-	-	M7-76-490	R4300	500
▲	B-499	F N A	48.26	25.40	-	-	M7-78-499	R4300, R6000HF, R6200, R6900	250
▲	B-492	F N H L	48.26	25.40	-	-	M7-78-492	R4300, R6400	250
▲	B-423	F A H	76.20	25.40	-	-	M7-22-423	R6000HF, R6200, R6900	100

Order references beginning with "B" indicate bulk rolls. *Order references ending with "AW" indicate all white labels with no clear area.

Laboratory identification

Lean lab identification



General lab equipment labels

With proper identification, time spent looking for the right sample or tool can be invested in what really matters. Brady offers a range of materials suitable for identifying drawers, cabinets, shelves, storage units and laboratory equipment.




Diagram	Material	Special Properties	Label Width A (mm)	Label Height B (mm)	Label Length B (m)	Order Reference	Printer Ribbon Series	Labels per Roll
⊙	B-430	F A H	9.53	-	15.24	M7C-375-430	R4400, R6000HF, R6200, R6900	1
▲	B-423	F A H	9.53	9.53	-	M7-3-423	R6000HF, R6200, R6900	500
▲	B-423	F A H	10.16	10.16	-	M7-4-423	R6000HF, R6200, R6900	500
∞	B-595	F	12.70	-	15.24	M7C-500-595-BK	R4400, R6700, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-BL	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-CL	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-GN	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-OR	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-RD	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-WT	R6000HF, R6900, R10000	1
∞	B-595	F	12.70	-	15.24	M7C-500-595-YL	R4400, R6000HF, R6900, R10000	1
⊙	B-430	F A H	12.70	-	15.24	M7C-500-430	R4400, R6000HF, R6200, R6900	1
⊙	B-423	F A H	12.70	-	15.24	M7C-500-423	R6000HF, R6200, R6900	1
▲	B-423	F A H	12.70	12.70	-	BM-7-423	R4400, R6000HF, R6200	5000
▲	B-423	F A H	12.70	12.70	-	M7-7-423	R6000HF, R6200, R6900	500
∞	B-595	F	25.40	-	15.24	M7C-1000-595-BK	R4400, R6700, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-BL	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-CL	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-GN	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-OR	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-RD	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-WT	R6000HF, R6900, R10000	1
∞	B-595	F	25.40	-	15.24	M7C-1000-595-YL	R4400, R6000HF, R6900, R10000	1
⊙	B-430	F A H	25.40	-	15.24	M7C-1000-430	R4400, R6000HF, R6200, R6900	1
▲	B-423	F A H	25.40	9.53	-	BM-16-423	R4400, R6000HF, R6200	5000
▲	B-430	F A H	25.40	9.53	-	M7-16-430	R4400, R6000HF, R6200, R6900	500
▲	B-423	F A H	25.40	9.53	-	M7-16-423	R6000HF, R6200, R6900	500
▲	B-423	F A H	25.40	12.70	-	BM-17-423	R4400, R6000HF, R6200	5000
▲	B-430	F A H	25.40	12.70	-	M7-17-430	R4400, R6000HF, R6200, R6900	500
▲	B-423	F A H	25.40	12.70	-	M7-17-423	R6000HF, R6200, R6900	500
▲	B-423	F A H	25.40	25.40	-	BM-19-423	R4400, R6000HF, R6200	2500
▲	B-423	F A H	25.40	25.40	-	M7-19-423	R6000HF, R6200, R6900	250
▲	B-423	F A H	25.40	50.80	-	BM-20-423	R4400, R6000HF, R6200	1000
▲	B-424	F	25.40	50.80	-	M7-20-424	R4300, R6900	100
▲	B-423	F A H	25.40	50.80	-	M7-20-423	R6000HF, R6200, R6900	100
▲	B-430	F A H	38.10	9.53	-	M7-45-430	R4400, R6000HF, R6200, R6900	500
▲	B-423	F A H	38.10	12.70	-	BM-29-423	R4400, R6000HF, R6200	5000
▲	B-423	F A H	38.10	12.70	-	M7-29-423	R6000HF, R6200, R6900	500
▲	B-423	F A H	38.10	25.40	-	M7-31-423	R6000HF, R6200, R6900	250
▲	B-423	F A H	38.10	38.10	-	M7-32-423	R6000HF, R6200, R6900	250
∞	B-595	F	50.80	-	15.24	M7C-2000-595-BK	R4400, R6700, R6900, R10000	1
∞	B-595	F	50.80	-	15.24	M7C-2000-595-BL	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	50.80	-	15.24	M7C-2000-595-CL	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	50.80	-	15.24	M7C-2000-595-GN	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	50.80	-	15.24	M7C-2000-595-OR	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	50.80	-	15.24	M7C-2000-595-RD	R4400, R6000HF, R6900, R10000	1
∞	B-595	F	50.80	-	15.24	M7C-2000-595-WT	R6000HF, R6900, R10000	1
∞	B-595	F	50.80	-	15.24	M7C-2000-595-YL	R4400, R6000HF, R6900, R10000	1
⊙	B-430	F A H	50.80	-	15.24	M7C-1900-430	R4400, R6000HF, R6200, R6900	1
▲	B-424	F	50.80	25.40	-	BM-20-424	R4300, R6900	1000

F Freezer environment N Liquid nitrogen environment A Autoclave environment H Hot water bath (100°C) S Self-laminating label L Low-profile (extremely thin) label R Removable

This section provides a quick reference to Brady materials listed throughout this brochure, including applications and regulatory compliance where applicable. For more detailed material attribute and performance information, please refer to the material's Technical Data Sheet, listed at www.bradyeurope.com/tds.

Material	Finish	Colour	Temp (°C) (Tested for 30 days)		Properties & Applications	Approval/Compliance	
			Min.	Max.			
B-109	Polyethylene	Matt	White	-40 °C	49 °C	White polyethylene tag material with matt finish. Excellent multi-purpose tag for identifying multiconductor cables, inventory, safety warning repair and work-in-processing manufacturing. Good weatherability, humidity resistance and legibility after solvent exposure.	–
B-342	Heat-shrink Polyolefin	Matt	White	-55 °C	130.6 °C	3:1 ratio heat shrinkable wire marking sleeve that fits snugly around wires for identification and protection. Fade-resistant and flame retardant. Also available in yellow and black.	UL Recognised to UL224SAE-AMS-DTL-23053/5 C (Class 1)SAE AS-81531
B-348	Polyolefin	Matt	White	-55 °C	105 °C	Brady's B-348 High Performance material complies with the minimal smoke and halogen emission requirements of the most stringent underground standards for high-performance vehicles. The material is printable on-site and in the field, making it a practical solution for identifying thick cables and cable bundles. B-348 has proven to be highly durable, exhibiting excellent UV resistance. Available in white and yellow colours.	EN-45545-2, requirement 24, Vehicle Category HL3
B-351	Tamper-resistant Vinyl	Matt	White	-40 °C	80 °C	White vinyl material with matt finish. Tamper evident material fractures to show signs of product tampering and prevent one-piece removal.	–
B-362	Tamper-resistant Metallised Vinyl	Gloss	Silver	-70 °C	80 °C	Designed to fracture easily in order to show signs of product tampering and to prevent one-piece label removal. Use caution when removing from liner as material is fragile.	–
B-412	Polypropylene	Matt	White	-40 °C	100 °C	White polypropylene tag material with matt finish. Offers high print legibility and high tensile strength.	–
B-414	Polyester	Matt	White	-40 °C	50 °C	Get a grip on your wire and cable identification – Brady and VELCRO® Brand have partnered to bring you BradyGrip™ Print-on Hook Material, an exclusive print-and-place material that can be easily applied, repositioned or removed.	–
B-417	Self-laminating Vinyl	Matt	White, Transparent	-40 °C	70 °C	Keep your wire identification secure with this self-laminating marker with extra-strong adhesive. The extra-strong adhesive makes these markers ideal for small-diameter wires. Features a white printable area and a clear tail that wraps around the marker.	UL Recognised to UL969 Labelling and Marking Standard when printed with the Brady Series R4300 and R7950 ribbons. See UL files MH62024 for specific details. Brady customers should specify at purchase if they require UL Recognised B-417 labels. Brady sells both UL Recognised B-417 labels and non-approved labels depending on customer requirements
B-422	Polyester	Gloss	White	-40 °C	100 °C	Designed to withstand solvent exposure. Used for component identification, barcoding, asset and inventory tracking.	UL RecognisedCSA Accepted
B-423	Polyester	Gloss	White	-70 °C	110 °C	Widely used for component identification, barcoding, asset and inventory tracking.	UL RecognisedCSA AcceptedHalogen Free (DIN VDE 0472/part 815) Approvals are for White material only
B-424	Paper	Matt	White	-40 °C	50 °C	White paper material with matt finish and smooth top coat finish for thermal transfer printing. Good contrast and smear resistance for thermal barcode printing. Used for general purpose labeling applications	–
B-425A	Polypropylene	Matt	White	-70 °C	80 °C	White polypropylene material stock with matt finish for thermal transfer printing or write-on applications. Excellent solvent resistance and print performance; not recommended for long-term outdoor use.	UL RecognisedCSA AcceptedHalogen Free (DIN VDE 0472/part 815)
B-427	Self-laminating Vinyl	Matt	White, Transparent	-40 °C	60 °C	Thermal transfer printable, self-laminating material. These labels have a printable area with a clear "tail" that wraps around the marker. The "tail" serves as overlaminates to protect the print. Superior resistance to abrasion, solvents, water, oil and dirt. Also available in grey, brown, green, yellow, blue, red, purple, orange.	UL Recognised to UL969 Labelling and Marking Standard when printed with the Brady Series R4300 and R6200 ribbons. See UL files MH17154 for specific details. Brady customers should specify at purchase if they require UL Recognised B-427 labels. Brady sells both UL Recognised B-427 labels and non-approved labels depending on customer requirements.
B-428	Metallised Polyester	Matt	Light Grey	-70 °C	120 °C	Thermal transfer printable metallised polyester with matt finish. Withstands solvents and variable temperatures. Excellent for serial and rating plate applications with name-plate quality and a metal-looking finish.	UL RecognisedCSA AcceptedAGA ApprovedHalogen Free (DIN VDE 0472/part 815)
B-430	Polyester	Gloss	Transparent	-70 °C	100 °C	Translucent, high performance polyester material with a glossy finish. Thermal transfer printable.	UL RecognisedCSA Accepted
B-437	Polyvinylfluoride	Matt	White	-70 °C	135 °C	Polyvinylfluoride label material with matt finish. Used in wire and cable identification applications where self-extinguishing features are required. This label material utilises an adhesive for heavy-duty applications and is available in continuous or die-cut formats. Excellent resistance to water, oil and other common fluids. Also available in yellow.	MIL-M-87958 Pressure Sensitive Adhesive Wire or Cable Marker and Identification specification

Master material index

Material	Finish	Colour	Temp (°C) (Tested for 30 days)		Properties & Applications	Approval/Compliance	
			Min.	Max.			
B-459	Polyester	Matt	White	-40 °C	100 °C	White polyester thermal transfer printable material with matt finish. Designed for applications such as topside of printed circuit boards and rating plates that utilise high quality/ density alphanumerics, barcodes and graphics.	UL Recognised
B-461	Self-laminating Polyester	Matt	White, Transparent	-196 °C	110 °C	Permanent adhesive; suitable for liquid nitrogen application if material is wrapped around itself, as in self-lamination; write-on capabilities. Temperature range increases to 121 °C when used in autoclave process	–
B-472	Polyimide	Matt	White	-70 °C	100 °C	Cable and wire bundle applications and label applications where self-extinguishing properties are required	–
B-473	Static Dissipative Polyester	Gloss	White	-40 °C	120 °C	This material is constructed with a static dissipative adhesive, it is designed for printed circuit board and electronic component post-process labeling.	UL RecognisedCSA AcceptedMeets surface resistivity values in the recommended range for dissipative ESD packaging materials as defined by ANS/ESD S541-2008 (between 10 and 10 ohms)
B-481	StainerBondz™ Polyester	Matt	White	-80 °C	130 °C	White polyester will remain resistant when exposed to xylene and other chemicals that are commonly used in the slide staining process	–
B-483A	Polyester	Gloss	White	-40 °C	120 °C	White polyester thermal transfer printable material with glossy finish and aggressive adhesive specifically designed for powder coated surfaces.	UL RecognisedCSA Accepted
B-483A / B-634	Polyester with Polyester Overlamine	Gloss	White	-18 °C	54 °C	ToughStripe™ floor marking thermal transfer printable polyester with ultra-aggressive adhesive which allows for printable messages to be placed on the floor. The floor marking roll ships with a separate roll of B-634 Polyester Overlamine to protect your legend. Ideal to create custom-printed floor labels. Available in white, yellow, red, orange, green, blue and black.	–
B-486B	Metallised Polyester	Matt	Light Grey	-40 °C	120 °C	Metallized polyester thermal transfer printable material, ideal for indoor product labeling, asset tracking and general ID on very rough surfaces.	UL RecognisedCSA Accepted
B-488	Polyester	Matt	White	-40 °C	145 °C	White polyester thermal transfer printable material, similar to B-423, but with matt finish. Widely used for component identification, barcoding, asset and inventory tracking.	–
B-489A	Polyester	Matt	White	-40 °C	120 °C	White polyester thermal transfer printable material, similar to B-483, but with matt finish. Aggressive adhesive specifically designed for powder coated surfaces.	UL RecognisedCSA Accepted
B-490	FreezerBondz™ Polyester	Matt	White	-196 °C	130 °C	Can be applied to frozen surfaces including glass and polypropylene stored in liquid nitrogen, except for Vial Tops. Material must slightly overlap itself.	–
B-492	FreezerBondz™ Polyester	Matt	White	-196 °C	110 °C	Ultra thin; can label frosted/frozen (with overlap) or room temperature labels and lasts in liquid nitrogen and hot water baths	–
B-498	Vinyl Cloth	Semi-gloss	White	-40 °C	80 °C	White vinyl cloth label material with glossy finish. The adhesive and cloth backing give excellent holding power, while being repositionable and removing cleanly.	UL Recognised
B-499	Nylon Cloth	Matt	Black on White	-40 °C	90 °C	Nylon cloth material with matt finish. The adhesive allows labelling in environments with heat, cold, oil and dirt. Also available in yellow.	UL RecognisedCSA AcceptedHalogen Free (DIN VDE 0472/part 815) Approvals are for White material only
B-509	Magnetic Polyester	Matt	White	-18 °C	70 °C	Magnetic Back Polyester is used for temporary, reusable and movable signs	–
B-526	Phosphorescent Polyester	Gloss	Photoluminescent Green	-40 °C	60 °C	BradyGlo™ High Intensity laminate is designed to provide high adhesion and luminance for egress marking in low light areas in and along stairwells of public buildings, exit and directional signs, identification of fire alarms and extinguishers, low location egress pathway markings, and directional systems for escape or evacuation routes.	New York Local Law 26 RS 6-1 & 6-1ACity of New York, Department of Buildings MEA No. 467-06-M UV: 46-9-7
B-529	Polypropylene	Gloss	White	-40 °C	100 °C	Brady's economy polypropylene tape is for use indoors on smooth, flat surfaces.	–
B-530	Tamper-resistant Vinyl	Gloss	White	-40 °C	90 °C	Brady's tamper resistant tape destructs into tiny fragments when tampered with.	–
B-549	Polyester	Gloss	White	-40 °C	100 °C	Flexible, dimensionally stable, low temperature, pressure sensitive adhesive tape for permanent application. Adhesive can be applied at temperatures down to -10°F (-23°C).	–
B-569	Polyester	Gloss	Green	-40 °C	100 °C	Designed for use on stainless steel pipes in harsh environments such as the Pulp and Paper Industry	–
B-581	Vinyl	Gloss	White	-40 °C	82 °C	Only indoor use, where frequent repositioning is required	–
B-582	Phosphorescent Polyester	Gloss	Photoluminescent Green	-40 °C	80 °C	Phosphorescent Polyester is used for exit and directional signs, identification of fire alarms and extinguishers, low location egress pathway markings, and directional systems for escape or evacuations routes.	ASTM E-2072-00 / ASTM E-2073-00ASTM E-162ASTM E-648ASTM E-662IMO Resolution A.752(18)ISO/CD 15370Marine Safety Committee MSC.27(61)DIN 67 510 (Parts 1 - 4)OSHA 1910.37
B-584	Reflective Tape	Gloss	Orange	-40 °C	70 °C	Suitable for outdoor use. Also available in silver and yellow.	–

Material	Finish	Colour	Temp (°C) (Tested for 30 days)		Properties & Applications	Approval/Compliance	
			Min.	Max.			
B-595	Vinyl	Gloss	White	-40 °C	82 °C	Durable, low-shrink vinyl with our most aggressive adhesive. Conforms to irregular, curved, rough and highly textured surfaces (painted cinder blocks, uneven wood, textured plastics, paper-jacketed pipes, powder-coated surfaces). Adheres to "difficult" low-surface energy items (PVC piping, blow-moulded equipment cases, ABS plastics, recycled plastics). Available in a wide range of colours.	BS 5609:1986 Section 2 and section 3
B-642	Polyvinylfluoride	Matt	White, Transparent	-70 °C	120 °C	Applications requiring self-extinguishing identification. Self-laminating, wire, cable and laboratory vial marking. Excellent abrasion and smudge resistance.	–
B-719	Polyimide	Matt	White	-70 °C	300 °C	White polyimide material with matt finish and ultra-durable adhesive. Used in printed circuit board and electronic component pre-process labelling. Designed for use with extreme wash protocol and cleaning chemicals. Surface resistivity values in the recommended range for dissipative ESD packing materials.	UL RecognisedANSI/ESD S541-2008 (between 10 and 10 ohms) for dissipative ESD packaging materialsMIL-STD-202G Method 215K
B-724	Polyimide	Matt	Amber	-70 °C	300 °C	Amber polyimide material with matt finish and ultra-durable adhesive. Used in printed circuit board and electronic component pre-process labelling. Designed for use with extreme wash protocol and cleaning chemicals.	MIL-STD-202G, Notice 12, Method 215KSAE AS81531 Marking of Electrical Insulating Material
B-7593	Polyethylene Foam Laminate Polyester	Gloss	White, Yellow, Red, Green, Silver, Black	-40 °C	100 °C	EPREP (Engraved Panel REplacement labels) are designed for patch panel identification in identifying external push-buttons, switches and internal connection points. Also available in black, green, red, silver and yellow.	–
B-7598	Polyester	Gloss	White, Yellow, Red, Green, Silver, Black, Blue	-40 °C	100 °C	A general identification polyester tag for cables exposed to extreme conditions. Up to 10 years outdoor durability. Also available in black, blue, green, red, silver and yellow.	Parts supplied in White, Black or Silver are Halogen Free as per IEC 61249-2-21 (2003-11)
B-7599	Polyethylene	Matt	Yellow	-40 °C	50 °C	White polyethylene tag material. Rapido™ Wiremarking Sleeves are fast and easy to apply. Simply squeeze the edges of the material together, thread your wire through the holes and pull away the wire to release the marker.	–
B-7641	Heat-shrink Polyolefin	Matt	White	-55 °C	105 °C	2:1 ratio heat shrinkable, zero halogen wire marking sleeves. The wire marking sleeves offer outstanding fire safety properties and minimal smoke emission. Also available in yellow.	BS-6853 (1999) Vehicle Category 1A; EN-45545-2, requirement 24, Vehicle Category HL3Zero Halogen
B-7643	Thermoplastic Polyether Polyurethane	Matt	White, Yellow	-40 °C	90 °C	Thermal transfer and dot matrix printable wire and cable bundle tag for harsh environments. Low halogen material. Also available in black, orange, red and yellow.	Halogen free per IEC 61249-2-21 (2003-11)Adherence: SAE-AS81531-1998Flame retardant: MIL-STD-202G
B-767	Static Dissipative Polyimide	Gloss	White	-80 °C	300 °C	The high performance B-767 material is ideal for PCB and electronic component manufacturing, this material is static dissipative and survive extreme processes like wave soldering and multiple harsh washes.	UL RecognisedANSI/ESD S541-2008 (between 10 and 10 ohms) for dissipative ESD packaging materialsMIL-STD-202G Method 215K
B-768	Static Dissipative Polyimide	Gloss	White	-80 °C	300 °C	The high performance ultra-thin B-768 material is ideal for PCB and electronic component manufacturing, this material is static dissipative and survive extreme processes like wave soldering and multiple harsh washes.	UL RecognisedANSI/ESD S541-2008 (between 10 and 10 ohms) for dissipative ESD packaging materialsMIL-STD-202G Method 215K
B-7696	Vinyl	Gloss	White, Yellow	-40 °C	70 °C	Brady DuraSleeve® printable inserts create a durable legend. The rigid construction of the DuraSleeve wire marking system provides inserts that can easily be inserted into a clean carrier. The legend can be changed before or after termination. Also available in yellow.	UL94 V0
B-7697	Polyester	Matt	White	-40 °C	120 °C	Brady DuraSleeve® printable polyester wire marking inserts. The rigid construction of the DuraSleeve system provides inserts that can easily be inserted into a clean carrier.	–
B-797	Polyimide	Gloss	White	-70 °C	300 °C	B-797 is a high performance material for PCB and electronic component manufacturing, that is engineered to survive extreme processes like wave soldering and multiple harsh washes.	UL RecognisedMIL-STD-202G, Notice 12, Method 215KDibutyltin and Dioctyltin free
B-854	Metal Detectable Polyester	Matt	White	-40 °C	110 °C	Tough against harsh washdown environments; metal detectable. Also available in yellow.	–
B-855	Polyester	Matt	White	-40 °C	110 °C	Tough against harsh washdown environments. Also available in yellow.	–

Design any label with Brady Workstation apps




In order to achieve full track & trace control, you can use Brady Workstation apps to quickly design labels, import data from ERP or LIMS-systems, add QR-codes, barcodes or other 2D-codes, serialise and hit print. When printed with the specialised inks of a Brady printer, our label materials can identify items throughout complete production cycles and in storage much more effectively and much longer than any non-specialised solution.

▶ Try it today! Discover Brady Workstation at www.bradyeurope.com/workstation or download at workstation.bradyid.com.

Brady Workstation Express Labels App

Access files faster. Anywhere you work.



- ▶ 20+ barcode types
- ▶ 85+ fonts
- ▶ 1,400+ symbols
- ▶ Microsoft Excel data imports
- ▶ Label sequencing
- ▶ Label saving and sharing
- ▶ Accurate print preview
- ▶ Real-time printer status
- ▶ 30+ Supported languages

▶ Get the free app from Apple App Store or Google Play (Search “Brady Express Labels”)



Specifications	
Print Technology	Thermal Transfer
Print Resolution (dpi)	300
Print Speed (mm/sec)	76.20
Colour Capability	Monocolour
Continuous vs Die-cut Labels	Continuous Die-cut
Max. Label Width (mm)	50.80
Max. Print Length (mm)	1016.00
Connectivity Options	Standalone Use USB Bluetooth on selected models WiFi on selected models
Phones & Tablets Supported	Android devices with Android OS 10+ iPhone with iOS 15+
Software Compatibility	Brady Workstation Express Labels Mobile App Windows based driver for 3rd party software use
Bar Code Type	QR Code Data Matrix Code 128 Code 39 EAN-8 EAN-13 Interleaved 2 of 5 UPC-A UPC-E More through software
Built-in Symbols	500+
Physical Properties	
Width x Height x Depth (mm)	240.03 x 345.20 x 116.75
Weight (kg)	2.45
On Screen Indicators	Battery Life Ribbon and label part number recognition Ribbon Remaining Supply Remaining WiFi Bluetooth Status Error Messaging
Cutter	Auto Cutter
Warranty	2 years
Drop Test	Resistant to 1.2 metre drops Sand & Dust



Printers



Order Reference	Art. No.	Description
M710-AZERTY-EU	317814	M710 AZERTY
M710-AZ-BWS	322912	M710 AZERTY EU + Brady Workstation Suite
M710-WB-AZ-BWS	322915	M710 AZERTY EU Wi-Fi, BT + Brady Workstation Suite
M710-WB-AZERTY-EU	317815	M710 AZERTY Wi-Fi, BT
M710-WB-CYR-BWS	322918	M710 CYRILLIC EU Wi-Fi, BT + Brady Workstation Suite
M710-WB-CYRILLIC	317817	M710 Cyrillic Wi-Fi, BT
M710-QWERTY-EU	317810	M710 QWERTY EU
M710-QY-EU-BWS	322911	M710 QWERTY EU + Brady Workstation Suite
M710-WB-QWERTY-EU	317811	M710 QWERTY EU Wi-Fi, BT
M710-WB-QY-EU-BWS	322914	M710 QWERTY EU Wi-Fi, BT + Brady Workstation Suite
M710-QWERTY-UK	317812	M710 QWERTY UK
M710-QY-UK-BWS	322913	M710 QWERTY UK + Brady Workstation Suite
M710-WB-QWERTY-UK	317813	M710 QWERTY UK Wi-Fi, BT
M710-WB-QY-UK-BWS	322917	M710 QWERTY UK Wi-Fi, BT + Brady Workstation Suite
M710-US	317834	M710 Qwerty US
M710-WB-US	317835	M710 Qwerty US Wi-Fi, BT
M710-WB-QZ-BWS	322916	M710 QWERTZ EU Wi-Fi, BT + Brady Workstation Suite
M710-WB-QWERTZ	317816	M710 QWERTZ Wi-Fi, BT

This printer ships in a hard case holding a USB cable, a quick start guide, a product USB (with product info and Windows driver), a Li-ION Rechargeable Battery, an AC Adapter, a Brady Workstation Software, a Media Adapter, a roll of M7C-1000-595-WT and an M7-R6000 ribbon.

▶ For more information about Brady Workstation App And Brady Express Label App, see page 52.

The Basic Suite is included with every printer, all you need to do is download it.
Workstation.BradyID.com/Free

Accessories

Hard case



Cleaning kit



Li-Ion Battery



Art. No.	Description
114886	Cleaning Kit
175664	Hard Case M710 Label Printer
321280	M710 Label Printer AC Adapter/Charger EU
321281	M710 Label Printer AC Adapter/Charger UK
147998	Media Adaptor for high-end portable printer
150619	Protective softbag for portable printers
175673	Rechargeable Lithium-ion Battery for M610/M710 printer
175674	Rechargeable NiMH Battery for M610/M710 printers
175665	USB-C to USB Type A Cord

Real support

We understand how important label printers can be. We appreciate the vital role label printers play in enabling track and trace capabilities, quality control, fraud prevention, enhanced safety, and operational efficiency. That is why we will deliver a solution to any technical issue, as fast as possible.



▶ **No matter which label printer you are using: contact us.**

☎ **0208 865 0438**

✉ **tseurope@bradycorp.com**

Easy to reach, anywhere

If you have a problem with a label printer, just call Brady. Our highly experienced Technical Excellence Centre Engineers are standby to solve your issue. Via phone, via email, or in person at your premises. Offer any technical label printer challenge you are facing, and you will get a first response within 24 hours, in your own language. Because we are here to reduce complexity, not add to it.

Customer focused support

We deliver complete solutions and complete support, tailored to the needs of your workplace. If fast response times and troubleshooting are what you need, that's what we will deliver. If you want to include professional label printer installation and programming, training, preventive maintenance, loaner printers or even standby loaners at your premises, that's what we will enable. Give us a call, tell us about your needs, and we will suggest an ideal service level.

Straight from the manufacturer

Our experienced engineers know every component of your Brady printer, from printhead, drivers and software, down to the smallest rivet. They will solve your issue, no matter how unique it might be. Because that is what happens when you have direct manufacturer support.

▶ **Review our service levels:**





Belgium & Luxembourg

+32 (0) 52 45 78 11
benelux@bradycorp.com

Czech Republic

+420 776 302 229
czechrepublic@bradycorp.com

Denmark

+45 66 14 44 00
denmark@bradycorp.com

France

+33 (0) 3 20 76 94 48
france@bradycorp.com

Germany, Austria & Switzerland

+49 (0) 6103 7598 660
germany@bradycorp.com

Hungary

+36 23 500 275
hungary@bradycorp.com

Italy

+39 02 26 00 00 22
italy@bradycorp.com

Netherlands

+31 (0)70 323 62 98
benelux@bradycorp.com

Norway

+47 70 13 40 00
norway@bradycorp.com

Poland

+48 22 104 6262
poland@bradycorp.com

Qatar, Saudi Arabia & UAE

+971 4881 2524
me@bradycorp.com

Slovakia

+421 902 939 406
slovakia@bradycorp.com

South Africa

+27 11 704 3295
africa@bradycorp.com

Spain & Portugal

+34 900 902 993
spain@bradycorp.com
portugal@bradycorp.com

**Sweden, Finland, Estonia, Latvia,
Lithuania**

+46 (0) 8 590 057 30
sweden@bradycorp.com

Turkey

+90 212 264 02 20
turkey@bradycorp.com

UK & Ireland

+44 (0) 1295 228 288
uk@bradycorp.com

We make products that make the world a safer and smarter place. From the depths of the ocean to outer space, from the factory floor to the delivery room - **we're just about everywhere you look.**



To help minimise our impact on the environment, Brady limits its number of reprints.

Updated versions are always available for download on bradyeurope.com/downloads.



Search for: EUR-M-314-EN



Y5178106

Your distributor