

Article No. : 6SL5510-1BE17-0AF0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :



Figure similar

Rated data	
Input	
Number of phases	3 AC
Line voltage	380 ... 480 V +10 % -15 %
Line frequency	45 ... 66 Hz
Rated current for 3 phases	14.0 A
Inrush current	3.0 A
Output	
Number of phases	3 AC
Rated power	7.00 kW
Rated current I _N	13.2 A
Max. output current	37.4 A
Pulse frequency	8 kHz
Output frequency	0 ... 550 Hz

Electronics power supply	
Voltage	20.4 ... 28.8 V

Control Type	
Communication	PROFINET

Ambient conditions	
Cooling	Air cooling using an integrated fan
Installation altitude (without derating)	4,000 m
Installation altitude	1,000 m (3,281.00 ft)

Ambient temperature during	
Operation	0 ... 55 °C (32 ... 131 °F)
Maximum without power reduction	45 °C
Transport	-40 ... 70 °C (-40 ... 158 °F)
Storage	-40 ... 70 °C (-40 ... 158 °F)

Relative humidity during	
Max. operation	95 %

Data sheet for SINAMICS S200

Article No. : 6SL5510-1BE17-0AF0

Inputs / outputs	
Standard digital inputs	
Number	4
Fail-safe digital inputs	
Number	2
Rapid input digital inputs	
Number	2
Digital outputs	
Number	2

Mechanical data	
Degree of protection	IP20 / UL open
Frame size	FSD
Net weight	4.00 kg (9.92 lb)
Dimensions	
Width	95.0 mm (3.74 in)
Height	260.0 mm (10.24 in)
Depth	230.0 mm (9.06 in)

Connections	
Signal cable	
Version	MDR plug
Line side	
Version	Push-in connection
Conductor cross-section	0.75 ... 2.50 mm ² / 19 ... 13 AWG
Motor end	
Version	Push-in connection
Conductor cross-section	0.75 ... 2.50 mm ² / 19 ... 13 AWG
DC link (for braking resistor)	
Version	Push-in connection
Conductor cross-section	0.75 ... 2.50 mm ² / 19 ... 13 AWG
Cable length	3.00 m ()
Holding brake	
Version	Push-in connection
Conductor cross-section	0.00 ... 2.00 mm ² / 23 ... 16 AWG
STO connection	
Version	Push-in connection
Conductor cross-section	0.00 ... 2.00 mm ² / 24 ... 16 AWG
encoder connection	
Version	plug connector IX Typ C
Max. motor cable length	
Shielded	30 m

Certificates	
Certificate of suitability	CE, UL, KC, UKCA, EAC, RCM, SEMI47
CE marking	EMC Directive 2014/30/EU with IEC 61800-3, Low-Voltage Directive 2014/35/EU, Machinery Directive 2006/42/EC, RoHS 2011/65/EU, WEE 2012/19/EU
Verification of suitability for fail-safety	SIL 3 according to IEC 61508 and IEC 61800-5-2, PL e according to ISO 13849-1, Category 3 or 4 according to ISO 13849-1

Data sheet for SINAMICS S200

Article No. : 6SL5510-1BE17-0AF0

Environmental conditions

Chemically active substances

Operation	Class 3C2 according to EN 60721-3-3: 2002
Transport	Class 2C2 according to IEC 60721-3-2:1997
Storage	Class 1C2 according to IEC 60721-3-1: 1997

Biologically active substances

Operation	Class 3B1, acc. to EN 60721-3-3: 2002, dust not permitted
Storage	Class 1B1 according to IEC 60721-3-1:1997

Mechanically active substances

Operation	3S2 according to IEC 60721-3-3: Ed. 2.2 2002
-----------	--

Climatic environmental conditions

Operation	Class 3K3 according to IEC 60721-3-3 Ed. 2.2: 2002
Transport	Class 2K4 according to IEC 60721-3-2:1997
Storage	Class 1K4 according to IEC 60721-3-1:1997

Mechanical environmental conditions

Operation	Class 3M1 according to IEC 60721-3-3 Ed. 2.2: 2002
Transport	Class 2M3 according to IEC 60721-3-2:1997
Storage	Class 1M2 according to IEC 60721-3-1:1997