






L-56B		L-456B		L-796B		L-816B	
-------	---	--------	---	--------	--	--------	---

Part No.	Emitting Color + Material	λ_D (nm)	Lens Type	Iv (mcd) VF=9V		Viewing Angle	Dimension
				Min.	Typ.		

L-56BHD	GaP	660	red diffused	2	5	60°	T-1 3/4 (5mm) Round  L53SRSGW
L-56BID	GaAsP/GaP	625	red diffused	20	40	60°	
L-56BGD	GaP	568	green diffused	5	20	60°	
L-56BYD	GaAsP/GaP	588	yellow diffused	5	20	60°	
L-56BSRD-B	GaAlAs	640	red diffused	100	200	60°	

L-456BHD	GaP	660	red diffused	0.8	1	60°	T-1 3/4 (5mm) Round 
L-456BID	GaAsP/GaP	625	red diffused	12	20	60°	
L-456BGD	GaP	568	green diffused	5	15	60°	
L-456BYD	GaAsP/GaP	588	yellow diffused	5	15	60°	
L-456BSRD-B	GaAlAs	640	red diffused	100	200	60°	

L-796BID	GaAsP/GaP	625	red diffused	20	60	60°	8mm Round 
L-796BGD	GaP	568	green diffused	20	50	60°	
L-796BYD	GaAsP/GaP	588	yellow diffused	20	40	60°	
L-796BSRD-B	GaAlAs	640	red diffused	100	300	60°	
L-796BSRC-B	GaAlAs	640	water clear	500	800	40°	

L-816BID	GaAsP/GaP	625	red diffused	20	60	60°	10mm Round 
L-816BGD	GaP	568	green diffused	20	50	60°	
L-816BYD	GaAsP/GaP	588	yellow diffused	20	40	60°	
L-816BSRD-B	GaAlAs	640	red diffused	100	300	60°	
L-816BSRC-B	GaAlAs	640	water clear	500	800	40°	

NOTES :

1. All dimensions are in millimeters (inches)
2. Tolerance is $\pm 0.25\text{mm}$ (0.01") unless otherwise noted.