






ITEM #	PART #	REV	DESCRIPTION	QTY	Material	Weight
1	MNZ028	03	Nozzle Body	1	Mild Steel	13.3g
2	FPZ006	03	Compression spring	1	Music Wire	0.2g
3	MZZ011	05	Nozzle seat	1	Aluminium	0.7g
4	HAZ002	03	5mm ball bearing	1	Chrome Steel	0.5g
5	ANZ020	03	Extension Spreader Assy.	1	Mild Steel & Copper tube	13g



SECTION A-A

 Power Adhesives THIS DRAWING AND THE INFORMATION IT CONTAINS IS THE PROPERTY OF POWER ADHESIVES AND IS CONFIDENTIAL. IT MUST NOT BE REPRODUCED EITHER WHOLLY OR IN PART. ALL RIGHTS IN RESPECT OF PATENTS, DESIGNS AND COPYRIGHTS ARE RESERVED.	MATERIAL		DRAWN	SteveE	DIMENSIONS ARE IN MM UNLESS OTHERWISE STATED  THIRD ANGLE	TOLERANCES UNLESS OTHERWISE STATED WHOLE NUMBERS ±0.5mm 1 DECIMAL PLACE ±0.3mm 2 DECIMAL PLACE ±0.1mm	SCALE 1:1
	FINISH		DATE	12/07/2016			SHEET 1 OF 2
	COLOUR		ECR No.		TITLE Spreader Extension Nozzle		
	NOTES Weight: 28.1g						
					DWG. No.		MPN - ADJ012
					A4		01

1	2	3	4	5	6				
A	Technical data								
	Type	Hot melt applicator nozzle							
	Material composition	Aluminium, steel, copper tube, music wire							
	Weight	7g (0.25 oz)							
	Thread size	5/16 UNF							
	Nozzle hole size	0.8 x 5mm (0.03" x 0.2")							
	Sping rate	0.48 N/mm (2.75 lb/inch)							
B									
C									
D	 THIS DRAWING AND THE INFORMATION IT CONTAINS IS THE PROPERTY OF POWER ADHESIVES AND IS CONFIDENTIAL. IT MUST NOT BE REPRODUCED EITHER WHOLLY OR IN PART. ALL RIGHTS IN RESPECT OF PATENTS DESIGNS AND COPYRIGHTS ARE RESERVED.	MATERIAL		DRAWN	SteveE	DIMENSIONS ARE IN MM UNLESS OTHERWISE STATED  THIRD ANGLE	TOLERANCES UNLESS OTHERWISE STATED WHOLE NUMBERS ±0.5mm 1 DECIMAL PLACE ±0.3mm 2 DECIMAL PLACE ±0.1mm	SCALE 1:1	
		FINISH		DATE	12/07/2016			TITLE Spreader Extension Nozzle	
		COLOUR		ECR No.		DWG. No. A4	ADJ012		REVISION 01
		NOTES							
		1	2	3	4	5	6		