


**FAG****NJ2314-E-XL-TVP2**

Cylindrical roller bearing

Cylindrical roller bearing NJ...E-XL-TVP2,
with cage, single row, semi-locating bearing,
2 ribs on outer ring, 1 rib on inner ring, type
NJ

X-life

Technical information




Your current product variant

Design	E	Increased Capacity Design
Cage	TVP2	Solid Window Cage made from PA66
Radial internal clearance	CN (Group N)	Normal internal clearance
Tolerance class	PN	Normal (PN)
Number of rolling element rows	1	Single-row design

Main Dimensions & Performance Data

d	70 mm	Bore diameter
D	150 mm	Outside diameter
B	51 mm	Width
C _r	325,000 N	Basic dynamic load rating, radial
C _{0r}	325,000 N	Basic static load rating, radial
C _{ur}	60,000 N	Fatigue load limit, radial
n _G	6,300 1/min	Limiting speed
n _{gr}	3,800 1/min	Reference speed
≈m	4.05 kg	Weight



Mounting dimensions

$d_{a \min}$	82 mm	Minimum diameter shaft shoulder
$d_{a \max}$	87 mm	Maximum diameter of shaft shoulder
$D_{a \max}$	138 mm	Maximum diameter of housing shoulder
$d_{c \min}$	100 mm	Minimum shaft shoulder
$r_{a \max}$	2.1 mm	Maximum recess radius

Dimensions

r_{\min}	2.1 mm	Minimum chamfer dimension
$r_{1 \min}$	2.1 mm	Minimum chamfer dimension
s	4.7 mm	Axial displacement
E	133 mm	Raceway diameter outer ring
F	89 mm	Raceway diameter inner ring
$D_{1 \min}$	126.8 mm	Minimum rib diameter outer ring
d_1	97.4 mm	Maximum rib diameter inner ring






Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.

Additional information

HJ2314-E	L-washer
----------	----------

Characteristics

-  F_r Radial load
-  F_a Axial load in one direction
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed