



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 171354-1
17 CIR MIC PLUG HSG



Customers Also Bought



TE Part #CAT-D9934-A75E
Header Assembly: Wire-to-Board, 15A, gold or tin plated



TE Part #350547-1
UMNL PIN 20-14 PTPBR L/P




TE Part #3-316080-5
DYNAMIC D-3200 HDR ASSY 10P H



TE Part #CAT-D9934-A75B
Receptacle and Tab Housing: 5.08 mm Pitch, 250-600V



TE Part #175288-3
DYNAMIC D-3 TAB CONT. M AU 0.76 L/P



TE Part #2-1447175-5
FS2N25.4A12PA FSJ (FSN-71A-12 V=PA4.0)



TE Part #171367-4
MIC CAP 21P H



TE Part #7-171363-1
MIC CAP W-PCB ASSY 17P V

Documents

Product Drawings

MIC 17P PLUG HSG

English

CAD Files

Customer View Model

ENG_CVM_171717-1_C.3d_igs.zip

English

Customer View Model

ENG_CVM_171717-1_C.3d_stp.zip

English

Customer View Model

ENG_CVM_171717-1_C.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Crimping Receptacle Contacts of Multi-Interlock Connector (MIC)

English

Instruction Sheets

Instruction Sheet (non U.S.)



Japanese

AMP EXTRACTION TOOL FOR MULTI-INTERLOCK CONNECTOR P/N 723735-1

Japanese