

T8 LED UV-A 24" 6.5W 230V PA

Item No: 0001686

SYLVANIA

SpecialLITE®



Sylvania T8 LED UV-A tubes in 18" and 24" for flykilling applications• Easy and safe replacement for fluorescent tubes without any rewiring required• LED upgrade for installations with CCG/ magnetic fluorescent ballast using a LED replacement starter (supplied)• Suitable for direct mains operation• Approx. 75% energy saving vs fluorescent originals• Flycatch rate in line with Sylvania Fluo T8 after 180 mins*• Special frosted glass tube does not block UV or degrade intranmission over life• Acid etched glass delivers optimal beam distribution to maximize insect attraction• Optimised UV spectrum to maximize insect attraction• UV-A LED chip with peak emission at 370nm

Technical Assets

Photometrics

General data

Product name	T8 LED UV-A 24" 6.5W 230V PA
Technology	LED
Lamp shape	Tube, double-ended
Cap/Base	G13
Lamp finish	Frosted/Coated
Fixture rating	Open
General application	SPG
Virtual assistant compatibility	N/A
Warranty	2 years

Optical data

UV-A irradiance	400
Light colour	BL368 Blacklight
Colour Variation Initial (SDCM)	N/A
Photobiological Risk Group	RG0

Electrical data

Power consumption (W)	6.5
Supply current (A)	40
Primary Supply/Product voltage - min (V)	220.0
Primary Supply/Product voltage - max (V)	240.0
Dimmable	No
Inrush Current (A)	25
Inrush Duration (µs)	200
Nominal Frequency (Hz)	50/60Hz

Lifetime data

Average life (Nominal) (h)	20000
----------------------------	-------

T8 LED UV-A 24" 6.5W 230V PA

Item No: 0001686



Physical data

Nominal Product Length (mm)	604
Nominal Product Diameter (mm)	28
Max. Lamp Diameter (mm) - D	28
Weight (kg)	0.156

Packaging

Product EAN number	5410288016863
Packaging single length / height (cm)	64.4
Packaging single width (cm)	3.5
Packaging single depth (cm)	3.5
DUN14 (inner)	15410288016860
Units per outer package	25
Packaging outer length / height (cm)	66.8
Packaging outer width (cm)	18.5
Packaging outer depth (cm)	18.5

Safety data

Breakage cleaning instructions	n/a
Special purpose lamp	Yes
Intended purpose	Flykilling - Insect attraction
Suitable for household illumination	No
Safety message	Not suitable for household