

DCE0825D1G-QW

Cross Laser Level + 5 Points XR 12V 2Ah Li-Ion - Green Beams



5035048666913

Product Description:

Working Range (m): 15 Beam Color: Green Accuracy: +/- 3 mm at 10 m



Product features and benefits:

- XR 10.8V battery pack included
- Range: points = 30 m, lines = 20 m
- Battery charge indicator
- Projects horizontal and vertical lines + 5 individual points
- Cross-line provides 150° angular range Horizontal beam at the back for upgrades
- Additional Built-in magnetic holder that allows the laser to be mounted directly on the metal rail to ensure accurate projections all around Pulse mode for use with a sensor up to 50 m Durable design and durability thanks to IP65 protection class (dust and waterproof) - 1.5 m drop test
- Compensator lock: Protection of the internal mechanism of the laser
-
-
- when transporting Integrated swivel base with 1/4" and 5/8" threads for
- tripod mounting

Specifications techniques :

- Working range with detector - diameter: 50 m
- Range: 30 m
- Battery voltage: 12 V

Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

Included Items:

- TSTAK Box (x1)
- 12V/2Ah Battery (x1)
- Charger (x1) Target
- (x1) Reading Glasses
- (x1) Ceiling Stand (x1)
-

