



Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Keying Plug**

Primary Product Color: **Natural**

Operating Temperature (Max): **105 °C [221 °F]**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Hardware Accessory Function: **Coding & Keying**

Features

Product Type Features

Connector Hardware Accessory Type	Keying Plug
Hardware Accessory Function	Coding & Keying

Body Features

Primary Product Color	Natural
-----------------------	---------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Bag
Packaging Quantity	1000

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)




EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-770988-0
MINI UMNL SOK 22-18AWG AU




TE Part # 770986-1
MINI UMNL SOK 26-22AWG SN LP




TE Part # 1-794058-0
MINI UMNL SOK L/P LF



TE Part # 1-770986-0
MINI UMNL SOK 26-22AWG AU LP




TE Part # 1-770987-0
MINI UMNL PIN 22-18 AWG AU LP



TE Part # 1-770988-1
MINI UMNL SOK 22-18AWG LP LF



TE Part # 1-794059-0
MINI UMNL PIN L/P LF



TE Part # 1-770985-0
MINI UMNL PIN 26-22AWG AU LP

Also in the Series | Mini-Universal MATE-N-LOK



Connector Caps & Covers(2)

Connector Contacts(89)

Connector Hardware(4)

Connector Seals & Cavity Plugs(17)

Connector Strain Relief(2)

Insertion & Extraction Tools(1)

PCB Headers & Receptacles(93)

Rectangular Power Connectors(196)

Wire-to-Board Headers & Receptacles (93)

Customers Also Bought

TE Part #2176078-1
EP 1W 10R 5%

TE Part #1-794407-0
MINI UMNL SOK 20-16 AWG AU LF

TE Part #2-826942-0
20P MOD2 STIFT LEI

TE Part #1623731-1
BCHE 5 W 10K 5%

TE Part #770584-1
18P MINI UMNL PLUG HSG

TE Part #5042433001
FLT0111-1.50-0

TE Part #2-34072-2
SPLICE,PG BUTT 12-10

TE Part #350536-7
UMNL SOK 20-14 .0126 AUNI/BR



Documents

Product Drawings

KEYING PLUG MINI U-M-N-L

English

CAD Files

Customer View Model

ENG_CVM_174670-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_174670-1_A.3d_stp.zip

English

Customer View Model

ENG_CVM_174670-1_A.2d_dxf.zip

English

3D PDF

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_174670-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_174670-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_174670-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG

English

Product Specifications

Application Specification

English

