




Connectors > Rectangular Connectors > Standard Rectangular Connectors > DYNAMIC 5000 REC AND TAB HSG



Connector Product Type: **Housing**  
Connector System: **Wire-to-Wire**  
Number of Positions: **2**  
Number of Rows: **1**  
Sealable: **No**

[All DYNAMIC 5000 REC AND TAB HSG \(56\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	2
Number of Rows	1

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CAT-D9934-A83  
Contact: Component To Wire ; 20-45A › 20-8 wire size

Also in the Series | [Dynamic 5000 Series](#)



Connector Contacts(43)



Connector Hardware(3)



Power Contacts(43)




Rectangular Connector Housings(45)



Rectangular Power Connectors(80)




Standard Rectangular Connectors(45)



Wire-to-Board Connector Assemblies & Housings(26)

Customers Also Bought



TE Part #2176469-1  
TLRP 2010 2.0W R010 1% 75PPM 4K RL




TE Part #6450572-1  
MBXL R/A RCPT 3ACP+4P+24S



TE Part #2-406549-5  
IMJ,1X1,PNL GRD,LED(G/G), SN



TE Part #917805-2  
DYNAMIC D-5 TAB CONT. M L/P



TE Part #3-1473562-4  
RITS CONN. PLUG ASSY 4P ORANGE




TE Part #534267-1  
14 MODIV VRT DR OE 100/125



TE Part #5650118-3  
CONN SEC II 6 POS 100C/L R/A



TE Part #1-1734035-1  
MINI USB, TYPE B, R/A, SMT



TE Part #826936-3  
3P AMPMODU II STIFT LEI



TE Part #5-2301994-3  
RJ45 JACK INT.MAG. 10/100 1X1 INV.

Documents



Product Drawings

DYNAMIC D-5200S TAB HSG 2P K/Y

English

CAD Files

3D PDF

English

Customer View Model

ENG\_CVM\_2-353047-2\_E.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_2-353047-2\_E.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_2-353047-2\_E.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

TUV Certificate

English