


TOLERANCES (UNLESS SPECIFIED)	
0-10mm	±0.2mm
10.1-50mm	±0.5mm
50.1-250mm	±1.0mm
>250mm	±2.0mm



MODEL Nos. CMA10K/FM0 & CMA30K/FM0
3 PHASE AUTOTRANSFORMER

CAN BE CONFIGURED AS STEP-UP
VOLTAGE TRANSFORMER OR STEP-DOWN
VOLTAGE TRANSFORMER

USED TO CONVERT THE SUPPLY VOLTAGE
TO OTHER COMMON EUROPEAN VOLTAGES

ENSURE THE 3 INPUT PHASES ARE ON THE
SAME VOLTAGE

ENSURE THE 3 OUTPUT PHASES ARE ON
THE SAME VOLTAGE

STAR POINT (NEUTRAL) PROVIDED AT Yn
TERMINAL. CAN BE CONNECTED TO WITH
4-WIRE SYSTEMS OR LEFT UNCONNECTED
WITH 3-WIRE SYSTEMS

TRANSFORMER NOT SUITABLE FOR
GENERATING A NEUTRAL TERMINAL WHEN
NON IS AVAILABLE ON THE SUPPLY

REV	4	
	3	
	2	
	1	

CARROLL & MEYNELL
TRANSFORMERS LIMITED
TEL: 01642 617406 FAX: 01642 614178
enquiries@carroll-meynell.com

TITLE	3 PHASE AUTOTRANSFORMER WIRING DIAGRAM
	ALL DIMENSIONS IN mm

DRAWN GB	PROJECTION ⊙ ▢	DATE 13/06/17	SCALE NTS
DRAW No 5989		REV 0	PAGE 1/1