

NOTES:

1. ELECTRICAL:

1.1 CONTACT CAPACITY 0.25 A, 60 V AC, 5 VA.

1.2 CONTACT RESISTANCE 5 OHMS MAX..

2. OPERATE:


2.1 BREAK ANGLE 4° TO 8° FROM VERTICAL.

2.2 OPERATING TEMPERATURE -10° C TO 40° C.

3. EXTERNALLY FINISHED:

3.1 TIN PLATED.

REV.	DATE	REVISION RECORDS	DR.
B	07/1998	REDRAWN	S.T.
C	04/26/99	CHANGE DIMENSIONING TYPE	S.H.
D	04/02/02	REMOVE REMAKE SPECIFICATION	L.L.



WORKING POSITION

COMUS INTERNATIONAL

454 ALLWOOD RD., CLIFTON, NJ 07012, U.S.A. PH. (973) 777 - 6900

TOLERANCES (Except as noted)	REF.:	SCALE:	DRAWN BY:	APPROVED:
		NONE	L.L.	DATE:
DECIMAL	TITLE: NORMALLY CLOSED TIP OVER SWITCH			
± .01 (0.254) 2 Digt				
± .005 (0.127) 3 Digt				
FRACTIONAL	DATE: 04/02/2002 DRAWING NUMBER: CM1706-1			
± 1/64 (0.397)				
± 1/2°				