

- Standard
- Wealth models
- RoHS compliance, Halogen free



Specifications

Items	Specifications						
Size code	A5	B6	C6	E7	F8	E12	F12
Category temperature range	-55 to +105 °C						
Rated voltage range	2.5 to 20 V.DC						
Rated capacitance range	3.3 to 33 μF	10 to 68 μF	22 to 220 μF	33 to 330 μF	56 to 680 μF	100 to 680 μF	150 to 1500 μF
Capacitance tolerance	±20 (120 Hz/+20 °C)						
Leakage current	Please see the attached characteristics list						
Dissipation factor(tan δ)	Please see the attached characteristics list						
Endurance	105 °C, 2,000 h, rated voltage applied						
	ΔC/C	Within±20 % of the initial value					
	DF	≤2 times of the initial limit					
	LC	Within the initial limit					
Damp heat (Steady State)	60°C, 90 to 95% RH 1,000h No-applied voltage						
	ΔC/C	Within±20 % of the initial value					
	DF	≤2 times of the initial limit					
	LC	Within the initial limit					

Marking and dimensions

(unit : mm)

Size code	φD ±0.5	L ^{+0.1} / _{-0.4}	W ±0.2	H ±0.2	C ±0.2	R	P ±0.2
A5	4.0	5.4	4.3	4.3	5.0	0.6~0.8	1.0
B6	5.0	5.9	5.3	5.3	6.0	0.6~0.8	1.4
C6	6.3	5.9	6.6	6.6	7.3	0.6~0.8	2.1
E7	8.0	6.9	8.3	8.3	9.0	0.6~0.8	3.2
F8	10.0	7.9	10.3	10.3	11.0	0.6~0.8	4.6
E12	8.0	11.9	8.3	8.3	9.0	0.8~1.1	3.2
F12	10.0	12.6	10.3	10.3	11.0	0.8~1.1	4.6

Characteristics list

Series	Rated voltage (V.DC)	Rated capacitance (μF)	Case size (mm)		Size code	Specifications				Standard (Reel size: φ 380)	
			φD	L		Rated ripple current (mA rms) ※1	ESR ※2 (mΩ max.)	tan δ ※3	LC ※4 (μA)	Part number	Min. Packaging Qty (pcs)
SVP	2.5	220	6.3	5.9	C6	2390	23	0.12	110	2R5SVP220M	1000
		680	8.0	11.9	E12	4520	13	0.15	340	2R5SVP680M	400
		1500	10.0	12.6	F12	5440	12	0.18	750	2R5SVP1500M	400
	4.0	33	4.0	5.4	A5	740	200	0.15	66	4SVP33M	2000
		39	5.0	5.9	B6	1100	70	0.12	78	4SVP39M	1500
		68	5.0	5.9	B6	1400	60	0.12	136	4SVP68M	1500
		150	6.3	5.9	C6	1810	40	0.12	120	4SVP150MX	1000
		330	8.0	6.9	E7	2560	35	0.12	264	4SVP330M	1000
		560	8.0	11.9	E12	4520	13	0.15	448	4SVP560M	400
		680	10.0	7.9	F8	3700	25	0.12	544	4SVP680M	500
		1200	10.0	12.6	F12	5440	12	0.18	960	4SVP1200M	400
		6.3	22	4.0	5.4	A5	740	200	0.12	69.3	6SVP22M
	47		5.0	5.9	B6	1100	70	0.12	148	6SVP47M	1500
	82		6.3	5.9	C6	1700	45	0.12	103	6SVP82M	1000
	100		6.3	5.9	C6	1810	40	0.12	126	6SVP100M	1000
	120		6.3	5.9	C6	2780	17	0.12	151	6SVP120MV	1000
	220		8.0	6.9	E7	2560	35	0.12	277	6SVP220MX	1000
			10.0	7.9	F8	3700	25	0.12	277	6SVP220M	500
	330		10.0	7.9	F8	3700	25	0.12	416	6SVP330M	500
	470		10.0	7.9	F8	3700	25	0.12	592	6SVP470MX	500
			8.0	11.9	E12	4210	15	0.15	592	6SVP470M	400
	820		10.0	12.6	F12	5440	12	0.15	775	6SVP820M	400
	10		4.7	4.0	5.4	A5	670	240	0.08	23.5	10SVP4R7M
		6.8	4.0	5.4	A5	670	240	0.09	34	10SVP6R8M	2000
		10	4.0	5.4	A5	700	220	0.10	50	10SVP10M	2000
		15	4.0	5.4	A5	740	200	0.10	75	10SVP15M	2000
		33	5.0	5.9	B6	1100	70	0.12	165	10SVP33M	1500
		47	6.3	5.9	C6	1620	50	0.12	94	10SVP47M	1000
		56	6.3	5.9	C6	1700	45	0.12	112	10SVP56M	1000
		120	8.0	6.9	E7	2560	35	0.12	240	10SVP120M	1000
		150	8.0	6.9	E7	2560	35	0.12	300	10SVP150MX	1000
			10.0	7.9	F8	3020	30	0.12	300	10SVP150M	500
		270	10.0	7.9	F8	3700	25	0.12	540	10SVP270M	500
		330	10.0	7.9	F8	3700	25	0.12	660	10SVP330MX	500
			8.0	11.9	E12	3950	17	0.15	660	10SVP330M	400
		560	10.0	12.6	F12	5230	13	0.15	840	10SVP560M	400
		16	3.3	4.0	5.4	A5	660	260	0.07	26.4	16SVP3R3M
	15		5.0	5.9	B6	1020	120	0.10	120	16SVP15M	1500
	22		5.0	5.9	B6	1060	90	0.10	176	16SVP22M	1500
	39		6.3	5.9	C6	1620	50	0.10	125	16SVP39M	1000
	56		8.0	6.9	E7	1890	45	0.12	179	16SVP56M	1000
	82		8.0	6.9	E7	2120	40	0.12	262	16SVP82M	1000
	100		10.0	7.9	F8	2670	35	0.12	320	16SVP100M	500
	150		10.0	7.9	F8	3020	30	0.12	480	16SVP150M	500
	180		10.0	7.9	F8	3020	30	0.12	576	16SVP180MX	500
			8.0	11.9	E12	3640	20	0.15	576	16SVP180M	400
	330		10.0	12.6	F12	4720	16	0.15	792	16SVP330M	400
	20		10	5.0	5.9	B6	1020	120	0.10	100	20SVP10M
		22	6.3	5.9	C6	1450	60	0.10	88	20SVP22M	1000
		27	6.3	5.9	C6	1450	60	0.10	108	20SVP27M	1000
		33	8.0	6.9	E7	1890	45	0.12	132	20SVP33M	1000
		47	8.0	6.9	E7	1890	45	0.12	188	20SVP47M	1000
		56	10.0	7.9	F8	2400	40	0.12	224	20SVP56M	500
		68	10.0	7.9	F8	2400	40	0.12	272	20SVP68M	500
100		8.0	11.9	E12	3320	24	0.15	400	20SVP100M	400	
150		10.0	12.6	F12	4320	20	0.15	600	20SVP150M	400	

※1: Rated ripple current (100 kHz/ +105 °C), ※2: ESR (100 kHz to 300 kHz/+20 °C) ※3: tan δ (120 Hz/+20 °C) ※4: After 2 minutes

◆Please refer to each page in this catalog for "Reflow conditions" and "Taping specifications".

Frequency Correction factor for ripple current

Frequency	120 Hz ≤ f < 1 kHz	1 kHz ≤ f < 10 kHz	10 kHz ≤ f < 100 kHz	100 kHz ≤ f ≤ 500 kHz
Coefficient	0.05	0.3	0.7	1