

Technical data


32908XU

Single row tapered roller bearings

Tapered roller bearing, pressed steel cage



VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	40 mm
D - External diameter	62 mm
B - Bearing/Inner ring width	15 mm
C - Outer ring width	12 mm
T - Total width	15 mm
a - Charge load application point	11,5 mm
rs - Min fillet radius	0,6 mm
r1s - Min fillet radius	0,6 mm
Mass	0,161 kg
ISO 355 reference	T2BC040

PRODUCT PERFORMANCE

C - Dynamic load	36000000 mN
C0 - Static load	48000000 mN
Cu - Fatigue limit load	5850000 mN
A2 - Rating life coefficient	1
e - Coefficient	0.29
Y0 - Static axial load coefficient	1.14
Y2 - Upper axial load coefficient	2.07
N lim - Oil lubrication limit speed	46800 °/s
N lim - Grease lubrication limit speed	35400 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

ABUTMENT

da max - Max shoulder diameter IR	44,5 mm
db min - Min IR shoulder diameter	45,5 mm
Da max - Max shoulder diameter OR	57,5 mm
Db min - Min OR shoulder diameter	58,5 mm
ra max - Max fillet radius	0,6 mm
r1a - Max fillet radius	0,6 mm

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$$P = X.F_r + Y.F_a$$

$F_a / F_r \leq e$		$F_a / F_r > e$	
X	Y	X	Y
1	0	0.4	Y2

Equivalent static radial load

$$P_0 = X_0.F_r + Y_0.F_a$$

X_0	Y_0
0.5	Y0

If $P_0 \leq F_r$, then use $P_0 = F_r$

The values for e, Y2 and Y0 are shown in the above table

