

**Specification:**

Impedance ratio:  
 Primary: 6k C.T. with 20% UL taps (reference CT)  
 Secondary: 3.75 / 7.5 / 15 ohms


DC resistance ( +/- 15%)  
 Primary (total): 294.7  
 Secondary (total): 682m

Primary inductance @ 1kHz, 0.1V: 20.7H  
 Primary leakage inductance @ 1kHz, 0.1V: 8mH (typical)  
 Interwinding capacitance @ 20kHz: 1.6nF (typical)

Frequency response (+/- 3dB): 40Hz - 25kHz


Max. load at 40Hz: 10W

Core material: grain orientated silicon steel  
 Mass: 0.935kg



Unit 5, Oxonian Park, Langford Locks,  
 Kidlington, Oxfordshire. OX5 1FP  
 Tel: (01865) 855085 Fax: (01865) 855075  
 Website: [www.oep.co.uk](http://www.oep.co.uk)

DESCRIPTION	ISSUE	DATE	DRAWN	CHECKED	DRAWING NUMBER
10W push-pull output transformer	1	09/01/13	CS		<b>D29A09F</b>
	2	27/09/13	CS		
Scale: nts					



All dimensions in mm unless stated otherwise