


一般用途单芯软导体无护套电缆

产品规格书

RS PRO 货号：

从 1840150 到 1840226

从 1856324 到 1856332



产品说明：

- 1) 额定电压: 450/750V
- 2) 温度等级: 70°C
- 3) 执行标准: GB5023-2008, IEC60227-1997.
- 4) 耐压测试: 6KV
- 5) 最小绝缘电阻: 0.010 Ω /km (在 70°C时)
- 6) 导体材质: 纯铜
- 7) 护套材质: PVC (聚氯乙烯) / LSOH (低烟无汞)
- 8) 工作温度: -20 °C ~ 75 °C
- 9) 应用范围: 适用于交流电压 450/750V 及以下动力装置、日用电器、仪表及电信设备用的电缆电线

注意事项：

本产品适用于额定电压 450/750V 及以下的动力装置，固定布线使用



一般用途单芯铜导体聚氯乙烯绝缘软电线



RS 料号	截面积 (mm ²)	导体种类	绝缘厚度 (mm)	平均外径 上限 (mm)	电缆近似重量 (kg/km)	20℃导体 最大电阻 (Ω/km)	70℃最小绝 缘电阻 (MΩ/km)	颜色
1840150	0.5	5	0.6	2.6	8	39	0.013	红
1840151	0.5	5	0.6	2.6	8	39	0.013	白
1840153	0.5	5	0.6	2.6	8	39	0.013	蓝
1840154	0.5	5	0.6	2.6	8	39	0.013	绿
1840155	0.5	5	0.6	2.6	8	39	0.013	灰
1840156	0.5	5	0.6	2.6	8	39	0.013	黑
1840157	0.5	5	0.6	2.6	8	39	0.013	黄/绿
1856324	0.5	5	0.6	2.6	8	39	0.013	黄
1840158	0.75	5	0.6	2.8	11	26	0.011	红
1840159	0.75	5	0.6	2.8	11	26	0.011	白
1840160	0.75	5	0.6	2.8	11	26	0.011	蓝
1840161	0.75	5	0.6	2.8	11	26	0.011	绿
1840162	0.75	5	0.6	2.8	11	26	0.011	灰
1840163	0.75	5	0.6	2.8	11	26	0.011	黑
1840164	0.75	5	0.6	2.8	11	26	0.011	黄/绿
1856325	0.75	5	0.6	2.8	11	26	0.011	黄
1840165	1	5	0.6	3	13	19.5	0.01	红
1840166	1	5	0.6	3	13	19.5	0.01	白
1840167	1	5	0.6	3	13	19.5	0.01	蓝
1840169	1	5	0.6	3	13	19.5	0.01	绿
1840170	1	5	0.6	3	13	19.5	0.01	灰
1840171	1	5	0.6	3	13	19.5	0.01	黑
1840172	1	5	0.6	3	13	19.5	0.01	黄/绿
1856326	1	5	0.6	3	13	19.5	0.01	黄
1840173	1.5	5	0.7	3.5	19	18.1	0.011	红
1840175	1.5	5	0.7	3.5	19	18.1	0.011	白
1840176	1.5	5	0.7	3.5	19	18.1	0.011	蓝
1840177	1.5	5	0.7	3.5	19	18.1	0.011	绿
1840178	1.5	5	0.7	3.5	19	18.1	0.011	灰
1840179	1.5	5	0.7	3.5	19	18.1	0.011	黑
1840180	1.5	5	0.7	3.5	19	18.1	0.011	黄/绿
1856327	1.5	5	0.7	3.5	19	18.1	0.011	黄
1840181	2.5	5	0.8	4.2	30	7.41	0.01	红
1840182	2.5	5	0.8	4.2	30	7.41	0.01	白
1840183	2.5	5	0.8	4.2	30	7.41	0.01	蓝
1840184	2.5	5	0.8	4.2	30	7.41	0.01	绿

1840185	2.5	5	0.8	4.2	30	7.41	0.01	灰
1840186	2.5	5	0.8	4.2	30	7.41	0.01	黑
1840187	2.5	5	0.8	4.2	30	7.41	0.01	黄/绿
1856328	2.5	5	0.8	4.2	30	7.41	0.01	黄
1840188	4	5	0.8	4.8	46	4.61	0.0085	红
1840189	4	5	0.8	4.8	46	4.61	0.0085	白
1840190	4	5	0.8	4.8	46	4.61	0.0085	蓝
1840191	4	5	0.8	4.8	46	4.61	0.0085	绿
1840192	4	5	0.8	4.8	46	4.61	0.0085	灰
1840193	4	5	0.8	4.8	46	4.61	0.0085	黑
1840194	4	5	0.8	4.8	46	4.61	0.0085	黄/绿
1856329	4	5	0.8	4.8	46	4.61	0.0085	黄
1840195	6	5	0.8	6.3	67	3.08	0.007	红
1840197	6	5	0.8	6.3	67	3.08	0.007	白
1840198	6	5	0.8	6.3	67	3.08	0.007	蓝
1840199	6	5	0.8	6.3	67	3.08	0.007	绿
1840200	6	5	0.8	6.3	67	3.08	0.007	灰
1840201	6	5	0.8	6.3	67	3.08	0.007	黑
1840202	6	5	0.8	6.3	67	3.08	0.007	黄/绿
1856307	6	5	0.8	6.3	67	3.08	0.007	黄
1840204	10	5	1	7.6	121	1.94	0.0056	红
1840205	10	5	1	7.6	121	1.94	0.0056	白
1840206	10	5	1	7.6	121	1.94	0.0056	蓝
1840207	10	5	1	7.6	121	1.94	0.0056	绿
1840208	10	5	1	7.6	121	1.94	0.0056	灰
1840209	10	5	1	7.6	121	1.94	0.0056	黑
1840210	10	5	1	7.6	121	1.94	0.0056	黄/绿
1856330	10	5	1	7.6	121	1.94	0.0056	黄
1840211	16	5	1	8.8	170	1.25	0.0048	红
1840212	16	5	1	8.8	170	1.25	0.0048	白
1840213	16	5	1	8.8	170	1.25	0.0048	蓝
1840214	16	5	1	8.8	170	1.25	0.0048	绿
1840215	16	5	1	8.8	170	1.25	0.0048	灰
1840216	16	5	1	8.8	170	1.25	0.0048	黑
1840217	16	5	1	8.8	170	1.25	0.0048	黄/绿
1856331	16	5	1	8.8	170	1.25	0.0048	黄
1840218	25	5	1.2	11	268	0.78	0.0044	红
1840220	25	5	1.2	11	268	0.78	0.0044	白
1840221	25	5	1.2	11	268	0.78	0.0044	蓝
1840222	25	5	1.2	11	268	0.78	0.0044	绿
1840223	25	5	1.2	11	268	0.78	0.0044	灰
1840224	25	5	1.2	11	268	0.78	0.0044	黑
1840226	25	5	1.2	11	268	0.78	0.0044	黄/绿
1856332	25	5	1.2	11	268	0.78	0.0044	黄