

Features

- **Universal Fit** – Specifically designed to lock out ABB Series 200–290 miniature circuit breakers and MS325 rotary-style breakers.
- **Tool-Free Installation** – Enables quick and simple setup without requiring additional tools.
- **One-Handed Operation** – Spring-loaded push button allows for easy positioning and lockout with a single hand.
- **Secure Lockout** – Accepts padlocks (sold separately) to prevent unauthorized operation of the breaker.
- **Non-Conductive Material** – Constructed from glass-filled nylon for electrical insulation and durability.
- **Enhanced Safety Compliance** – Provides an effective method for isolating power during maintenance and servicing.

RS PRO Pin Out ABB Motor Protection Circuit Breaker Lockout

RS Stock No.: 0710495



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *Designed for use with ABB Series 200–290 and MS325 rotary-style breakers.*
- *Quick, tool-free installation using a spring-loaded push button for efficient lockout.*
- *Allows one-handed positioning for ease of use in tight or complex panels.*
- *Accepts a padlock to ensure full security and prevent breaker operation during maintenance.*
- *Made from non-conductive glass-filled nylon for safe electrical applications.*
- *Ideal for maintenance teams needing fast, secure, and code-compliant breaker isolation.*

General Specifications

| | |
|----------------------|-------------------------|
| Type | Circuit Breaker Lockout |
| Material | Nylon |
| Colour | Yellow, Black & Red |
| Padlock holes | 01 |
| Package | PE-LD |

Mechanical Specifications

| | |
|--|---------|
| A | 19.8mm |
| B | 44.5mm |
| C | 23.5mm |
| D | 3mm |
| Attachment Point Maximum Shackle Dia. (E) | 7mm |
| Weight | 6 Grams |

Operation Environment Specifications

| | |
|------------------------------|---------------|
| Withstand temperature | -20°C to 70°C |
|------------------------------|---------------|

