



IWLAN client, SCALANCE W721-1, RJ45, 1 radio, 1 R-SMA antenna port, IEEE 802.11a/b/g/h/n, 2.4/5 GHz, gross data rate 150 Mbit/s, 1x RJ45 max. 100 Mbit/s, 24 V DC, terminal block, IP20, 0... +55°C, WPA2/802.11i/e, observe national approvals! CERT ID: ELN-W1-RJ-E1, scope of delivery: Manuals on CD-ROM, German/English, 1x terminal block; for operation outside of USA/Israel

Transfer rate	
Transfer rate	
<ul style="list-style-type: none"> <li>with WLAN / maximum</li> </ul>	150 Mbit/s
<ul style="list-style-type: none"> <li>for Industrial Ethernet</li> </ul>	10, 100 Mbit/s
Transfer rate / for Industrial Ethernet	
<ul style="list-style-type: none"> <li>minimum</li> </ul>	10 Mbit/s
<ul style="list-style-type: none"> <li>maximum</li> </ul>	100 Mbit/s
Interfaces	
Number of electrical connections	
<ul style="list-style-type: none"> <li>for network components or terminal equipment</li> </ul>	1
<ul style="list-style-type: none"> <li>for power supply</li> </ul>	1
<ul style="list-style-type: none"> <li>for redundant voltage supply</li> </ul>	0
Type of electrical connection	
<ul style="list-style-type: none"> <li>for network components or terminal equipment</li> </ul>	RJ45 socket
<ul style="list-style-type: none"> <li>for power supply</li> </ul>	3-pole screw terminal
design of the removable storage	
<ul style="list-style-type: none"> <li>C-PLUG</li> </ul>	No
<ul style="list-style-type: none"> <li>KEY-PLUG</li> </ul>	No

Interfaces / wireless	
Number of radio cards / permanently installed	1
Number of electrical connections / for external antenna(s)	1
Type of electrical connection / for external antenna(s)	R-SMA (socket)
Product feature / external antenna can be mounted directly on device	Yes

Supply voltage, current consumption, power loss	
Type of voltage / of the supply voltage	DC
Supply voltage / 1 <ul style="list-style-type: none"> <li>• from terminal block</li> </ul>	19.2 V
Supply voltage / 2 <ul style="list-style-type: none"> <li>• from terminal block</li> </ul>	28.8 V
Consumed current <ul style="list-style-type: none"> <li>• at DC / at 24 V / typical</li> </ul>	0.15 A
Power loss [W] <ul style="list-style-type: none"> <li>• at DC / at 24 V / typical</li> </ul>	3.6 W

Ambient conditions	
Ambient temperature <ul style="list-style-type: none"> <li>• during operation</li> <li>• during storage</li> <li>• during transport</li> </ul>	0 ... 55 °C -40 ... +85 °C -40 ... +85 °C
Relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
Ambient condition / for operation	When used under hazardous conditions (Zone 2), the SCALANCE W761-1 RJ45 or W72x-1 RJ45 product must be installed in an enclosure. To comply with EN 50021, this enclosure must meet the requirements of at least IP 54 in compliance with EN 60529.
Protection class IP	IP20

Design, dimensions and weights	
Width	50 mm
Height	114 mm
Depth	74 mm
Width / of the enclosure / without antenna	50 mm
Height / of the enclosure / without antenna	114 mm
Depth / of the enclosure / without antenna	74 mm
Net weight	0.13 kg
Mounting type <ul style="list-style-type: none"> <li>• S7-300 rail mounting</li> <li>• S7-1500 rail mounting</li> <li>• 35 mm DIN rail mounting</li> <li>• wall mounting</li> </ul>	No No Yes No

## Radio frequencies

Operating frequency	
<ul style="list-style-type: none"> <li>• for WLAN in 2.4 GHz frequency band</li> </ul>	2.41 ... 2.48 GHz; depending on the country approvals
<ul style="list-style-type: none"> <li>• for WLAN in 5 GHz frequency band</li> </ul>	4.9 ... 5.8 GHz; depending on the country approvals

## Product features, product functions, product components / general

Product function / Access Point Mode	No
Product function / Client Mode	Yes
Product function	
<ul style="list-style-type: none"> <li>• iPCF client</li> </ul>	No
<ul style="list-style-type: none"> <li>• iPCF-MC client</li> </ul>	No
Product function / iREF	No
Product function / iPRP	No

## Product functions / management, configuration, engineering

Number of manageable IP addresses / in client	4
Product function	
<ul style="list-style-type: none"> <li>• CLI</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• web-based management</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• MIB support</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• TRAPs via email</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Configuration with STEP 7</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• configuration with STEP 7 in the TIA Portal</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• WDS</li> </ul>	No
Protocol / is supported	
<ul style="list-style-type: none"> <li>• Address Resolution Protocol (ARP)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• ICMP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Telnet</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• HTTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• HTTPS</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• TFTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• DCP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• LLDP</li> </ul>	No
Identification & maintenance function	
<ul style="list-style-type: none"> <li>• I&amp;M0 - device-specific information</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• I&amp;M1 – higher-level designation/location designation</li> </ul>	Yes

## Product functions / Diagnostics

Product function	
<ul style="list-style-type: none"> <li>• PROFINET IO diagnosis</li> </ul>	No
<ul style="list-style-type: none"> <li>• Link Check</li> </ul>	No
<ul style="list-style-type: none"> <li>• connection monitoring IP-Alive</li> </ul>	No
<ul style="list-style-type: none"> <li>• SysLog</li> </ul>	Yes

Protocol / is supported	
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes

#### Product functions / VLAN

Product function	
• function VLAN with IWLAN	No

#### Product functions / DHCP

Product function	
• DHCP client	Yes
• DHCP server	Yes
• DHCP Option 82	Yes

#### Product functions / redundancy

Protocol / is supported	
• STP/RSTP	Yes
• MSTP	Yes
• RSTP	Yes

#### Product functions / Security

Product function	
• ACL - MAC-based	Yes
• Management security, ACL-IP based	Yes
• IEEE 802.1x (radius)	Yes
• NAT/NAPT	No
• access protection according to IEEE802.11i	Yes
• WPA/WPA2	Yes
• TKIP/AES	Yes
Protocol / is supported	
• SSH	Yes
• RADIUS	Yes

#### Product functions / time

Protocol / is supported	
• NTP	Yes
• SNTP	Yes
• SIMATIC time synchronization (SIMATIC Time)	Yes

#### Standards, specifications, approvals

Standard	
• for FM	FM 3611: Class I, Division 2, Groups A,B,C,D, T4 / Class 1, Zone 2, Group IIC, T4
• for hazardous zone	EN 60079-15:2005, EN 60079-0:2006, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X

<ul style="list-style-type: none"> <li>• for safety / from CSA and UL</li> </ul>	UL 60950-1, CSA C22.2 No. 60950-1
<b>Certificate of suitability</b> <ul style="list-style-type: none"> <li>• EC declaration of conformity</li> <li>• CE marking</li> <li>• C-Tick</li> <li>• E1 approval</li> <li>• Railway application in accordance with EN 50155</li> <li>• NEMA TS2</li> <li>• IEC 61375</li> <li>• IEC 61850-3</li> <li>• NEMA4X</li> <li>• Power-over-Ethernet according IEEE802.3at for type 1 and IEEE802.3af</li> <li>• Power-over-Ethernet according to IEEE802.3at for type 2</li> </ul>	<ul style="list-style-type: none"> <li>Yes</li> <li>Yes</li> <li>Yes</li> <li>No</li> <li>No</li> <li>No</li> <li>No</li> <li>No</li> <li>No</li> <li>No</li> </ul>
<b>Standard for wireless communication</b> <ul style="list-style-type: none"> <li>• IEEE 802.11a</li> <li>• IEEE 802.11b</li> <li>• IEEE 802.11e</li> <li>• IEEE 802.11g</li> <li>• IEEE 802.11h</li> <li>• IEEE 802.11i</li> <li>• IEEE 802.11n</li> </ul>	<ul style="list-style-type: none"> <li>Yes</li> <li>Yes</li> <li>Yes</li> <li>Yes</li> <li>Yes</li> <li>Yes</li> <li>Yes</li> </ul>
<b>Wireless approval</b>	You will find the current list of countries at: <a href="http://www.siemens.de/funkzulassungen">www.siemens.de/funkzulassungen</a>
<b>Marine classification association</b> <ul style="list-style-type: none"> <li>• American Bureau of Shipping Europe Ltd. (ABS)</li> <li>• Bureau Veritas (BV)</li> <li>• DNV GL</li> <li>• Korean Register of Shipping (KRS)</li> <li>• Lloyds Register of Shipping (LRS)</li> <li>• Nippon Kaiji Kyokai (NK)</li> <li>• Polski Rejestr Statkow (PRS)</li> <li>• Royal Institution of Naval Architects (RINA)</li> </ul>	<ul style="list-style-type: none"> <li>No</li> <li>No</li> <li>No</li> <li>No</li> <li>No</li> <li>No</li> <li>No</li> <li>No</li> </ul>

### accessories

accessories	24 V DC screw terminal included in scope of delivery
-------------	--

### Further information / Internet-Links

<b>Internet-Link</b> <ul style="list-style-type: none"> <li>• to website: TIA Selection Tool</li> <li>• to the website: IWLAN</li> </ul>	<ul style="list-style-type: none"> <li><a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a></li> <li><a href="http://www.siemens.com/iwlan">http://www.siemens.com/iwlan</a></li> </ul>
--	--

- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<https://mall.industry.siemens.com>

<http://www.siemens.com/industry/infocenter>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

## Security information

### Security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

**last modified:**

05/28/2020