



ENGLISH

Datasheet

## RS Pro 12 Piece HSS Tap & Drill Set, M3 to M10

RS Stock No: **669-9404**



### Product Details


RS Pro 12-piece tap and drill set includes M3 to M10 die taps and 2.5 to 8.5 mm tapping drills. These tools are made of HSS for added durability. The tap and drill set is suitable for general workshop and engineering applications.

### Features and Benefits

- High speed steel taps and drills
- Ideal for general workshop and engineering applications
- Featuring popular sizes for hand or power tool usage

**Specifications:**

Material	HSS
Maximum Drill Size	8.5 mm
Maximum Tap Size	M10
Minimum Drill Size	2.5 mm
Minimum Tap Size	M3
Number of Pieces	12



**1/4in hexagon drive tap**

RS Stock Number	Manufacturer Part No.	Size	Pitch mm	Overall Length (L-1.5)mm	Flute Length (L-1.5)mm	Shank Length mm	Shank A/F mm	No. of flute	
6699372	T10500300	M3	0.5	32.5	9	15	6.35	3	
6699381	T10500400	M4	0.7	35.0	11	15	6.35	3	
6699384	T10500500	M5	0.8	35.0	14	15	6.35	3	
6699388	T10500600	M6	1.0	37.5	16	15	6.35	3	
6699397	T10500800	M8	1.25	40.4	18	15	6.35	4	
6699390	T10501000	M10	1.5	40.5	21	15	6.35	4	
6699394	T9061	6pcs (M3-M4-M5-M6-M8-M10)							
6699404	HT9120	6pcs drills(2.5-3.3-4.2-5.0-6.8-8.5) and 6pcs taps(M3-M4-M5-M6-M8-M10)							

Remarks:

Material: HSS M2