


■ GEBERIT



Example image

• For cold and hot potable water • For cooling and heating water without antifreeze agent • For cooling and heating water with antifreeze agent • For district heating water $\leq 120\text{ }^{\circ}\text{C}$ • For saturated steam $\leq 120\text{ }^{\circ}\text{C}$ • For service water and process water • For treated water • For grey and black water with a pH value ≥ 5.5	• For extinguishing water (wet/dry, dry) • For sprinklers (wet) • For chemicals and technical liquids • For compressed air (oil purity class 0–3) • For negative pressure • For inert gases (e.g. nitrogen) • For industrial gases (e.g. acetylene, shielding gases) • For technical building systems, industry and shipbuilding
--	---

- Pressing indicator
- Leaky if unpressed
- Seal ring made of CIIR, black

Product material	CrNiMo steel 1.4401 (EN 10088)
------------------	--------------------------------

Art. no.	DN	d ø mm	R "	L cm	H cm
81726	12 / 10	15	3/8	3.8	1.8
81703	12 / 15	15	1/2	4.1	2.1
81714	12 / 20	15	3/4	4.3	2.3
81704	15	18	1/2	4.2	2.2

Art. no.	DN	d _ø mm	R _e	L cm	H cm
81705	15 / 20	18	3/4	4.4	2.4
81715	20 / 15	22	1/2	4.2	2.1
81707	20	22	3/4	4.4	2.3
81716	20 / 25	22	1	4.6	2.5
81717	25 / 20	28	3/4	4.6	2.3
81708	25	28	1	4.8	2.3
81718	25 / 32	28	1 1/4	4.8	2.5
81719	32 / 25	35	1	5.1	2.5
81709	32	35	1 1/4	5.3	2.7
81720	32 / 40	35	1 1/2	5.3	2.7
81721	40 / 32	42	1 1/4	5.7	2.7
81710	40	42	1 1/2	5.7	2.7
81722	50 / 40	54	1 1/2	8.3	4.8

Art. no.	DN	d _ø mm	R "	L cm	H cm
81711	50	54	2	8.9	5.4
81713	65	76.1	2 1/2	12.3	7
81724	80	88.9	3	13.7	7.7