



www.eao.com



Series 61

Buzzer.

Both visual and audible signals provide direct feedback from equipment and machinery to interaction or status. EAO offers HMI products which fully meet the needs of users in relation to the operating conditions.

As a pioneer in the field of illuminated pushbuttons and an expert in Human Machine Interfaces (HMIs), EAO continues to set new standards in machine operability. The Series 61 buzzer is capable of meeting precisely the requirements demanded by industrial users. In addition to signals which use visual effects, feedback or warnings also need to be given in audible form if the operating systems are not always in the field of view of the operator.

The modern flush-mounting design matches the front appearance of EAO's Series 51, 61, 71 and 84. This enables a variety of flat pushbuttons to be combined in the same control panel while optimising the aesthetic appearance.

The innovative buzzer is especially suitable for machinery control panels, and is guaranteed for safe, reliable operation at temperatures of $-25\,^{\circ}\text{C}$ to $+55\,^{\circ}\text{C}$, even when exposed to spraying water.

Typical applications

- · Machinery and equipment
- · Process visualisation
- · Vehicle cockpits

Materials

The materials used are compliant with the strict EAO standards regarding quality, functional safety, service life and design.

Mechanical characteristics

- 2.8 x 0.5 mm plug-in connection
- Tightening torque for fixing nut max. 50 Ncm

Electrical characteristics

- Frequency (sound) approx. 2.0 kHz
- Interval frequency 2 Hz (for continuous tone use reverse polarity)
- Sound pressure level 88 dB (A) ±8 dB at 0.1 m distance (IP40)
- Sound pressure level 82 dB (A) ±8 dB at 0.1 m distance (IP65)
- Voltage/current consumption 10 VDC ... 26 VDC, ≤ 20 mA

Ambient conditions

Temperature

- Storage temperature $-40\,^{\circ}\text{C}$ to $+85\,^{\circ}\text{C}$
- Operating temperature -25 °C to +55 °C

Front protection

IP40 or IP65

Advantages.

- Flush, modern design
- IP40 or IP65 front protection
- Easy to mount
- Continuous or intermittent tone
- Reliable and proven technology

Colour of front

Plastic: Black RAL 9017Markings: White pad printed

Standards and directives


Declaration of Conformity

- CE
- RoHS


Mounting

The buzzer is mounted from the front of the panel with the aid of an anti-rotation device and the fixing nut. It is connected by means of two plug-in connectors, which can also be soldered. Continuous or intermittent tone can be controlled via the polarity of the connection.

Dimensions



Mounting cut-out





EAO reserves the right to change specifications without further notice.

EAO Contact.

Your centre of excellence.

Headquarters

EAO Holding AG

Tannwaldstrasse 88 CH-4600 Olten Telephone +41 62 286 92 00 info@eao.com

Manufacturing Companies

Switzerland

EAO AG Tannwaldstrasse 88 CH-4600 Olten Telephone +41 62 286 91 11 info@eao.com

EAO Systems AG Tannwaldstrasse 88 CH-4600 Olten Telephone +41 62 286 91 11 sales.esy@eao.com

China

EAO (Guangzhou) Ltd.
3/F, Block G4, South China
New Materials Innovation Park
31 Kefeng Road
Guangzhou Science City
CN-Guangzhou, PRC
Telephone +86 20 3229 0390
sales.ecn@eao.com

Germany

EAO Automotive GmbH & Co. KG Richard-Wagner-Straße 3 DE-08209 Auerbach/Vogtland Telephone +49 3744 8264 0 sales.esa@eao.com

North America

EAO Corporation One Parrott Drive Shelton US-CT 06484 Telephone +1 203 951 4600 sales.eus@eao.com

Sales Companies

China

EAO (Guangzhou) Ltd.
3/F, Block G4, South China
New Materials Innovation Park
31 Kefeng Road
Guangzhou Science City
CN-Guangzhou, PRC
Telephone +86 20 3229 0390
sales.ecn@eao.com

EAO (Shanghai) Office Rm.401, Lihpao Plaze, NO.159 Shenwu Road, Minhang District, CN-Shanghai, 201106. PRC Telephone +86 21 6095 0717 sales.ecn@eao.com

France

EAO France SAS Nextdoor – Bâtiment Silex 15 rue des Cuirassiers CS 33821 FR-69487 Lyon Cedex O3 Telephone +33 9 74 18 93 41 sales.efr@eao.com

Germany, Austria, Czech Republic,

Poland, Slovakia

EAO GmbH Langenberger Straße 570 DE-45277 Essen Telephone +49 201 8587 0 sales.ede@eao.com

Hong Kong (Asia Pacific)

EAO (Far East) Ltd. Unit A1, 1/F, Block A Tin On Industrial Building 777 Cheung Sha Wan Road Lai Chi Kok, Kln HK-Hong Kong Telephone +852 27 86 91 41 sales.ehk@eao.com

Italy

EAO Italia S.r.I.
Centro Direzionale Summit –
Palazzo D1
Via Brescia 28
IT-20063 Cernusco sul Naviglio (MI)
Telephone +39 029 247 0722
sales.eit@eao.com

Japan

EAO Japan Co. Ltd. Net 1 Mita Bldg. 3F 3-1-4 Mita Minato-ku JP-Tokyo 108-0073 Telephone +81 3 5444 5411 sales.ejp@eao.com

Netherlands, Belgium

EAO Benelux B.V. Kamerlingh Onnesweg 46 NL-3316 GL Dordrecht Telephone +31 78 653 17 00 sales.enl@eao.com

North America

EAO Corporation One Parrott Drive Shelton US-CT 06484 Telephone +1 203 951 4600 sales.eus@eao.com

Switzerland

EAO Schweiz AG Tannwaldstrasse 86 CH-4600 Olten Telephone +41 62 286 95 00 sales.ech@eao.com

United Kingdom, Denmark, Finland, Ireland, Norway, Sweden

EAO Ltd.
Highland House
Albert Drive
Burgess Hill
GB-West Sussex RH15 9TN
Telephone +44 1444 236 000
sales.euk@eao.com