WWW.PHIHONG.COM



65 Watt* Open-Frame Power Supply PSA065 Single Output 2" x 4" Series (for ITE)



 ϵ



*45W Convection, 65W 20CFM Airflow cooling

Features

• 2 x 4 Footprint

• Low-Cost

• Low Profile Design Fits 1U Applications

Applications

• Telecom/Datacom

• Industrial

• Peripherals

Safety Approvals

• cUL/UL 60601-1

• IEC 60601-1

• CE (Low Voltage Directive)

Mechanical Characteristics

Length: 101.6mm (4.0in)Width: 50.8mm (2.0in)

Height: 30.6mm (1.2in)Weight: 160g (5.64oz)

Output Specifications

Model	DC Output	Line			Ripple (1) Regula		lation
	Voltage	Min.	Convection	20cfm	P-P (max)	Line	Load
PSA065-120	+12V	0A	3.75	5.42A	120mV	±2%	±2%
PSA065-240	+24V	0A	1.88	2.71A	240mV	±2%	±2%
PSA065-480	+48V	0A	0.94	1.36A	480mV	±2%	±2%

⁽¹⁾ Measured by using a 12 inch twisted pair terminated with a 10uF capacitor and a 0.1uF ceramic in parallel, measured at maximum load after a 20 minute warm up and bandwidth set to 20MHz.

Phihong is not responsible for any error, and reserves the right to make changes without notice. Please visit our website at www.phihong.com for the most up-to-date specifications and contact information.

PSA065 Characteristics

WWW.PHIHONG.COM

Input:

AC Input Voltage Rating

100 to 240V AC

AC Input Voltage Range

90 to 264V AC

AC Input Frequency

47 to 63Hz

Input Current

1.5A at maximum load and 115V AC 0.75A at maximum load and 230V AC

Leakage Current

100uA maximum at 264V AC

Inrush Current

30A for 1150V AC at maximum load 60A for 230V AC at maximum load

(Cold start at ambient 25°C)

Hold-up Time

10mS typical at maximum load and 115V AC

Output:

Efficiency

80% minimum at maximum load and 115V AC

Over-Voltage Protection

+48V DC at +72V DC maximum

Over-Current Protection

Auto-restart

Input Protection

Fuse in line and neutral

Environmental:

Temperature

Operation 0 to 50°C Non-operation -25 to +85°C Humidity

Operation 5 to 95% non-condensing

Emissions

FCC Class B EN55022 Class B

Immunity

EN55024 1998 EN61000-4-2 Level 3 EN61000-4-3 Level 2 EN61000-4-4 Level 3 EN61000-4-5 Level 3 EN61000-4-6 Level 2

EN61000-4-11

EN61000-3-2 Harmonic Class A

EN61000-3-3 Flicker

General:

Insulation Resistance

10M Ohm minimum, 500V DC

Dielectric Withstand (Hi-pot) Test

Input to Ground: 1600V AC for 3 seconds, 10mA Input to Output: 4200V AC for 3 seconds, 10mA

Switching Frequency

50K Hz typical

MTBF (Full load and 110V AC, 25°C)


>100K Hrs


Input Connector

Molex 09-51-4034 housing with Molex 08-50-0106 pins

DC Output Connector

Molex 26-03-4041 housing with Molex 08-50-0189 pins.





CN2. OUTPUT CONNECTOR

DIAZ.	0011 01 001
PIN	DESCRIPTION
1	RTN
2	RTN
3	V+
4	V+

