

SAFETY DATA SHEET

Eco-Rite(TM) Multi-Purpose Cleaner

RS REACH revision date 01/09/11

1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

Identification of the substance or mixture

Product name : Eco-Rite(TM) Multi-Purpose Cleaner
 Synonyms : ES3277
 Product type : Liquid.
 Use of the substance/mixture : Cleaning Products

Company/undertaking identification

Manufacturer : ITW Chemtronics
 8125 Cobb Center Drive
 Kennesaw, GA 30152
 Tel. 770-424-4888 or toll free 800-645-5244

Distributor : RS Components Ltd,
 Birchington Road, Corby, Northants, NN17 9RS.
 Tel: +44 (0) 1536 402888 (8am to 8pm)
 Email: technical.help@rs-components.com

Importer : ITW Contamination Control BV
 Saffierlaan 5
 VZ-2132 Hoofddorp
 The Netherlands

Tel: +31 88 1307 400
 FAX: +31 88 1307 499

e-mail address of person responsible for this SDS : askchemtronics@chemtronics.com

Emergency telephone number (with hours of operation) : Chemtrec - 1-800-424-9300 or collect 703-527-3887

2. HAZARDS IDENTIFICATION

The product is not classified as dangerous according to Directive 1999/45/EC and its amendments.

Classification : Not classified.

See Section 11 for more detailed information on health effects and symptoms.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance/preparation : Mixture

There are no ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

4. FIRST AID MEASURES

First-aid measures

Inhalation : Remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical attention if symptoms occur.

Ingestion : Wash out mouth with water. Remove victim to fresh air and keep at rest in a position comfortable for breathing. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Do not induce vomiting unless directed to do so by medical personnel. Get medical attention if symptoms occur.

Skin contact : Flush contaminated skin with plenty of water. Remove contaminated clothing and shoes. Get medical attention if symptoms occur.

Eye contact : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Get medical attention if irritation occurs.

Protection of first-aiders : No action shall be taken involving any personal risk or without suitable training.

Notes to physician : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.

See Section 11 for more detailed information on health effects and symptoms.

5. FIRE-FIGHTING MEASURES

Extinguishing media

Suitable : Use an extinguishing agent suitable for the surrounding fire.

Not suitable : None known.

Special exposure hazards : In a fire or if heated, a pressure increase will occur and the container may burst. Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.

Hazardous thermal decomposition products : Decomposition products may include the following materials:
 carbon dioxide
 carbon monoxide

5. FIRE-FIGHTING MEASURES

- Special protective equipment for fire-fighters** : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode. Clothing for fire-fighters (including helmets, protective boots and gloves) conforming to European standard EN 469 will provide a basic level of protection for chemical incidents.

6. ACCIDENTAL RELEASE MEASURES

- Personal precautions** : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilled material. Put on appropriate personal protective equipment (see Section 8).
- Environmental precautions** : Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).
- Methods for cleaning up**
- Small spill** : Stop leak if without risk. Move containers from spill area. Dilute with water and mop up if water-soluble. Alternatively, or if water-insoluble, absorb with an inert dry material and place in an appropriate waste disposal container. Dispose of via a licensed waste disposal contractor.
- Large spill** : Stop leak if without risk. Move containers from spill area. Prevent entry into sewers, water courses, basements or confined areas. Wash spillages into an effluent treatment plant or proceed as follows. Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations. Dispose of via a licensed waste disposal contractor.

7. HANDLING AND STORAGE

- Handling** : Put on appropriate personal protective equipment (see Section 8). Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas.
- Storage** : Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabelled containers. Use appropriate containment to avoid environmental contamination.
- Packaging materials**
- Recommended** : Use original container.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Exposure limit values

Ingredient name	Occupational exposure limits
No exposure limit value known.	

- Recommended monitoring procedures** : If this product contains ingredients with exposure limits, personal, workplace atmosphere or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment. Reference should be made to European Standard EN 689 for methods for the assessment of exposure by inhalation to chemical agents and national guidance documents for methods for the determination of hazardous substances.
- Exposure controls**
- Occupational exposure controls** : No special ventilation requirements. Good general ventilation should be sufficient to control worker exposure to airborne contaminants. If this product contains ingredients with exposure limits, use process enclosures, local exhaust ventilation or other engineering controls to keep worker exposure below any recommended or statutory limits.
- Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.
- Respiratory protection** : Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.
- Hand protection** : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.
- Eye protection** : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists or dusts.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

- Skin protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Environmental exposure controls** : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

9. PHYSICAL AND CHEMICAL PROPERTIESGeneral informationAppearance

- Physical state** : Liquid.
- Colour** : Green.
- Odour** : Lemon-like. [Slight]

Important health, safety and environmental information

- pH** : 9.68
- Boiling point** : Lowest known value: 100°C (212°F) (water).
- Melting point** : May start to solidify at the following temperature: 0°C (32°F) This is based on data for the following ingredient: water.

Evaporation rate (butyl acetate = 1) : <1 compared with butyl acetate

10. STABILITY AND REACTIVITY

- Stability** : The product is stable.
- Conditions to avoid** : No specific data.
- Materials to avoid** : No specific data.
- Hazardous decomposition products** : Under normal conditions of storage and use, hazardous decomposition products should not be produced.

11. TOXICOLOGICAL INFORMATIONPotential acute health effects

- Inhalation** : No known significant effects or critical hazards.
- Ingestion** : No known significant effects or critical hazards.
- Skin contact** : No known significant effects or critical hazards.
- Eye contact** : No known significant effects or critical hazards.

Acute toxicityPotential chronic health effects

- Chronic effects** : No known significant effects or critical hazards.
- Carcinogenicity** : No known significant effects or critical hazards.
- Mutagenicity** : No known significant effects or critical hazards.
- Teratogenicity** : No known significant effects or critical hazards.
- Developmental effects** : No known significant effects or critical hazards.
- Fertility effects** : No known significant effects or critical hazards.

Over-exposure signs/symptoms

- Inhalation** : No specific data.
- Ingestion** : No specific data.
- Skin** : No specific data.
- Eyes** : No specific data.

12. ECOLOGICAL INFORMATION

- Environmental effects** : No known significant effects or critical hazards.
- Aquatic ecotoxicity
- Conclusion/Summary** : Not available.
- Biodegradability
- Conclusion/Summary** : Not available.
- Other adverse effects** : No known significant effects or critical hazards.

13. DISPOSAL CONSIDERATIONS

- Methods of disposal** : The generation of waste should be avoided or minimised wherever possible. Significant quantities of waste product residues should not be disposed of via the foul sewer but processed in a suitable effluent treatment plant. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Empty containers or liners may retain some product residues. Avoid

13. DISPOSAL CONSIDERATIONS

dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers.

Hazardous waste

: Within the present knowledge of the supplier, this product is not regarded as hazardous waste, as defined by EU Directive 91/689/EEC.

14. TRANSPORT INFORMATIONInternational transport regulations

Regulatory information	UN number	Proper shipping name	Classes	PG*	Label	Additional information
ADR/RID Class	Not available.	Not available.	Not available.	-		-
ADN/ADNR Class	Not available.	Not available.	Not available.	-		-
IMDG Class	Not available.	Not available.	Not available.	-		-
IATA Class	Not available.	Not available.	Not available.	-		-

PG* : Packing group

15. REGULATORY INFORMATIONEU regulations

Classification and labeling have been determined according to EU Directives 67/548/EEC and 1999/45/EC (including amendments) and take into account the intended product use.

Risk phrases

: This product is not classified according to EU legislation.

Product use

: Professional applications.

Europe inventory

: All components are listed or exempted.

16. OTHER INFORMATIONHistory**Date of printing**

: 5/9/2011.

Date of issue/Date of revision

: 5/9/2011.

Date of previous issue

: No previous validation.

Version

: 21

Prepared by

: Not available.

☑ Indicates information that has changed from previously issued version.

Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.