

1554649

https://www.phoenixcontact.com/gb/products/1554649

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, Universal, 4-position, Socket, straight, M12-Standard, coding: A, on free cable end, Front mounting, Pg9, Individual wires, cable length: 0.5 m, 0.34 mm<sup>2</sup>, TPE

### Your advantages

- · Preassembled with litz wires for immediate use
- · Customer-specific assemblies and litz wire lengths available
- · Sealed on the litz wire side for optimum leak-tightness
- · All standard pin assignments and codings for signal, data, and power transmission with a uniform design-in design
- · For high transmission safety: shield connection to the housing with optional EMC nut

### Commercial data

Item number	1554649
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ABQCVE
Product key	ABQCVE
Catalog page	Page 268 (C-2-2013)
GTIN	4046356170260
Weight per piece (including packing)	37.2 g
Weight per piece (excluding packing)	25.8 g
Customs tariff number	85444290
Country of origin	DE



1554649

https://www.phoenixcontact.com/gb/products/1554649

#### Technical data

#### **Notes**

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Order information:	Lock nut is included in the scope of delivery
General	Contact connection method: Crimp connection

#### Safety note

Sa	tety	no	te

WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.

- WARNING: Commission properly functioning products only.
   The products must be regularly inspected for damage.
   Decommission defective products immediately. Replace damaged products. Repairs are not possible.
- WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.
- The products are suitable for applications in plant, controller, and electrical device engineering.
- When operating the connectors in outdoor applications, they must be separately protected against environmental influences.
- Assembled products may not be manipulated or improperly opened.
- Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products).
- When using the product in direct connection with third-party manufacturers, the user is responsible.
- For operating voltages > 50 V AC, conductive connector housings must be grounded
- Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.
- Observe the corresponding technical data. You will find information:
- o On the product
- o On the packing label
- o In the supplied documentation
- o Online at phoenixcontact.com/products under the product
- Only use tools recommended by Phoenix Contact
- Use a protective cap to protect connectors that are not in use.



1554649

https://www.phoenixcontact.com/gb/products/1554649

	The suitable accessories are available online in the accessory section of the product at phoenixcontact.com/products
	<ul> <li>Ensure that the protective or functional ground has been properly connected.</li> </ul>
	VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector
	<ul> <li>The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).</li> </ul>
lounting	
Mounting type	Front mounting Pg9 With locking nut
Assembly note	With locking nut
roduct properties	
Product type	Circular connectors (device side)
Application	Signal
Sensor type	Universal
Number of positions	4
No. of cable outlets	1
Shielded	no
Coding	A
Thread type	M12
Data management status	
Article revision	09
Insulation characteristics	
Overvoltage category	II
Degree of pollution	3
laterial specifications	
Flammability rating according to UL 94	V0
Seal material	NBR
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 66 GF
Material for screw connection	Stainless steel
Conductor material	Tin-plated Cu litz wires
lectrical properties	
Rated surge voltage	2.5 kV
Contact resistance	≤ 3 mΩ



1554649

https://www.phoenixcontact.com/gb/products/1554649

Nominal voltage U <sub>N</sub>	250 V (AC)
	250 V (DC)
Nominal current I <sub>N</sub>	4 A
Max. conductor resistance	57.6 Ω/km

#### Connection data

#### Conductor connection

Connection method	Individual wires
Contact connection type	Socket
Conductor cross section	0.34 mm²
Tightening torque	2 Nm 3 Nm (Installation-side)

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	> 100
meetical, maranara, ejelee	.00

#### Connector

#### Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Head locking type	Standard
Coding	A

#### Connection 2

Head design free cable end	
----------------------------	--

### Cable/line

Cable length	0.5 m
Cable type	TPE litz wire
Signal type/category	Universal
Wire diameter incl. insulation	1.2 mm ±0.07 mm
Single wire, color	brown, white, blue, black
Cable cross section	0.34 mm²
Conductor material	Tin-plated Cu litz wires
Conductor structure signal line	7x 0.25 mm
AWG signal line	22
Material wire insulation	TPE
Thickness, insulation	0.21 mm (Core insulation)
Nominal voltage, cable	300 V
Test voltage, cable	2000 V AC
Cable resistance	≤ 57.6 Ω/km



1554649

https://www.phoenixcontact.com/gb/products/1554649

Cable insulation resistance	≥ 20 MΩ*km
Ambient temperature (operation)	-40 °C 85 °C (cable, fixed installation)
	-25 °C 85 °C (Cable, flexible installation)

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65/IP67/IP69/IP69K
	IP65/IP67/IP69K
Ambient temperature (operation)	-25 °C 85 °C (Plug / socket)
	-40 °C 85 °C (without mechanical actuation)
	-25 °C 85 °C (Cable, flexible installation)
	-40 °C 85 °C (cable, fixed installation)

### Standards and regulations

#### M12

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101




1554649

https://www.phoenixcontact.com/gb/products/1554649

## Drawings

### Circuit diagram







1554649

https://www.phoenixcontact.com/gb/products/1554649

### Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side





1554649

https://www.phoenixcontact.com/gb/products/1554649

## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/gb/products/1554649

cUL Recognized Approval ID: E118976-20100522				
	Nominal	voltage U <sub>N</sub> Nominal cu	rrent I <sub>N</sub> Cross section AV	VG Cross section mm <sup>2</sup>
	250 V	4 A	22 - 22	-

<b>7.1</b>	UL Recognized Approval ID: E118976-20100522					
		Nominal voltage U <sub>N</sub>	Nominal current I <sub>N</sub>	Cross section AWG	Cross section mm <sup>2</sup>	
		250 V	4 A	22 - 22	-	

e <b>Flus</b> cU	cULus Recognized Approval ID: E221474-20140616				
	Nom	inal voltage U <sub>N</sub>	Nominal current I <sub>N</sub>	Cross section AWG	Cross section mm <sup>2</sup>
	250 \	V	4 A	22 - 20	-

cULus Recognized



1554649

https://www.phoenixcontact.com/gb/products/1554649

### Classifications

### **ECLASS**

	ECLASS-11.0	27440102		
	ECLASS-12.0	27440116		
	ECLASS-13.0	27440116		
ETIM				
	ETIM 9.0	EC002635		
UNSPSC				
	UNSPSC 21.0	39121400		



1554649

https://www.phoenixcontact.com/gb/products/1554649

## Environmental product compliance

#### EU RoHS

25 1616				
Fulfills EU RoHS substance requirements	Yes, No exemptions			
China RoHS				
Environment friendly use period (EFUP)	EFUP-E			
	No hazardous substances above the limits			
EU REACH SVHC				
REACH candidate substance (CAS No.)	No substance above 0.1 wt%			

Phoenix Contact 2024 © - all rights reserved https://www.phoenixcontact.com

PHOENIX CONTACT Ltd Halesfield 13, Telford Shropshire, TF7 4PG 01952 681700 info@phoenixcontact.co.uk