

SECTION 1: Identification of the substance/mixture and of the company/undertaking

· 1.1 Product identifier

· Trade name: 838AR

· Other Means of Identification: 838AR Total Ground™ Carbon Conductive Paint

· Related Part Number:

838AR-Liquid, 838AR-15ML, 838AR-15MLCA, 838AR-55ML, 838AR-900ML, 838AR-3.78L, 838AR-18.9L

· UFI: DXJ0-N0W4-800H-NG7W

· 1.2 Relevant identified uses of the substance or mixture and uses advised against

· Application of the substance / the mixture Electrically conductive coating and EMI/RFI shield.

· Uses advised against Not applicable

· 1.3 Details of the supplier of the safety data sheet

· Manufacturer/Supplier:

MG Chemicals Ltd. (Head Office)
1210 Corporate Drive
Burlington, Ontario L7L 5R6
CANADA
+(1) 905-331-1396
info@mgchemicals.com

MG Chemicals
Heame House, 23 Bliston Street
Sedgely Dudley DY3 1JA.
United Kingdom
+(44) 1663 362888

MG Chemicalst Ltd.
Level 2, Vision Exchange, Building Territorials Street,
Zone 1, Central Business, District,
Birkirkara CBD 1070,
MALTA

· Further information obtainable from: sds@mgchemicals.com

· 1.4 Emergency telephone number:

Verisk 3E (Access code: 335388)
+(44) 20 3514787
+(1) 760 476 3961
UK Toll free: +(0) 800 680 0425

Members of the public seeking specific information on poisons should contact:
In England and Wales: NHS 111 - dial 111
In Scotland: NHS 24 - dial 111

SECTION 2: Hazards identification

· 2.1 Classification of the substance or mixture

· Classification according to Regulation (EC) No 1272/2008



GHS02 flame

Flam. Liq. 2 H225 Highly flammable liquid and vapour.

(Contd. on page 2)

— GB —

Trade name: 838AR

(Contd. of page 1)



GHS08 health hazard

Carc. 2 H351 Suspected of causing cancer. Route of exposure: Inhalation.



GHS05 corrosion

Eye Dam. 1 H318 Causes serious eye damage.



GHS07

Skin Sens. 1 H317 May cause an allergic skin reaction.

STOT SE 3 H336 May cause drowsiness or dizziness.

2.2 Label elements

Labelling according to Regulation (EC) No 1272/2008

The product is classified and labelled according to the GB CLP regulation.

Hazard pictograms



GHS02



GHS05



GHS07



GHS08

Signal word Danger

Hazard-determining components of labelling:

acetone
butan-1-ol
Carbon black
barium bis(dinonylnaphthalenesulfonate)

Hazard statements

H225 Highly flammable liquid and vapour.
H318 Causes serious eye damage.
H317 May cause an allergic skin reaction.
H351 Suspected of causing cancer. Route of exposure: Inhalation.
H336 May cause drowsiness or dizziness.

Precautionary statements

P102 Keep out of reach of children.
P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P280 Wear protective gloves, protective clothing, and eye protection.
P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P310 Immediately call a POISON CENTER/doctor.
P403+P235 Store in a well-ventilated place. Keep cool.
P501 Dispose of contents and container in accordance with local, regional, and national regulations.

Additional information:

EUH066 Repeated exposure may cause skin dryness or cracking.

(Contd. on page 3)

— GB —

Trade name: 838AR

(Contd. of page 2)

· **2.3 Other hazards**

· **Results of PBT and vPvB assessment**

- **PBT:** Not applicable.
- **vPvB:** Not applicable.

· **Determination of endocrine-disrupting properties** Endocrine Disruptor substance $\geq 0.1\%$ = none

SECTION 3: Composition/information on ingredients

· **3.2 Mixtures**

· **Description:** Mixture of substances listed below with nonhazardous additions.

· **Dangerous components:**

CAS: 67-64-1 EINECS: 200-662-2 Index number: 606-001-00-8	acetone ⚠ Flam. Liq. 2, H225; ⚠ Eye Irrit. 2, H319; STOT SE 3, H336, EUH066	36.0%
CAS: 110-19-0 EINECS: 203-745-1 Index number: 607-026-00-7	isobutyl acetate ⚠ Flam. Liq. 2, H225, EUH066	30.0%
CAS: 71-36-3 EINECS: 200-751-6 Index number: 603-004-00-6	butan-1-ol ⚠ Flam. Liq. 3, H226; ⚠ Eye Dam. 1, H318; ⚠ Acute Tox. 4, H302; Skin Irrit. 2, H315; STOT SE 3, H335-H336	10.0%
CAS: 1333-86-4 EINECS: 215-609-9	Carbon black ⚠ Carc. 2, H351, EUH066	6.0%
CAS: 108-65-6 EINECS: 203-603-9 Index number: 607-195-00-7	2-methoxy-1-methylethyl acetate ⚠ Flam. Liq. 3, H226; ⚠ STOT SE 3, H336	4.0%
CAS: 25619-56-1 EINECS: 247-132-7	barium bis(dinonylnaphthalenesulfonate) ⚠ Acute Tox. 4, H302; Acute Tox. 4, H332; Skin Irrit. 2, H315; Eye Irrit. 2, H319; Skin Sens. 1, H317	0.5%

· **Additional information:** For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

· **4.1 Description of first aid measures**

· **After inhalation:**

Remove person to fresh air and keep comfortable for breathing.
If feeling unwell: Call a POISON CENTRE or doctor.
If exposed or concerned: Get medical advice/attention.

· **After skin contact:**

Wash with plenty water.
If skin irritation or rash occurs: Get medical advice or attention.
Take off contaminated clothing and wash it before reuse.
If exposed or concerned: Get medical advice or attention.

· **After eye contact:**

Rinse cautiously with water for at least 30 minutes. Remove contact lenses, if present and easy to do.
Continue rinsing.
Immediately call a POISON CENTER or doctor.

· **After swallowing:**

Rinse mouth.
Do NOT induce vomiting.
If symptoms persist consult doctor.

(Contd. on page 4)

Trade name: 838AR

If exposed or concerned: Get medical advice or attention.

(Contd. of page 3)

· **4.2 Most important symptoms and effects, both acute and delayed**

No further relevant information available.

· **4.3 Indication of any immediate medical attention and special treatment needed**

No further relevant information available.

SECTION 5: Firefighting measures

· **5.1 Extinguishing media**

· **Suitable extinguishing agents:**

CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

· **For safety reasons unsuitable extinguishing agents:** Water with full jet

· **5.2 Special hazards arising from the substance or mixture**

Vapors are heavier than air. Vapors may travel to sources of ignition near the ground. They can cause flash fire or ignite explosively.

Produces irritating and toxic fumes in fires or in contact with hot surfaces.

Prevent fire-fighting wash from entering waterway or sewer system.

· **Hazardous combustion products:**

Carbon Oxides (CO_x)

other toxic fumes

· **5.3 Advice for firefighters**

· **Protective equipment:** Wear self-contained breathing apparatus and full fire-fighting turn-out gear.

SECTION 6: Accidental release measures

· **6.1 Personal precautions, protective equipment and emergency procedures**

Wear protective equipment. Keep unprotected persons away.

Ensure adequate ventilation

Remove or keep away all sources of extreme heat or open flames.

Avoid breathing mist, spray, or vapors.

· **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.

· **6.3 Methods and material for containment and cleaning up:**

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

Collect liquid in a sealable, chemical-resistant container.

Wash residue with a paper towel and place dirty towels in container.

Use soap and water to remove the last traces of residue.

· **6.4 Reference to other sections**

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

SECTION 7: Handling and storage

· **7.1 Precautions for safe handling**

Wear protective gloves and eye protection.

Wash hands and exposed skin thoroughly after handling.

Take off contaminated clothing and wash it before reuse.

(Contd. on page 5)

— GB —

Trade name: 838AR

(Contd. of page 4)

Contaminated work clothing should not be allowed out of the workplace.

Avoid breathing mist, spray, or vapors.

Use only outdoors or in a well-ventilated area.

Obtain, read and follow all safety instructions before use.

· **Information about fire - and explosion protection:**

Keep ignition sources away - Do not smoke.

Protect against electrostatic charges.

Use explosion-proof apparatus / fittings and spark-proof tools.

Ground and bond container and receiving equipment.

· **7.2 Conditions for safe storage, including any incompatibilities**

· **Storage:**

· **Requirements to be met by storerooms and receptacles:**

Store in a cool location.

Keep in a dry and clean area, away from incompatible substances

· **Information about storage in one common storage facility:** Not required.

· **Further information about storage conditions:**

Keep container tightly sealed.

Store in cool, dry conditions in well sealed receptacles.

Store locked up.

· **7.3 Specific end use(s)** See section 1.2

SECTION 8: Exposure controls/personal protection

· **8.1 Control parameters**

· Ingredients with limit values that require monitoring at the workplace:	
67-64-1 acetone	
WEL	Short-term value: 3620 mg/m ³ , 1500 ppm Long-term value: 1210 mg/m ³ , 500 ppm
110-19-0 isobutyl acetate	
WEL	Short-term value: 903 mg/m ³ , 187 ppm Long-term value: 724 mg/m ³ , 150 ppm
71-36-3 butan-1-ol	
WEL	Short-term value: 154 mg/m ³ , 50 ppm Sk
1333-86-4 Carbon black	
WEL	Short-term value: 7 mg/m ³ Long-term value: 3.5 mg/m ³
108-65-6 2-methoxy-1-methylethyl acetate	
WEL	Short-term value: 548 mg/m ³ , 100 ppm Long-term value: 274 mg/m ³ , 50 ppm Sk

· **Additional information:**

The lists valid during the making were used as basis.

Refer to the national or regional occupational exposure limit regulation for abbreviations and acronyms.

· **8.2 Exposure controls**

· **Appropriate engineering controls** No further data; see section 7.

· **Individual protection measures, such as personal protective equipment**

· **General protective and hygienic measures:**

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing

(Contd. on page 6)

Trade name: 838AR

(Contd. of page 5)

Wash hands before breaks and at the end of work.

Avoid contact with the eyes and skin.

· **Respiratory protection:**

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.

Advice should be sought from respiratory protection specialists.

If the product is heated or worker has a known allergic reaction, consider using a full mask with organic vapor cartridge or with an independent air supply.

· **Hand protection**

For Incidental Contact: Type = Nitrile ; Permeation 3 (> 360 min); Min. Thickness = 0.11 mm ; EN 374-2

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.



Protective gloves: EN374

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation. Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye/face protection**



Safety glasses or tightly sealed goggles: EN 166

SECTION 9: Physical and chemical properties

· 9.1 Information on basic physical and chemical properties

· Physical state	Liquid
· Form:	Viscous
· Colour:	Black
· Odour:	Solvent-like
· Odour threshold:	Not determined.
· Melting point/freezing point:	Undetermined.
· Boiling point or initial boiling point and boiling range	56 °C
· Flammability	Highly flammable.
· Lower and upper explosion limit	
· Lower:	2.4 Vol %
· Upper:	12.7 Vol %
· Flash point:	-17 °C (67-64-1 acetone)
· Auto-ignition temperature:	465 °C
· Decomposition temperature:	Not determined.

(Contd. on page 7)

Trade name: 838AR

(Contd. of page 6)

· pH	Not determined.
· Viscosity:	
· Kinematic viscosity	Not determined.
· Dynamic:	Not determined.
· Solubility	
· water:	Partly miscible.
· Partition coefficient n-octanol/water (log value)	Not determined.
· Vapour pressure at 50 °C:	800 hPa
· Relative density at 25 °C:	0.89
· Vapour density (air=1):	≥2
· Particle characteristics	Not applicable.
· 9.2 Other information	
· 9.2.1 Information with regard to physical hazard classes	
· Flammable liquids	Highly flammable liquid and vapour.
· 9.2.2 Other safety characteristics	
· Evaporation rate	<1 (ButAc=1)
· Ignition temperature:	Product is not selfigniting.
· Explosive properties:	Product is not explosive. However, formation of explosive air/vapour mixtures are possible.
· Solvent content:	
· Organic solvents:	80.00 %
· VOC (EC)	80.00 %
· Solids content:	19.5 %

SECTION 10: Stability and reactivity

· 10.1 Reactivity

Acetone reacts exothermically with phosphorous oxychloride, which can lead to an explosion.

· 10.2 Chemical stability

Chemically stable at normal temperatures and pressures.

· Thermal decomposition / conditions to be avoided:

No decomposition if used according to specifications.

· 10.3 Possibility of hazardous reactions

No dangerous reactions known.

· 10.4 Conditions to avoid

Avoid open flames, excessive heat, sparks, ignition sources, and incompatible substances.

· 10.5 Incompatible materials:

Strong oxidizing agents

Strong bases

Acids

Strong reducing agents

· 10.6 Hazardous decomposition products:

No dangerous decomposition products known.

Hazardous combustion products: see section 5.

— GB —

(Contd. on page 8)

Trade name: 838AR

(Contd. of page 7)

SECTION 11: Toxicological information

11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

- Acute toxicity Based on available data, the classification criteria are not met.

LD/LC50 values relevant for classification:		
ATE (Acute Toxicity Estimates)		
Oral	LD50	7,900 mg/kg (rat)
67-64-1 acetone		
Oral	LD50	5,800 mg/kg (rat)
Dermal	LD50	>7,426 mg/kg (rabbit)
Inhalative	LC50/ 3 h	132 mg/L (rat)
110-19-0 isobutyl acetate		
Oral	LD50	13,400 mg/kg (rat)
71-36-3 butan-1-ol		
Oral	LD50	790 mg/kg (rat)
Dermal	LD50	3,400 mg/kg (rabbit)
Inhalative	LC50/4 h	8,000 mg/L (rat)
1333-86-4 Carbon black		
Oral	LD50	>15,400 mg/kg (rat)
Dermal	LD50	>3,000 mg/kg (rabbit)
108-65-6 2-methoxy-1-methylethyl acetate		
Oral	LD50	8,532 mg/kg (rat)
Dermal	LD/50	5 g/kg (rabbit)
Inhalative	LC50/4 h	35.7 mg/L (rat)
25619-56-1 barium bis(dinonylnaphthalenesulfonate)		
Oral	LD50	500 mg/kg (ATE)
Inhalative	LC50/4 h	1.5 mg/L (ATE)

- Primary irritant effect:
 - Skin corrosion/irritation Based on available data, the classification criteria are not met.
 - Serious eye damage/irritation Causes serious eye damage.
- Respiratory or skin sensitisation May cause an allergic skin reaction.
- Germ cell mutagenicity Based on available data, the classification criteria are not met.
- Carcinogenicity Suspected of causing cancer. Route of exposure: Inhalation.
- Reproductive toxicity Based on available data, the classification criteria are not met.
- STOT-single exposure May cause drowsiness or dizziness.
- STOT-repeated exposure Based on available data, the classification criteria are not met.
- Aspiration hazard Based on available data, the classification criteria are not met.
- Summary of Effects and Symptoms by Routes of Exposure
 - Eyes:
 - blurred vision
 - redness
 - eye damage, pain
 - Skin:
 - redness
 - rash, allergic contact dermatitis
 - dry skin
 - Inhalation:
 - vomiting
 - shortness of breath
 - cough

(Contd. on page 9)

Trade name: 838AR

(Contd. of page 8)

sore throat
headache
drowsiness
dizziness or drowsiness

· **Swallowed:**

nausea, vomiting
drowsiness or dizziness
shortness of breath
abdominal pain

· **Additional toxicological information:**

· **Delayed and immediate effects as well as chronic effects from short and long-term exposure**

Prolonged or repeated exposure may defat skin and cause skin dryness and cracking, and local redness and discomfort.

Prolonged or repeated exposure may cause skin allergies.

· **11.2 Information on other hazards**

· **Endocrine disrupting properties**

None of the ingredients is listed.

SECTION 12: Ecological information

· **12.1 Toxicity**

· **Aquatic toxicity:**

67-64-1 acetone

EC50/ 48 h	13,500 mg/L (daphnia)
LC50 96h	5,540 mg/L (trout)

1333-86-4 Carbon black

EC50/ 24 h	>5,600 mg/L (aquatic invertebrates)
EC50/ 72 h	>10,000 mg/L (aquatic algae and cyanobacteria)
EC0/ 3 h	>800 mg/L (microorganisms)
LC50	>1,000 mg/L (fish)

· **12.2 Persistence and degradability** No further relevant information available.

· **12.3 Bioaccumulative potential** No further relevant information available.

· **12.4 Mobility in soil** No further relevant information available.

· **12.5 Results of PBT and vPvB assessment**

· **PBT:** Not applicable.

· **vPvB:** Not applicable.

· **12.6 Endocrine disrupting properties**

The product does not contain substances with endocrine disrupting properties.

· **12.7 Other adverse effects**

· **Additional ecological information:**

· **General notes:**

Must not reach sewage water or drainage ditch undiluted or unneutralised.

Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water

(Contd. on page 10)

Trade name: 838AR

(Contd. of page 9)
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

- **Recommendation** This material and its container must be disposed of as hazardous waste.

European waste catalogue


HP3	Flammable
HP4	Irritant - skin irritation and eye damage
HP5	Specific Target Organ Toxicity (STOT)/Aspiration Toxicity

Uncleaned packaging:

Recommendation:

Containers may still present a chemical hazard/ danger when empty.
Dispose of contents in accordance with all local, regional, national, and international regulations.
Where possible retain label warnings and SDS and observe all notices pertaining to the product.


* SECTION 14: Transport information

14.1 UN number or ID number	
· ADR, IMDG, IATA	UN1263
14.2 UN proper shipping name	
· ADR, IMDG	PAINT
· IATA	Paint
14.3 Transport hazard class(es)	
· ADR, IMDG, IATA	
	
· Class	3 Flammable liquids.
· Label	3
14.4 Packing group	
· ADR, IMDG, IATA	II
14.5 Environmental hazards:	Not applicable.
14.6 Special precautions for user	Not applicable.
· Hazard identification number (Kemler code):	33
· EMS Number:	F-E, S-E
· Stowage Category	B
14.7 Maritime transport in bulk according to IMO instruments	Not applicable.

(Contd. on page 11)

Trade name: 838AR

(Contd. of page 10)

· Transport/Additional information:  Limited Quantity 838AR-55ML, 838AR-900ML, 838AR-3.78L	
· ADR · Limited quantities (LQ) · Excepted quantities (EQ)	5L Code: E2 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 500 ml · Transport category 2 · Tunnel restriction code D/E
· IMDG · Limited quantities (LQ) · Excepted quantities (EQ)	5L Code: E2 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 500 ml
· UN "Model Regulation":	UN 1263 PAINT, 3, II

SECTION 15: Regulatory information

· 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

· Poisons Act

· Regulated explosives precursors (Part 1)		
None of the ingredients is listed.		
· Regulated poisons (Part 2)		
None of the ingredients is listed.		
· Reportable explosives precursors (Part 3)		
67-64-1	acetone	Listed
· Reportable poisons (Part 4)		
None of the ingredients is listed.		

· Directive 2012/18/EU

- **Named dangerous substances - ANNEX I** None of the ingredients is listed.
- **Seveso category** P5c FLAMMABLE LIQUIDS
- **Qualifying quantity (tonnes) for the application of lower-tier requirements** 5,000 t
- **Qualifying quantity (tonnes) for the application of upper-tier requirements** 50,000 t
- **REGULATION (EC) No 1907/2006 ANNEX XVII** Conditions of restriction: 3

(Contd. on page 12)

Trade name: 838AR

(Contd. of page 11)

· DIRECTIVE 2011/65/EU on the restriction of the use of certain hazardous substances in electrical and electronic equipment – Annex II

None of the ingredients is listed.

· 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

*** SECTION 16: Other information**

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· Relevant phrases

- H225 Highly flammable liquid and vapour.
- H226 Flammable liquid and vapour.
- H302 Harmful if swallowed.
- H315 Causes skin irritation.
- H317 May cause an allergic skin reaction.
- H318 Causes serious eye damage.
- H319 Causes serious eye irritation.
- H332 Harmful if inhaled.
- H335 May cause respiratory irritation.
- H336 May cause drowsiness or dizziness.
- H351 Suspected of causing cancer.
- EUH066 Repeated exposure may cause skin dryness or cracking.

· Classification according to Regulation (EC) No 1272/2008

Flammable liquids	On basis of test data
Serious eye damage/irritation Skin sensitisation Carcinogenicity Specific target organ toxicity (single exposure)	The classification of the mixture is generally based on the calculation method using substance data according to Regulation (EC) No 1272/2008.

· Department issuing SDS: Regulatory department

· Contact: sds@mgchemicals.com

· Date of previous version: 03.09.2024

· Version number of previous version: 8.01

· Abbreviations and acronyms:

ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)
 IMDG: International Maritime Code for Dangerous Goods
 IATA: International Air Transport Association
 GHS: Globally Harmonised System of Classification and Labelling of Chemicals
 EINECS: European Inventory of Existing Commercial Chemical Substances
 ELINCS: European List of Notified Chemical Substances
 CAS: Chemical Abstracts Service (division of the American Chemical Society)
 VOC: Volatile Organic Compounds (USA, EU)
 LC50: Lethal concentration, 50 percent
 LD50: Lethal dose, 50 percent
 PBT: Persistent, Bioaccumulative and Toxic
 vPvB: very Persistent and very Bioaccumulative
 ATE: Acute toxicity estimate values
 Flam. Liq. 2: Flammable liquids – Category 2
 Flam. Liq. 3: Flammable liquids – Category 3
 Acute Tox. 4: Acute toxicity – Category 4
 Skin Irrit. 2: Skin corrosion/irritation – Category 2
 Eye Dam. 1: Serious eye damage/eye irritation – Category 1
 Eye Irrit. 2: Serious eye damage/eye irritation – Category 2
 Skin Sens. 1: Skin sensitisation – Category 1
 Carc. 2: Carcinogenicity – Category 2
 STOT SE 3: Specific target organ toxicity (single exposure) – Category 3

· * Data compared to the previous version altered.