



21578-281 Trousers with kneepad pockets

Ladies fit DIAMOND - Stretch Zones - flame retardant
MASCOT® ACCELERATE MULTISAFE



| | | | | | | |
|-------|-------|-------|-------|-------|-------|-------|
| 82C34 | 82C36 | 82C38 | 82C40 | 82C42 | 82C44 | 82C46 |
| 82C48 | 82C50 | 82C52 | 82C54 | 82C56 | 76C34 | 76C36 |
| 76C38 | 76C40 | 76C42 | 76C44 | 76C46 | 76C48 | 76C50 |
| 76C52 | 76C54 | 76C56 | 70C34 | 70C36 | 70C38 | 70C40 |
| 70C42 | 70C44 | 70C46 | 70C48 | 70C50 | 70C52 | 70C54 |
| 70C56 | | | | | | |



- Specially designed for women in a DIAMOND fit.
- A high level of protection with anti-static, acid protection and flame retardant properties.
- Protects from electric arcs.
- The combination of firm fabric and stretch gives you an added freedom of movement.
- CORDURA® reinforcements on the front of the leg - stretch under the CORDURA® material ensures good freedom of movement.
- Easily add holster pockets with the Click Pocket System.
- The trousers can easily be folded down. Leg lengths 70 and 76 can be extended by 3 cm, leg length 82 can be extended by 5 cm.
- Suitable for Industrial Laundering.

Technical info

Ladies fit DIAMOND. Anti-static, acid-protective and flame retardant. Protects from electric arcs. Stretch fabric on parts of the product. Prepared for holster pockets with Click Pocket System. Double stitched seams on the leg and crotch. Ergonomically formed trouser leg. Belt loops. Hidden stud fastening. Fly with zip. Front pockets. Back pockets with reinforcement and flaps. Ruler pocket with flap and Kevlar® reinforcement. Thigh pocket with phone pocket and flap with hidden press stud and integrated ID card holder. Detachable ID card holder. Adjustable kneepad pockets with CORDURA fabric. The trousers can easily be folded down. Leg lengths 70 and 76 can be extended by 3 cm, leg length 82 can be extended by 5 cm. With print effects.

Main material/upper material

44% modacrylic/30% cotton/20% polyamide/5% aramid/1% carbon fibres
260 g/m²



Ripstop. According to EN ISO 20471, this product is certified to retain its properties with 50 domestic washes or 40 industrial washes. Impregnation is required after each wash to maintain EN 13034 protection.

Industrial care category B1



Certifications



- OEKO-TEX® STANDARD 100
- EN 1149-5
- EN ISO 11612 (A1, A2, B1, C1, E1, F1)
- EN 13034 (Type 6)
- EN 13034, category K
- EN 61482-1-2 APC 1
- EN IEC 61482-1-1 (ELIM 10 cal/cm², ATPV 11 cal/cm², stretch seat area ELIM 7,7 cal/cm², ATPV 9,5 cal/cm²)
- ProWash®

Logo

Due to the unique properties of the fabric, logo printing is only available through the use of specific transfer types. As this is a safety product, we strongly recommend that MASCOT affix the logo to reduce the risk of errors. Please

User



contact customer service for further information.

Logo placement:

- Workwear logo. Special placement. Contact to discuss further