

## Plastic label - US-EMLP (60X15) YE CUS - 0830113

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Plastic label, can be ordered: By card, yellow, labeled according to customer specifications, Mounting type: Adhesive, Lettering field: 60 x 15 mm



The figure shows the US-EMLP (27x18) version in white



### Key commercial data

Packing unit	1 pc
GTIN	 4 046356 614757
Weight per Piece (excluding packing)	19.0 g
Custom tariff number	39199000
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Length (b)	59.7 mm
Height	0.5 mm
Width (a)	14.9 mm

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
---------------------------------	------------------

#### General

Color	yellow
Components	Silicone-free
Inflammability class according to UL 94	V0
Material	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	9
Number of individual labels per row	1

# Plastic label - US-EMLP (60X15) YE CUS - 0830113

## Technical data

### General

Marking mounting type	Adhesive
-----------------------	----------

## Classifications

### eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137

### ETIM

ETIM 4.0	EC000761
ETIM 5.0	EC000761

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410