



Data Sheet | Item Number: 294-5425

Lighting connector; push-button, external; with screw-type ground contact; L´-N´-L-PE-N; 5-pole; Lighting side: for solid conductors; Inst. side: for all conductor types; max. 2.5 mm²; Surrounding air temperature: max 85°C (T85); white

<https://www.wago.com/294-5425>



Color: white



Dimensions in mm

Field-wiring terminal block, 294 Series, Push-in CAGE CLAMP®

Easily, quickly and safely connect conductors with this field-wiring terminal block (item number 294-5425). Conductors can only be connected to this field-wiring terminal block if their strip length is between 8 and 9 mm . This product features four conductor terminals and utilizes Push-in CAGE CLAMP® as well as PUSH WIRE®. Push-in CAGE CLAMP® technology provides a universal connection solution for all conductor types. It allows both solid and fine-stranded conductors with ferrules to be inserted directly into the clamping point without the need for tools. Our PUSH WIRE® connection is the quick and easy method for connecting solid conductors. Dimensions: (50 x 21.53 x 27.3) mm (width x height x depth). This field-wiring terminal block is suitable for conductor cross sections ranging from 0.5 mm² to 2.5 mm² on one side and for conductor cross sections ranging from 0.5 mm² to 2.5 mm² on the other side as well as conductor cross sections from 0.5 mm² to 2.5 mm² and from 0.5 mm² to 0.75 mm² depending on the conductor type.

The contact surface is coated with tin.

Electrical data				
Ratings per		IEC/EN 60998-1		
Overvoltage category		III	III	II
Pollution degree		3	2	2
Nominal voltage		-	-	500 V
Rated impulse withstand voltage		-	-	4 kV
Rated current		-	-	24 A

Ratings per IEC/EN – Notes	
Ratings (note)	Connection points

Ratings per		IEC/EN 60998-2-2		
Overvoltage category		III	III	II
Pollution degree		3	2	2
Nominal voltage		-	-	500 V
Rated impulse withstand voltage		-	-	4 kV
Rated current		-	-	24 A

General information	
Wiring direction	Side-entry wiring

Connection Data

Clamping units	25
Total number of potentials	5
Number of connection types	4
PE function	Screw-type PE contact

Connection 1

Connection type	External 1
Connection technology	Push-in CAGE CLAMP®
Number of connection points	2
Actuation type	Push-button
Connectable conductor materials	Copper
Solid conductor	0.5 ... 2.5 mm ² / 18 ... 12 AWG
Solid conductor; push-in termination	0.5 ... 2.5 mm ² / 18 ... 12 AWG
Stranded conductor	0.5 ... 2.5 mm ² / 18 ... 14 AWG
Fine-stranded conductor	0.5 ... 2.5 mm ² / 18 ... 14 AWG
Fine-stranded conductor; with insulated ferrule	0.5 ... 1.5 mm ² / 18 ... 16 AWG
Fine-stranded conductor; with uninsulated ferrule	0.5 ... 1.5 mm ² / 18 ... 16 AWG
Fine-stranded conductor; with ferrule; push-in termination	0.5 mm ² / 18 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches
Pole number	5
Wiring direction	Side-entry wiring

Connection 2

Connection type	Internal 2
Connection technology	PUSH WIRE®
Number of connection points	1
Actuation type	Push-in
Solid conductor	0.5 ... 2.5 mm ² / 18 ... 14 AWG
Fine-stranded conductor; with insulated ferrule	0.5 ... 1 mm ² / 18 ... 16 AWG
Fine-stranded conductor; with uninsulated ferrule	0.5 ... 1.5 mm ² / 18 ... 14 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches

Connection 3

Connection type	Internal 3
Connection technology	PUSH WIRE®
Number of connection points	1
Actuation type	Push-in
Solid conductor	0.5 ... 1.5 mm ² / 18 ... 16 AWG
Fine-stranded conductor; with insulated ferrule	0.5 ... 0.75 mm ² / 18 AWG
Fine-stranded conductor; with uninsulated ferrule	0.5 ... 1 mm ² / 18 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches

Connection 4

Connection type	Internal 4
Connection technology	PUSH WIRE®
Number of connection points	1
Actuation type	Push-in
Solid conductor	0.5 ... 0.75 mm ² / 18 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches

Physical data

Pin spacing	10 mm / 0.394 inches
Width	50 mm / 1.969 inches
Height	21.53 mm / 0.848 inches
Height from the surface	17 mm / 0.669 inches
Depth	27.3 mm / 1.075 inches

Mechanical data		
Marking		L´-N´-L-⊕-N
Mounting type		Snap-in foot

Material data		
Note (material data)		Information on material specifications can be found here
Color		white
Material group		IIIa
Insulation material (main housing)		Polycarbonate (PC)
Flammability class per UL94		V0
Clamping spring material		Chrome-nickel spring steel (CrNi)
Contact material		Electrolytic copper (E _{Cu})
Contact Plating		Tin
Fire load		0.23 MJ
Halogen-free		Yes
Weight		15.9 g

Environmental requirements		
Temperature stability		120 °C
T marking		T85

Commercial data		
Product Group		8 (Misc. Chassis Mount Blocks)
PU (SPU)		250 pcs
Packaging type		Bag
Country of origin		PL
GTIN		4050821098614
Customs tariff number		85369010000

Product Classification		
UNSPSC		39121409
eCl@ss 10.0		27-14-11-06
eCl@ss 9.0		27-14-11-06
ETIM 9.0		EC001284
ETIM 10.0		EC001284
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant, No Exemption
SCIP notification number (Austria)		761a957f-8021-45bb-8249-9582b2f2eb2f
SCIP notification number (Belgium)		dc275b7e-6882-4065-a057-6b67681aeaad
SCIP notification number (Bulgaria)		50ece0c5-8dbd-4a1e-a5a4-4c5c8d9ac1c5
SCIP notification number (Czech Republic)		36e7d44c-464f-4645-8db3-1dc46d313dcf
SCIP notification number (Denmark)		1e0e7f29-90a8-4805-a025-9ccce97638b3
SCIP notification number (Finland)		8c170572-7446-4a9c-83c2-18950fe82a27
SCIP notification number (France)		f9ed6b84-f57a-48d4-8334-3b9a70591268
SCIP notification number (Germany)		1c805b93-a8bd-4995-bbef-28f39b54041c
SCIP notification number (Hungary)		33b1fde9-f696-43f3-9185-e1178f04e048
SCIP notification number (Italy)		31a36b6b-1bb6-448f-9442-e9d8cf5a5327
SCIP notification number (Netherlands)		bda551b8-f26f-4e56-87bd-660dc7749286
SCIP notification number (Poland)		ca13ba90-0e3f-4465-ae8c-9edfe5096db6
SCIP notification number (Romania)		e08c060f-0d73-4f20-95f0-9ca1e5dc3087

Environmental Product Compliance	
SCIP notification number (Sweden)	d291a6e6-cca4-4656-b57c-322ad23250ed

Approvals / Certificates

General approvals		Declarations of conformity and manufacturer's declarations
		
Approval	Standard	Certificate Name
ENEC 05 DEKRA Certification B.V.	EN 60998	2128791.01
		EU-Declaration of Conformity WAGO GmbH & Co. KG
		UK-Declaration of Conformity WAGO GmbH & Co. KG

Downloads

Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 294-5425	

Documentation

Bid Text			
294-5425	13.06.2017	doc 28.00 KB	
294-5425	19.02.2019	xml 5.59 KB	

CAD/CAE-Data

CAD data	CAE data
2D/3D Models 294-5425 	WSCAD Universe 294-5425 
	ZUKEN Portal 294-5425 

1 Compatible Products

1.1 Optional Accessories

1.1.1 Strain relief

1.1.1.1 Strain relief



Item No.: 294-370
Strain relief; for 294 Series; with snap-in mounting feet; white



Item No.: 294-375
Strain relief; for 294 Series; without snap-in mounting feet; white

1.1.1.2 Strain relief plate

Item No.: 294-364
Strain relief plate; for 294 Series; for multi-core cables; 3- to 5-pole; with secured clamp; white

Item No.: 294-384
Strain relief plate; for 294 Series; for single strands; 3- to 5-pole; with secured clamp; white


1.1.2 Tool

1.1.2.2 Operating tool


Item No.: 206-294
Disconnection tool; green

Installation Notes


Installation



5-pole – with screw-type ground contact, d ≤ 4.1 mm




Snap-in foot



Drilled hole for snap-in mounting foot


Conductor termination




Internal connection:
PUSH WIRE® for internal wiring with solid conductors

EUROPE
1 x 0.5 ... 2.5 mm ² "s"
1 x 0.5 ... 1.5 mm ² "s"
1 x 0.5 ... 0.75 mm ² "s"
AMERICA
1 x AWG 18 ... 14 "s"
1 x AWG 18 ... 16 "s"
1 x AWG 18 "s"
JAPAN
1 x 0.8 ... 1.6 mm diam. "s"
1 x 0.8 ... 1 mm diam. "s"
1 x 0.8 mm diam. "s"

EUROPE
2 x 0.5 ... 2.5 mm ² "s, str, f-str"
AMERICA
2 x AWG 18 ... 12 "s"
2 x AWG 18 ... 14 "s, f-str"
JAPAN
2 x 0.8 ... 2 mm diam. "s"
2 x 0.5 ... 2 mm ² str, f-str"



External connection:
Push-in CAGE CLAMP® for field-wiring with all conductor types



Terminating five conductors per pole – solid and fine-stranded.

