

Technical Data Sheet



Description

Description	93 A/St
Part Number	10115189
Marking according to EN	A2 - P3
Conditions of use	- organic gases and vapors with a boiling point > 65° C - particles
Colour code	



Labels



Characteristics

Weight [g]	260
Diameter [mm]	107
Height incl. thread [mm]	78
Connection	EN 148 - 1

Breathing Resistance

	at	EN 14387 requirements	Typical values
	30 l / min	2,60 mbar	1,20 mbar
	95 l / min	9,80 mbar	4,60 mbar

Concentration of Testing Gases

Class 1	1000 ppm [0,1 Vol.-%]
Class 2	5000 ppm [0,5 Vol.-%]

Performances

Filter type and class	Gases of reference	EN 14387 requirements	Typical values
A2	cyclohexane [C ₆ H ₁₂]	35 min	60 min
Filter type and class	Particles of reference	EN 143 requirements	Typical values
P3	sodium chloride [NaCl]	0.05%	< 0,01%
	paraffin oil	0.05%	< 0,01%
R	Reusable according EN 143:2000/A1:2006		
D	Dolomite clogging test & marking according to EN 143:2000/A1:2006 and EN 14387		

Material

Housing	aluminium
Cover (particle filter)	polypropylene
Filtering material	filtering paper / impregnated activated carbon

Details/Special Information

Storage conditions & time	- 5 °C to + 50°C, < 90 % r. h. 6,0 years
---------------------------	--

Technical Data Sheet



Description

Description	93 AB/St
Part Number	10097993
Marking according to EN	A2, B2 - P3
Conditions of use	- organic gases and vapors with a boiling point > 65° C - inorganic gases and vapors, e.g. chlorine, hydrogen sulfide, hydrogen cyanide - particles



Colour code

brown
grey
white

Labels



Characteristics

Weight [g]	270
Diameter [mm]	107
Height incl. thread [mm]	78
Connection	EN 148 - 1

Breathing Resistance

at	EN 14387 requirements	Typical values
30 l / min	2,60 mbar	1,40 mbar
95 l / min	9,80 mbar	5,50 mbar

Concentration of Testing Gases

Class 1	1000 ppm [0,1 Vol.-%]
Class 2	5000 ppm [0,5 Vol.-%]

Performances

Filter type and class	Gases of reference	EN 14387 requirements	Typical values
A2	cyclohexane [C ₆ H ₁₂]	35 min	60 min
B2	chlorine [Cl ₂]	20 min	40 min
	hydrogen sulfide [H ₂ S]	40 min	60 min
	hydrocyanic acid [HCN]	25 min	45 min
Filter type and class	Particles of reference	EN 143 requirements	Typical values
P3	sodium chloride [NaCl]	0.05%	< 0,01%
	paraffin oil	0.05%	< 0,01%
R	Reusable according EN 143:2000/A1:2006		
D	Dolomite clogging test & marking according to EN 143:2000/A1:2006 and EN 14387		

Material

Housing	aluminium
Cover (particle filter)	polypropylene
Filtering material	filtering paper / impregnated activated carbon

Details/Special Information


Storage conditions & time	- 5 °C to + 50°C, < 90 % r. h. 6,0 years
---------------------------	--

Technical Data Sheet



Description

Description	93 ABEK Hg / St
Part Number	10097231

Marking according to EN	A2, B2, E2, K1, Hg - P3	
Conditions of use	• organic gases and vapors with a boiling point > 65° C • inorganic gases and vapors, e.g. chlorine, hydrogen sulfide, hydrogen cyanide • sulfur dioxide, hydrogen chloride and other acid gases • ammonia and organic ammonia derivatives • mercury • particles	

Colour code	<table><tr><td>brown</td></tr><tr><td>grey</td></tr><tr><td>yellow</td></tr><tr><td>green</td></tr><tr><td>red</td></tr><tr><td>white</td></tr></table>	brown	grey	yellow	green	red	white	
brown								
grey								
yellow								
green								
red								
white								

Labels



CE0121

Characteristics

Weight [g]	295
Diameter [mm]	107
Height incl. thread [mm]	78
Connection	EN 148-1

Breathing Resistance

	at	EN 14387 requirements	Typical values
	30 l / min	2,6 mbar	1,70 mbar
	95 l / min	9,8 mbar	6,50 mbar

Concentration of Testing Gases

Class 1	1000 ppm [0,1 Vol.-%]
Class 2	5000 ppm [0,5 Vol.-%]
Hg	13 mg/m ³

Performances

Filter type and class	Gases of reference	EN 14387 requirements	Typical values
A2	cyclohexane [C ₆ H ₁₂]	35 min	45 min
B2	chlorine [Cl ₂]	20 min	40 min
	hydrogen sulfide [H ₂ S]	40 min	55 min
	hydrocyanic acid [HCN]	25 min	45 min
E2	sulfur dioxide [SO ₂]	20 min	22 min
K1	ammonia [NH ₃]	50 min	60 min
Hg	mercury [vapor]	100 h	> 100 h
Filter type and class	Particles of reference	EN 143 requirements	Typical values
P3	sodium chloride [NaCl]	0.05%	< 0,01%
	paraffin oil	0.05%	< 0,01%
R	Reusable according EN 143:2000/A1:2006		
D	Dolomite clogging test & marking according to EN 143:2000/A1:2006 and EN 14387		

Material

Housing	aluminium
Cover (particle filter)	polypropylene
Filtering material	filtering paper / impregnated activated carbon


Details/Special Information

Storage conditions & time	- 5 °C to + 50°C, < 90 % r. h. 6,0 years
The maximum service time of the special filter against mercury is 50 h. This applies if no other hazardous agents has penetrated the filter earlier. The filter must always be replaced in case of penetration by a hazardous age	

Technical Data Sheet



Description

Description	93 ABEK 2 Hg / St	
Part Number	10097232	
Marking according to EN	A2, B2, E2, K2, Hg - P3	
Conditions of use	• organic gases and vapors with a boiling point > 65° C • inorganic gases and vapors, e.g. chlorine, hydrogen sulfide, hydrogen cyanide • sulfur dioxide, hydrogen chloride and other acid gases • ammonia and organic ammonia derivatives • mercury • particles	
Colour code		

Labels



Characteristics

Weight [g]	350
Diameter [mm]	107
Height incl. thread [mm]	88
Connection	EN 148 - 1

Breathing Resistance

	at	EN 14387 requirements	Typical values
	30 l / min	2,6 mbar	2,00 mbar
	95 l / min	9,8 mbar	8,00 mbar

Concentration of Testing Gases

Class 1	1000 ppm [0,1 Vol.-%]
Class 2	5000 ppm [0,5 Vol.-%]
Hg	13 mg / m ³

Performances

Filter type and class	Gases of reference	EN 14387 requirements	Typical values
A2	cyclohexane [C ₆ H ₁₂]	35 min	60 min
B2	chlorine [Cl ₂]	20 min	55 min
	hydrogen sulfide [H ₂ S]	40 min	65 min
	hydrocyanic acid [HCN]	25 min	60 min
E2	sulfur dioxide [SO ₂]	20 min	33 min
K2	ammonia [NH ₃]	40 min	55 min
Hg	mercury [vapor]	100 h	> 100 h
Filter type and class	Particles of reference	EN 143 requirements	Typical values
P3	sodium chloride [NaCl]	0.05%	< 0,01%
	paraffin oil	0.05%	< 0,01%
R	Reusable according EN 143:2000/A1:2006		
D	Dolomite clogging test & marking according to EN 143:2000/A1:2006 and EN 14387		

Material

Housing	aluminium
Cover (particle filter)	polypropylene
Filtering material	filtering paper / impregnated activated carbon

Details/Special Information


Storage conditions & time	- 5 °C to + 50°C, < 90 % r. h. 6,0 years
The maximum service time of the special filter against mercury is 50 h. This applies if no other hazardous agents has penetrated the filter earlier. The filter must always be replaced in case of penetration by a hazardous agent.	

Technical Data Sheet



Description

Description	F 93 ABEK 2 Hg / St
Part Number	10098022
Marking according to EN	A2, B2, E2, K2, Hg - P3
Conditions of use	• organic gases and vapors with a boiling point > 65° C • inorganic gases and vapors, e.g. chlorine, hydrogen sulfide, hydrogen cyanide • sulfur dioxide, hydrogen chloride and other acid gases • ammonia and organic ammonia derivatives • mercury • particles



Colour code



Labels



Characteristics

Weight [g]	370
Diameter [mm]	107
Height incl. thread [mm]	90
Connection	EN 148-3 [M 45 x 3]

Breathing Resistance

	at	EN 14387 requirements	Typical values
	30 l / min	2,60 mbar	2,00 mbar
	95 l / min	9,80 mbar	8,00 mbar

Concentration of Testing Gases

Class 1	1000 ppm [0,1 Vol.-%]
Class 2	5000 ppm [0,5 Vol.-%]
Hg	13 mg / m ³

Performances

Filter type and class	Gases of reference	EN 14387 requirements	Typical values
A2	cyclohexane [C ₆ H ₁₂]	35 min	60 min
B2	chlorine [Cl ₂]	20 min	55 min
	hydrogen sulfide [H ₂ S]	40 min	65 min
	hydrocyanic acid [HCN]	25 min	60 min
E2	sulfur dioxide [SO ₂]	20 min	33 min
K2	ammonia [NH ₃]	40 min	55 min
Hg	mercury [vapor]	100 h	> 100 h
Filter type and class	Particles of reference	EN 143 requirements	Typical values
P3	sodium chloride [NaCl]	0.05%	< 0,01%
	paraffin oil	0.05%	< 0,01%
R	Reusable according to EN 143:2000/A1:2006		
D	Dolomite clogging test & marking according to EN 143:2000/A1:2006 and EN 14387		

Material

Housing	aluminium
Cover (particle filter)	polypropylene
Filtering material	filtering paper / impregnated activated carbon

Details/Special Information


Storage conditions & time	- 5 °C to + 50°C, < 90 % r. h. 6,0 years
The maximum service time of the special filter against mercury is 50 h. This applies if no other hazardous agents has penetrated the filter earlier. The filter must always be replaced in case of penetration by a hazardous agent.	

Technical Data Sheet



Description

Description	93 Hg / St
Part Number	10115201
Marking according to EN	Hg-P3
Conditions of use	• mercury and particles



Colour code



Labels



CE 0121

Characteristics

Weight [g]	270
Diameter [mm]	107
Height incl. thread [mm]	78
Connection	EN 148-1

Breathing Resistance

	at	EN 14387 requirements	Typical values
	30 l / min	2,60 mbar	1,20 mbar
	95 l / min	9,80 mbar	4,60 mbar

Concentration of Testing Gases

Hg	13 mg/m ³
----	----------------------

Performances

Filter type and class	Gases of reference	EN 14387 requirements	Typical values
Hg	mercury [vapor]	100 h	> 190 h
Filter type and class	Particles of reference	EN 143 requirements	Typical values
P3	sodium chloride [NaCl]	0.05%	< 0,01%
	paraffin oil	0.05%	< 0,01%
R	Reusable according to EN 143:2000/A1:2006		
D	Dolomite clogging test & marking according to EN 143:2000/A1:2006 and EN 14387		

Material

Housing	aluminium
Cover (particle filter)	polypropylene
Filtering material	filtering paper / impregnated activated carbon

Details/Special Information

Storage conditions & time - 5 °C to + 50°C, < 90 % r. h. 6,0 years

The maximum service time of the special filter against mercury is 50 h. This applies if no other hazardous agents has penetrated the filter earlier. The filter must always be replaced in case of penetration by a hazardous agent.

Technical Data Sheet



Description

Description	93 K/St
Part Number	10115190
Marking according to EN	K2 - P3
Conditions of use	• ammonia and organic ammonia derivatives • particles
Colour code	green white



Labels



Characteristics

Weight [g]	295
Diameter [mm]	107
Height incl. thread [mm]	78
Connection	EN 148-1

Breathing Resistance

	at	EN 14387 requirements	Typical values
	30 l / min	2,60 mbar	1,40 mbar
	95 l / min	9,80 mbar	5,50 mbar

Concentration of Testing Gases

Class 1	1000 ppm [0,1 Vol.-%]
Class 2	5000 ppm [0,5 Vol.-%]

Performances

Filter type and class	Gases of reference	EN 14387 requirements	Typical values
K2	ammonia [NH ₃]	40 min	60 min
Filter type and class	Particles of reference	EN 143 requirements	Typical values
P3	sodium chloride [NaCl]	0.05%	< 0,01%
	paraffin oil	0.05%	< 0,01%
R	Reusable according to EN 143:2000/A1:2006		
D	Dolomite clogging test & marking according to EN 143:2000/A1:2006 and EN 14387		

Material

Housing	aluminium
Cover (particle filter)	polypropylene
Filtering material	filtering paper / impregnated activated carbon

Details/Special Information

Storage conditions & time	- 5 °C to + 50°C, < 90 % r. h. 6,5 years
---------------------------	--

Technical Data Sheet



Description

Description 93 AX / St

Part Number 10108409

Marking according to EN AX, P3

Conditions of use

- low-boiling organic compounds [boiling point $\leq 65^{\circ}\text{C}$] of groups 1 and 2
- particles



Colour code

brown

white

Labels



Characteristics

Weight [g] 260

Diameter [mm] 107

Height incl. thread [mm] 88

Connection EN 148-1

Breathing Resistance

	at	EN 14387 requirements	Typical values
	30 l / min	2,60 mbar	1,55 mbar
	95 l / min	9,80 mbar	5,80 mbar

Concentration of Testing Gases

dimethyl ether 0,05 Vol.-%

isobutane 0,25 Vol. %

Performances

Filter type and class	Gases of reference	EN 14387 requirements	Typical values
AX	dimethyl ether [CH ₃ OCH ₃]	50 min	75 min
	isobutane [C ₄ H ₁₀]	50 min	75 min

Filter type and class	Particles of reference	EN 143 requirements	Typical values
P3	sodium chloride [NaCl]	0.05%	< 0,01%
	paraffin oil	0.05%	< 0,01%
R	Reusable according to EN 143:2000/A1:2006		
D	Dolomite clogging test & marking according to EN 143:2000/A1:2006 and EN 14387		

Material

Housing aluminium

Cover (particle filter) polypropylene

Filtering material filtering paper / unimpregnated activated carbon

Details/Special Regulations

• Against the low boiling compounds of groups 1 and 2 gas filters AX according to EN 14387 must be used. The following maximum concentrations and usetimes apply:

low boiling compounds group	max. concentration [ml/m ³]	max. usetime [min]
1	100	40
	500	20
2	1000	60
	5000	20

• For low boiling compounds of group 3 protection is provided by filters other than AX [e.g. type B or K], for low boiling compounds of group 4 gas filters provide no sufficient protection.

• AX filters may also be used as A2 filters. In this case however, they shall not be used against low boiling compounds.

• Use of AX filters against mixtures of low boiling compounds or mixtures of low boiling compounds and other organic compounds is not permitted because desorption effects may occur.

• Only factory sealed AX filters must be used. Within one work shift [max. 8 hours] repeated use is permitted, provided the maximum usetime, listed in the above table is not exceeded. Further use is not permitted.

storage condition&time 5°C to 50 °C < 90 % r.h..


6,5 years

Technical Data Sheet




Description

Description	93 NO CO / St
Part Number	10115314
Marking according to EN	NO-P3, CO
Conditions of use	- nitrous gases, e.g. NO, NO₂, NO_x - carbon monoxide - particles
Colour code	black blue white



Labels



CE0121

Characteristics

Weight [g]	470
Diameter [mm]	108.2
Height incl. thread [mm]	78
Connection	EN 148-1

Breathing Resistance

	at	EN 14387 requirements	Typical values
	30 l / min	2,60 mbar	1,50 mbar
	95 l / min	9,80 mbar	5,50 mbar

Concentration of Testing Gases

NO, CO	2500 ppm [0,25 Vol.-%]
--------	------------------------

Performances

Filter type and class	Gases of reference	EN 14387/58620 requirements	Typical values
NO	nitric oxide [NO]	20 min	73 min
	nitrogen dioxide [NO ₂]	20 min	42 min
CO 20	carbon monoxide [CO]	< 200 ppm [temporal weighted average / 20 min]	35 min
Filter type and class	Particles of reference	EN 143 requirements	Typical values
P3	sodium chloride [NaCl]	0.05%	< 0,01%
	paraffin oil	0.05%	< 0,01%
R	Reusable according EN 143:2000/A1:2006		
D	Dolomite clogging test & marking according to EN 143:2000/A1:2006 and EN 14387		

Material

Housing	aluminium
Cover (particle filter)	polypropylene
Filtering material	filtering paper / hopcalite

Details/Special Information

Storage conditions & time	- 5 °C to + 50°C, < 90 % r. h. 4,0 years
---------------------------	--

		MSA The Safety Company	
Technical Data Sheet			
Description			
Description	93 ABEK CO NO Hg / St		
Part Number	10115315		
Marking according to EN	A1, B2, E2, K1, CO, NO, Hg-P3		
Conditions of use	<		