


FEATURES

- **Annealed Copper Conductor:** Provides excellent conductivity and flexibility
- **Polyvinyl Chloride Jacket:** Offers robust protection against wear and environmental conditions
- **Plain Conductor Type:** Ensures ease of installation and reliable performance
- **30/0.25 Core Strands:** Enhances flexibility and durability
- **Temperature Range -15 °C to 70 °C:** Suitable for a wide range of operating environments
- **Voltage Rating 500 V:** Supports medium voltage applications
- **Black Jacket Colour:** Ideal for discreet installations

RS PRO 1.5 mm² Flexible Cable, 5 Core

RS Stock No: 606-087



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible cable is designed for reliable electrical connections in various industrial and commercial settings. With a 1.5 mm² cross-sectional area and 5 cores, it is ideal for applications requiring flexibility and durability. The cable's PVC jacket ensures protection against environmental factors, making it suitable for both indoor and outdoor use.

General Specifications

Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	Black
Product Type	Flexible Cable

Mechanical Specifications

Cable CSA	1.5 mm ²
Cable Length	100 m
Core Strands	30/0.25
Jacket Material	Polyvinyl Chloride
Number of Cores	5
Outside Diameter	11.6 mm

Operation Environment Specifications

Maximum Operating Temperature	70 °C
Minimum Operating Temperature	-15 °C

Approvals

Standards/Approvals	ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228
---------------------	---

Electrical Specifications

Voltage	500 V
---------	-------