



Main

Range	TeSys
Device short name	GV2ME
Product or component type	Motor starter
Motor starter type	Non reversing
Poles description	3P
Utilisation category	AC-3 AC-3e
Motor power kW	1.1 kW at 400/415 V AC 50/60 Hz 1.5 kW at 400/415 V AC 50/60 Hz 1.5 kW at 440 V AC 50/60 Hz 1.5 kW at 500 V AC 50/60 Hz 2.2 kW at 500 V AC 50/60 Hz
[Uc] control circuit voltage	230 V AC 50/60 Hz
Magnetic tripping current	51 A

Complementary

Device composition	1 3-pole contactor 1 motor circuit breaker type GV2ME 1 combination block GV2AF01
Coordination type	Type 1
Thermal protection adjustment range	2.5...4 A
Breaking capacity	50 kA Iq at 400/415 V AC 50/60 Hz conforming to IEC 60947-4-1 50 kA Iq at 440 V AC 50/60 Hz conforming to IEC 60947-4-1 50 kA Iq at 500 V AC 50/60 Hz conforming to IEC 60947-4-1
Net weight	0.46 kg
Height	152 mm
Width	45 mm
Depth	87 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins