

## FEATURES

- Thread-cutting self-tapping screws with pan and countersunk heads
- BZP galvanised steel
- Generally non-magnetic
- Cannot be hardened by heat treatment
- Supplied in a polypropylene case

## 1230 piece Steel Screw/Bolt Kit, No. 10, No. 4, No. 6, No. 8

RS Stock No.: 393-163



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

From the trusted RS PRO professional brand, this set of high-quality Pozidriv flat pan and countersunk head self-tapping screws are ideal for many applications. Self-tapping screws are split into two main categories, thread-forming and thread-cutting. The screws are similar in the job they do, however they have two noticeable differences. Thread-forming screws have a flat base whereas thread-cutting screws have a sharp point. The difference between self-tapping and self-drilling fasteners is that self-tapping screws will tap a hole into a soft material, self-drilling screws can drill a hole into anything from metal to wood meaning no pilot hole is needed.

### General Specifications

<b>Number Of Pieces</b>	1230
<b>Screw/Bolt Type</b>	Self-Tapping Screw
<b>Head Shape</b>	Flat, Pan
<b>Drive Type</b>	Pozidriv
<b>Kit Contents</b>	Pan Pozi No.4 Length-1/4in. Qty-100 Length-3/8in. Qty-100 Length-1/2in. Qty-100
<b>Applications</b>	Carpentry, Construction, DIY applications, such as cabinets and paneling


### Mechanical Specifications



















<b>Screw/Bolts Lengths</b>	1/4in to 1-1/4in
<b>Thread Size</b>	No. 10, No. 4, No. 6, No. 8
<b>Material</b>	Steel
<b>Finish</b>	Galvanised
<b>Screw/Bolt Length Longest</b>	1-1/4in
<b>Screw/Bolt Length Shortest</b>	1/4in



Kit Contents									
Head Type	Size	Length	Qty	Length	Qty	Length	Qty	Length	Qty
<b>Cross-recess CSK &amp; Pan head, BZP Steel</b>									
Pan Pozi	No.4	1/4 in.	100	3/8 in.	100	1/2 in.	100	–	–

## 93-163



 6 x 1/2	 6 x 1	 8 x 1/2	 8 x 1	 10 x 1/2	 10 x 1
 4 x 1/4	 4 x 3/8	 4 x 1/2	 6 x 1/4	 6 x 3/8	 6 x 1/2
 8 x 3/8	 8 x 1/2	 8 x 3/4	 8 x 1.1/4	 10 x 3/8	 10 x 1/2