



APC Smart-UPS RT 20kVA RM 230V

SURT20KRMXLI

Overview

Presentation	High density, double-conversion on-line power protection with scalable runtime.
Lead time	Usually in Stock

Main	
Main Input Voltage	230 V 400 V 3 phases
Product or component type	Uninterruptible power supply (UPS)
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated power in W	16000 W
rated power in VA	20000 VA
output connection type	2 IEC Jumpers 8 IEC 60320 C19
Output connector type	Hard wire 3-wire (H N + E) 1 Hard wire 5-wire (3P + N + E) 1
Number of rack unit	12U
Provided equipment	CD with software Rack mounting support rails Smart UPS signalling RS-232 cable User manual Web/SNMP management card
Range of product	Smart-UPS On-Line

Batteries & Runtime

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Battery type	Lead-acid battery
Battery voltage	+/- 192 V (split battery referenced to neutral)
Extended runtime	1
Number of battery filled slots	4
Number of battery free slots	0
Battery recharge time	2.5 h
Number of battery replacement quantity	4

Battery life	35 year(s)
Replacement battery	APCRBC140 ☐
Discharge battery voltage	+/- 154 V
Battery charger power	1530 W rated

General

Number of power module filled slots	0
Number of power module free slots	0
Redundant	No
UPS type	Double conversion online

Physical

Colour	Black
Height	53.3 cm
Width	43.2 cm
Depth	77.3 cm
Net weight	247.73 kg
Mounting location	Front
Mounting preference	Lower
Mounting mode	Rack-mounted
Two post mountable	0
USB compatible	No

Input

Maximum input current	115 A
Input harmonic distortion	Less than 5 % for full load
Input Power Factor at Full Load	0.98
Switching current capacity	125 A
Input voltage limits	160280 V
Input current	115 A (1 phase) 38.3 A per phase (3 phases)
Number of input connectors	1 hard wire 3-wire (1P + N + E) 1 hard wire 5-wire (3P + N + E)
Network frequency	4070 Hz auto-sensing

Output

Bypass type	Built-in static bypass Internal bypass (automatic and manual) Optional external bypass
Crest factor	3:1
Harmonic distortion	Less than 5 %
Maximum configurable power in VA	20000 VA
Maximum configurable power in W	16000 W

Output overload operation	60 seconds at 125% and 30 seconds at 150%
Wave type	Sine wave
Efficiency	93 % (in battery operation)
Output frequency	50/60 Hz +/- 3 Hz user adjustable +/- 0.1 Hz sync to mains
Additional information	Configurable for 400 or 415 V 3 Phase nominal output voltage

Conformance

Product certifications	BSMI VDE
Standards	EN/IEC 62040-1:2019/A11:2021
	EN/IEC 62040-2:2006/AC:2006
	EN/IEC 62040-2:2018

Environmental

Acoustic level	59 dBA
Heat dissipation	3770 Btu/h
Operating altitude	010000 ft
Ambient air temperature for operation	040 °C
Ambient air temperature for storage	-1545 °C
Storage altitude	0.000000000015240.000000000 m
IP degree of protection	IP20
Relative humidity	095 % non-condensing
Storage Relative Humidity	095 % non-condensing

Communications & Management

Emergency power off	Yes
Free slots	0
Preinstalled device	Network management card 2 with environmental monitoring

Surge Protection and Filtering

Noise suppression	Full time multi-pole noise filtering: 0.3% IEEE surge let-through: zero clamping
	response time: meets III 1449

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	99 cm
Package 1 Width	61 cm
Package 1 Length	100.3 cm
Package 1 Weight	314.09 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	2
Package 2 Height	111 cm
Package 2 Width	100 cm

Package 2 Length	120 cm	
Package 2 Weight	626.864 ka	

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	37662
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	409c68a1-39a6-4e5f-b080-12befe783ad8
REACh Regulation	REACh Declaration
Optimized Energy Efficiency	Energy efficient product

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins