

SIPLUS ET 200SP DQ 4x24 V DC/2 A HF based on 6ES7132-6BD21-0CA0 with conformal coating -40...+70 °C output module, DQ 4x24 V DC/2 A high feature, source output (PNP, sourcing output) packing unit: 1 unit, suitable for BU type A0, color code CC02, channel diagnostics for: short-circuit and wire break, supply voltage, channel fault channel fault LED

General information	
Product type designation	DQ 4x24VDC/2A HF
Firmware version	
<ul style="list-style-type: none"> <li>FW update possible</li> </ul>	Yes
based on	<a href="#">6ES7132-6BD21-0CA0</a>
usable BaseUnits	BU type A0
Color code for module-specific color-coded label	CC02
Product function	
<ul style="list-style-type: none"> <li>I&amp;M data</li> </ul>	Yes; I&M0 to I&M3
<ul style="list-style-type: none"> <li>Isochronous mode</li> </ul>	Yes
Engineering with	
<ul style="list-style-type: none"> <li>STEP 7 TIA Portal configurable/integrated from version</li> </ul>	see entry ID: 109746275
Operating mode	
<ul style="list-style-type: none"> <li>DQ</li> </ul>	Yes
<ul style="list-style-type: none"> <li>DQ with energy-saving function</li> </ul>	No
<ul style="list-style-type: none"> <li>PWM</li> </ul>	No
<ul style="list-style-type: none"> <li>Oversampling</li> </ul>	No
<ul style="list-style-type: none"> <li>MSO</li> </ul>	Yes
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, max.	20 mA; without load
Output voltage	
Rated value (DC)	24 V
Power loss	
Power loss, typ.	1 W
Address area	
Address space per module	
<ul style="list-style-type: none"> <li>Address space per module, max.</li> </ul>	4 byte; 2 channels per submodule + QI information
Hardware configuration	
Automatic encoding	Yes
<ul style="list-style-type: none"> <li>Mechanical coding element</li> </ul>	Yes
<ul style="list-style-type: none"> <li>Type of mechanical coding element</li> </ul>	Type A
Submodules	
<ul style="list-style-type: none"> <li>Number of configurable submodules, max.</li> </ul>	2
Selection of BaseUnit for connection variants	
<ul style="list-style-type: none"> <li>1-wire connection</li> </ul>	BU type A0
<ul style="list-style-type: none"> <li>2-wire connection</li> </ul>	BU type A0
<ul style="list-style-type: none"> <li>3-wire connection</li> </ul>	BU type A0 with AUX terminals or potential distributor module
Digital outputs	
Type of digital output	Source output (PNP, current-sourcing)
Number of digital outputs	4
Current-sinking	No
Current-sourcing	Yes

Digital outputs, parameterizable	Yes
output type acc. to IEC 61131, type 2	Yes
Short-circuit protection	Yes; Electronic
• Response threshold, typ.	2.8 to 5.2 A
Open-circuit detection	Yes
Limitation of inductive shutdown voltage to	Typ. L+ (-50 V)
Controlling a digital input	Yes
<b>Switching capacity of the outputs</b>	
• with resistive load, max.	2 A
• with inductive load, max.	2 A
• on lamp load, max.	10 W
<b>Load resistance range</b>	
• lower limit	12 Ω
• upper limit	3 400 Ω
<b>Output current</b>	
• for signal "1" rated value	2 A
• for signal "1" permissible range, max.	2 A
• for signal "0" residual current, max.	0.1 mA
<b>Output delay with resistive load</b>	
• "0" to "1", typ.	50 μs
• "1" to "0", typ.	100 μs
<b>Parallel switching of two outputs</b>	
• for uprating	No
• for redundant control of a load	Yes
<b>Switching frequency</b>	
• with resistive load, max.	100 Hz
• with inductive load, max.	0.1 Hz; higher frequencies are possible, see Equipment Manual "Maximum permitted switching frequency of inductive loads"
• on lamp load, max.	10 Hz
<b>Total current of the outputs</b>	
• Current per channel, max.	2 A
• Current per module, max.	8 A; see Equipment Manual "Derating curve"
<b>Total current of the outputs (per module)</b>	
horizontal installation	
— up to 30 °C, max.	8 A
— up to 40 °C, max.	8 A
— up to 50 °C, max.	6 A
— up to 60 °C, max.	4 A
— up to 70 °C, max.	2 A
vertical installation	
— up to 30 °C, max.	8 A
— up to 40 °C, max.	6 A
— up to 50 °C, max.	4 A
<b>Cable length</b>	
• shielded, max.	1 000 m
• unshielded, max.	600 m
<b>Isochronous mode</b>	
Execution and activation time (TCO), min.	75 μs
Bus cycle time (TDP), min.	500 μs
Jitter, max.	8 μs
<b>Interrupts/diagnostics/status information</b>	
Diagnostics function	Yes
Substitute values connectable	Yes
<b>Alarms</b>	
• Diagnostic alarm	Yes
<b>Diagnoses</b>	
• Monitoring the supply voltage	Yes
— parameterizable	Yes
• Wire-break	Yes; channel by channel

<ul style="list-style-type: none"> <li>• Short-circuit to M</li> </ul>	Yes; channel by channel
<ul style="list-style-type: none"> <li>• Short-circuit to L+</li> </ul>	Yes; channel by channel
<ul style="list-style-type: none"> <li>• Group error</li> </ul>	Yes
<b>Diagnostics indication LED</b>	
<ul style="list-style-type: none"> <li>• Monitoring of the supply voltage (PWR-LED)</li> </ul>	Yes; green PWR LED
<ul style="list-style-type: none"> <li>• Channel status display</li> </ul>	Yes; green LED
<ul style="list-style-type: none"> <li>• for channel diagnostics</li> </ul>	Yes; red LED
<ul style="list-style-type: none"> <li>• for module diagnostics</li> </ul>	Yes; green/red DIAG LED
<b>Potential separation</b>	
<b>Potential separation channels</b>	
<ul style="list-style-type: none"> <li>• between the channels</li> </ul>	No
<ul style="list-style-type: none"> <li>• between the channels and backplane bus</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Between the channels and load voltage L+</li> </ul>	No
<b>Isolation</b>	
Isolation tested with	707 V DC (type test)
<b>Standards, approvals, certificates</b>	
Suitable for safety functions	No
Suitable for safety-related tripping of standard modules	Yes; see FAQ Entry ID: 39198632
<b>Highest safety class achievable for safety-related tripping of standard modules</b>	
<ul style="list-style-type: none"> <li>• Performance level according to ISO 13849-1</li> </ul>	PL d
<ul style="list-style-type: none"> <li>• Category according to ISO 13849-1</li> </ul>	Cat. 3
<ul style="list-style-type: none"> <li>• SIL acc. to IEC 62061</li> </ul>	SIL 2
<ul style="list-style-type: none"> <li>• remark on safety-oriented shutdown</li> </ul>	<a href="https://support.industry.siemens.com/cs/de/en/view/39198632">https://support.industry.siemens.com/cs/de/en/view/39198632</a>
<b>Ambient conditions</b>	
<b>Ambient temperature during operation</b>	
<ul style="list-style-type: none"> <li>• horizontal installation, min.</li> </ul>	-40 °C; = Tmin (incl. condensation/frost)
<ul style="list-style-type: none"> <li>• horizontal installation, max.</li> </ul>	70 °C; = Tmax; > +60 °C max. total current 2 A
<ul style="list-style-type: none"> <li>• vertical installation, min.</li> </ul>	-40 °C; = Tmin
<ul style="list-style-type: none"> <li>• vertical installation, max.</li> </ul>	50 °C; = Tmax
<b>Altitude during operation relating to sea level</b>	
<ul style="list-style-type: none"> <li>• Installation altitude above sea level, max.</li> </ul>	5 000 m; restrictions for installation altitudes > 2 000 m, see ET 200SP system manual
<b>Relative humidity</b>	
<ul style="list-style-type: none"> <li>• With condensation, tested in accordance with IEC 60068-2-38, max.</li> </ul>	100 %; RH incl. condensation / frost (no commissioning in bedewed state), horizontal installation
<b>Resistance</b>	
<b>Coolants and lubricants</b>	
— Resistant to commercially available coolants and lubricants	Yes; Incl. diesel and oil droplets in the air
<b>Use in stationary industrial systems</b>	
— to biologically active substances according to EN 60721-3-3	Yes; Class 3B2 mold, fungus and dry rot spores (with the exception of fauna); Class 3B3 on request
— to chemically active substances according to EN 60721-3-3	Yes; Class 3C4 (RH < 75%) incl. salt spray acc. to EN 60068-2-52 (severity degree 3)
— to mechanically active substances according to EN 60721-3-3	Yes; Class 3S4 incl. sand, dust
— Against mechanical environmental conditions acc. to EN 60721-3-3	Yes; Class 3M8 using the SIPLUS Mounting Kit ET 200SP (6AG1193-6AA00-0AA0/6AG1193-6AB00-0AA0)
<b>Use on ships/at sea</b>	
— to biologically active substances according to EN 60721-3-6	Yes; Class 6B2 mold, fungal and dry rot spores (excluding fauna)
— to chemically active substances according to EN 60721-3-6	Yes; Class 6C3 (RH < 75%) incl. salt spray acc. to EN 60068-2-52 (severity degree 3).
— to mechanically active substances according to EN 60721-3-6	Yes; Class 6S3 incl. sand, dust
— Against mechanical environmental conditions acc. to EN 60721-3-6	Yes; class 6M4 using the SIPLUS Mounting Kit ET 200SP (6AG1193-6AA00-0AA0/6AG1193-6AB00-0AA0)
<b>Usage in industrial process technology</b>	
— Against chemically active substances acc. to EN 60654-4	Yes; Class 3 (excluding trichlorethylene)
— Environmental conditions for process, measuring and control systems acc. to ANSI/ISA-71.04	Yes; Level GX group A/B (excluding trichlorethylene; harmful gas concentrations up to the limits of EN 60721-3-3 class 3C4 permissible); level LC3 (salt spray) and level LB3 (oil)

**Conformal coating**

- Coatings for printed circuit board assemblies acc. to EN 61086
- Protection against fouling acc. to EN 60664-3
- Military testing according to MIL-I-46058C, Amendment 7
- Qualification and Performance of Electrical Insulating Compound for Printed Board Assemblies according to IPC-CC-830A

Yes; Class 2 for high reliability  
 Yes; Type 1 protection  
 Yes; Discoloration of coating possible during service life  
 Yes; Conformal coating, Class A

**Dimensions**

Width	15 mm
Height	73 mm
Depth	58 mm

**Weights**

Weight, approx.	30 g
-----------------	------

**Classifications**

	Version	Classification
eClass	14	27-24-26-04
eClass	12	27-24-26-04
eClass	9.1	27-24-26-04
eClass	9	27-24-26-04
eClass	8	27-24-26-04
eClass	7.1	27-24-26-04
eClass	6	27-24-26-04
ETIM	10	EC001599
ETIM	9	EC001599
ETIM	8	EC001599
ETIM	7	EC001599

**Approvals / Certificates**

General Product Approval	EMV
--------------------------	-----

[Manufacturer Declaration](#)



[China RoHS](#)



**For use in hazardous locations**



last modified:

10/23/2025