SAFETY DATA SHEET

according to Commission Regulation (EU) 2020/878 as amended

RS PRO Multipurpose liquid

Creation date	25th June 2020		
Revision date	05th March 2025	Version	3.0

SECTION 1: Identification of the substance / mixture and of the company / undertaking

1.1. Product identifier

Product Name	RS PRO Multipurpose Liquid
Product Code(s)	802720
Substance / mixture	mixture
UFI	EQP1-N0F3-600T-JD2T

1.2. Relevant identified uses of the substance or mixture and uses advised against

Mixture's intended use

Lubricating agent. Cleaning agent.

Mixture uses advised against

The product should not be used in ways other than those referred in Section 1.

1.3. Details of the supplier of the safety data sheet

Supplier

RS Components Ltd
Birchington Road
Corby
Northants
NN17 9RS
Tel: +44 (0) 845 850 9900
RCustomerServicesUK@rs-components.com

RS Components Ltd
Glenview Industrial Estate
Herberton Road
Rialto
Dublin 12
Tel: +353 (0) 1 415 3100

Competent person responsible for the safety data sheet
Email enquiries.ie@rs-components.com

1.4. Emergency telephone number

Tel: +44 (0) 1865 407333 (24hr) +44 1235 239670 (24hr)
GB: N/A IE: +353 (0)1 809 2166 (08:00 - 22:00)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification of the mixture in accordance with Regulation (EC) No 1272/2008

The mixture is classified as dangerous.


Asp. Tox. 1, H304
STOT SE 3, H336

Most serious adverse effects on human health and the environment

May be fatal if swallowed and enters airways. May cause drowsiness or dizziness.

2.2. Label elements

Hazard pictogram



Signal word

Danger

Hazardous substances

Hydrocarbons C9-C11, N-alkanes, cyclic isoalkanes, <2% aromatics

Hazard statements

H304	May be fatal if swallowed and enters airways.
H336	May cause drowsiness or dizziness.

Precautionary statements

P101	If medical advice is needed, have product container or label at hand.
P102	Keep out of reach of children.
P301+P310	P301+P310: IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician.
P331	Do NOT induce vomiting.
P405	Store locked up.
P501	Dispose of contents/container to by handing over to the person authorized to dispose of waste or by returning to the supplier.

Supplemental information

EUH066	Repeated exposure may cause skin dryness or cracking.

Requirements for child-resistant fastenings and tactile warning of danger

Container must carry a tactile warning of danger. Container must be fitted with child-resistant fastening.

2.3. Other hazards

The mixture does not contain substances with endocrine disrupting properties in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605. Mixture does not contain any substance meet the criteria for PBT or vPvB in accordance with Annex XIII of Regulation (EC) No. 1907/2006 (REACH) as amended. Does not contain any PMT or vPvM components.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Mixture contains these hazardous substances and substances with the highest permissible concentration in the working environment

Identification numbers	Substance name	Content in % weight	Classification according to Regulation (EC) No 1272/2008	Note
EC: 919-857-5 Registration number: 01-2119463258-33	Hydrocarbons C9-C11, N-alkanes, cyclic isoalkanes, <2% aromatics	>60	Flam. Liq. 3, H226 Asp. Tox. 1, H304 STOT SE 3, H336 EUH066	

Full text of all classifications and hazard statements is given in the section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

Do not perform artificial respiration without self-protection (e.g. a mask). Take care of your own safety. If any health problems are manifested or if in doubt, inform a doctor and show him information from this safety data sheet. If unconscious, put the person in the stabilized (recovery) position on his side with his head slightly bent backwards and make sure that airways are free; never induce vomiting. If the person vomits by himself, make sure that the vomit is not inhaled. In life threatening conditions first of all provide resuscitation of the affected person and ensure medical assistance. Respiratory arrest - provide artificial respiration immediately. Cardiac arrest - provide indirect cardiac massage immediately.

If inhaled

Terminate the exposure immediately; move the affected person to fresh air. Take care of your own safety, do not let the affected person walk! Beware of the contaminated clothes. Depending on the situation, call the medical rescue service and ensure medical treatment considering the frequent need of further observation for at least 24 hours.

If on skin

Remove contaminated clothes. Wash the affected area with plenty of water, lukewarm if possible. Soap, soap solution or shampoo should be used if there is no skin injury. Provide medical treatment if skin irritation persists.

If in eyes

Rinse eyes immediately with a flow of running water, open the eyelids (also using force if needed); remove contact lenses immediately if worn by the affected person. Rinsing should continue at least for 10 minutes.

If swallowed

If the affected person vomits, make sure to prevent inhalation of the vomit (as there is a danger of lung damage after inhalation of these liquids in the airways also in infinitesimal amount). Provide medical treatment considering the frequent need of further observation for at least 24 hours. Bring an original container with the label and the

Safety Data Sheet of the given substance as appropriate.

4.2. Most important symptoms and effects, both acute and delayed

If inhaled

Cough, headache. May cause drowsiness or dizziness.

If on skin

Not expected.

If in eyes

Not expected.

If swallowed

Irritation, nausea.

4.3. Indication of any immediate medical attention and special treatment needed

Symptomatic treatment.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Alcohol-resistant foam, carbon dioxide, powder, water spray jet, water mist.

Unsuitable extinguishing media

Water - full jet.

5.2. Special hazards arising from the substance or mixture

In the event of fire, carbon monoxide, carbon dioxide and other toxic gases may arise. Inhalation of hazardous degradation (pyrolysis) products may cause serious health damage.

5.3. Advice for firefighters

Self-Contained Breathing Apparatus (SCBA) with a chemical protection suit only where personal (close) contact is likely. Use a self-contained breathing apparatus and full-body protective clothing. Do not allow run-off of contaminated fire extinguishing material to enter drains or surface and ground water.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Use personal protective equipment for work. Follow the instructions in the Sections 7 and 8. Do not inhale mist/vapours/spray.

6.2. Environmental precautions

Prevent contamination of the soil and entering surface or ground water.

6.3. Methods and material for containment and cleaning up

Spilled product should be covered with suitable (non-flammable) absorbing material (sand, diatomaceous earth, earth and other suitable absorption materials); to be contained in well closed containers and removed as per the Section 13. In the event of leakage of the substantial amount of the product, inform fire brigade and other competent bodies. After removal of the product, wash the contaminated site with plenty of water. Do not use solvents.

6.4. Reference to other sections

See the Section 7, 8 and 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Do not inhale mist/vapours/spray. Use only outdoors or in a well-ventilated area. Use personal protective equipment as per Section 8. Observe valid legal regulations on safety and health protection.

7.2. Conditions for safe storage, including any incompatibilities

Store in tightly closed containers in cold, dry and well ventilated areas designated for this purpose. Store locked up. Keep container tightly closed.

7.3. Specific end use(s)

not available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

The mixture contains no substances for which occupational exposure limits are set.

8.2. Exposure controls

Follow the usual measures intended for health protection at work and especially for good ventilation. This can be achieved only by local suction or efficient general ventilation. If exposure limits cannot be observed in this mode, suitable protection of airways must be used. Do not eat, drink and smoke during work. Wash your hands thoroughly with water and soap after work and before breaks for a meal and rest.

Eye/face protection

It is not needed.

Skin protection

Hand protection: Protective gloves resistant to the product. When choosing appropriate thickness, material and permeability of the gloves, observe recommendations of their particular manufacturer. Other protection: protective workwear. Contaminated skin should be washed thoroughly.

Glove material	Thickness	Breakthrough time	Class
Butyl rubber (IIR)	≥ 0.3 mm	>480 min	6

Respiratory protection

Mask with a filter against organic vapours in a poorly ventilated environment.

Thermal hazard

Data not available.

Environmental exposure controls

Observe usual measures for protection of the environment, see Section 6.2.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	liquid
Colour	data not available
Odour	data not available
Melting point/freezing point	data not available
Boiling point or initial boiling point and boiling range	187-219 °C
Flammability	data not available
Lower and upper explosion limit	
bottom	0.6 %
upper	7 %
Flash point	>61 °C
Auto-ignition temperature	>230 °C
Decomposition temperature	data not available
pH	data not available
Kinematic viscosity	1.77 mm^2/s at 40 °C
Solubility in water	data not available
Partition coefficient n-octanol/water (log value)	data not available
Vapour pressure	data not available
Density and/or relative density	
Density	809 g/cm^3 at 15 °C
Relative vapour density	data not available
Particle characteristics	data not available

9.2. Other information

not available

SECTION 10: Stability and reactivity

10.1. Reactivity

not available

10.2. Chemical stability

The product is stable under normal conditions.

10.3. Possibility of hazardous reactions

Unknown.

10.4. Conditions to avoid

The product is stable and no degradation occurs under normal use. Protect against flames, sparks, overheating and against frost.

10.5. Incompatible materials

Protect against strong acids, bases and oxidizing agents.

10.6. Hazardous decomposition products

Not developed under normal uses. Dangerous outcomes such as carbon monoxide and carbon dioxide are formed at high temperature and in fire.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

No toxicological data is available for the mixture.

Acute toxicity

No data are available for either the mixture or the components. Based on the available data, the criteria for classification of the mixture are not met.

Skin corrosion/irritation

No data are available for either the mixture or the components. Based on the available data, the criteria for classification of the mixture are not met.

Serious eye damage/irritation

No data are available for either the mixture or the components. Based on the available data, the criteria for classification of the mixture are not met.

Respiratory or skin sensitisation

No data are available for either the mixture or the components. Based on the available data, the criteria for classification of the mixture are not met.

Germ cell mutagenicity

No data are available for either the mixture or the components. Based on the available data, the criteria for classification of the mixture are not met.

Carcinogenicity

No data are available for either the mixture or the components. Based on the available data, the criteria for classification of the mixture are not met.

Reproductive toxicity

No data are available for either the mixture or the components. Based on the available data, the criteria for classification of the mixture are not met.

Toxicity for specific target organ - single exposure

May cause drowsiness or dizziness. Data for the components of the mixture are not available.

Toxicity for specific target organ - repeated exposure

No data are available for either the mixture or the components. Based on the available data, the criteria for classification of the mixture are not met.

Aspiration hazard

May be fatal if swallowed and enters airways. Data for the components of the mixture are not available.

11.2. Information on other hazards

Endocrine disrupting properties

Based on the available data, the criteria for classification of the mixture are not met. Does not contain any components that may cause endocrine disruption for humans.

Other information

not available

SECTION 12: Ecological information

12.1. Toxicity

No data are available for either the mixture or the components. Based on the available data, the criteria for classification of the mixture are not met.

12.2. Persistence and degradability

No data are available for either the mixture or the components.

12.3. Bioaccumulative potential

No data are available for either the mixture or the components.

12.4. Mobility in soil

Based on the available data, the criteria for classification of the mixture are not met. Does not contain any PMT or vPvM components.

12.5. Results of PBT and vPvB assessment

Based on the available data, the criteria for classification of the mixture are not met. Does not contain any PBT or vPvB components.

12.6. Endocrine disrupting properties

Based on the available data, the criteria for classification of the mixture are not met. Does not contain any components that may cause endocrine disruption in the environment.

12.7. Other adverse effects

Data not available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Hazard of environmental contamination; dispose of the waste in accordance with the local and/or national regulations. Any unused product and contaminated packaging should be put in labelled containers for waste collection and submitted for disposal to a person authorised for waste removal (a specialized company) that is entitled for such activity. Do not empty unused product in drainage systems. The product must not be disposed of with municipal waste. Empty containers may be used at waste incinerators to produce energy or deposited in a dump with appropriate classification. Perfectly cleaned containers can be submitted for recycling.

Waste management legislation

Directive 2008/98/EC of the European Parliament and of the Council of 19 November 2008 on waste, as amended. Decision 2000/532/EC establishing a list of wastes, as amended.

SECTION 14: Transport information

14.1. UN number or ID number

not subject to transport regulations

14.2. UN proper shipping name

not relevant

14.3. Transport hazard class(es)

not relevant

14.4. Packing group

not relevant

14.5. Environmental hazards

not relevant

14.6. Special precautions for user

Reference in the Sections 4 to 8.

14.7. Maritime transport in bulk according to IMO instruments

not relevant

SAFETY DATA SHEET

according to Commission Regulation (EU) 2020/878 as amended

RS PRO Multipurpose liquid

Creation date	25th June 2020		
Revision date	05th March 2025	Version	3.0

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Regulation (EC) No. 1907/2006 of the European Parliament and of the Council of 18th December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing the European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No. 793/93 and Commission Regulation (EC) No. 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, as amended. REGULATION (EC) No. 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL as amended. Commission Regulation (EU) 2020/878 of 18 June 2020 amending Annex II to Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH).

15.2. Chemical safety assessment

not available

SECTION 16: Other information

A list of standard risk phrases used in the safety data sheet

EUH066	Repeated exposure may cause skin dryness or cracking.
H226	Flammable liquid and vapour.
H304	May be fatal if swallowed and enters airways.
H336	May cause drowsiness or dizziness.

Guidelines for safe handling used in the safety data sheet

P101	If medical advice is needed, have product container or label at hand.
P102	Keep out of reach of children.
P301+P310	IF SWALLOWED: Immediately call a doctor.
P331	Do NOT induce vomiting.
P405	Store locked up.
P501	Dispose of contents/container to by handing over to the person authorized to dispose of waste or by returning to the supplier.

Other important information about human health protection

The product must not be - unless specifically approved by the manufacturer/importer - used for purposes other than as per the Section 1. The user is responsible for adherence to all related health protection regulations.

Key to abbreviations and acronyms used in the safety data sheet

ADR	Agreement concerning the international carriage of dangerous goods by road
Asp. Tox.	Aspiration hazard
BCF	Bioconcentration Factor
CAS	Chemical Abstracts Service
CLP	Regulation (EC) No 1272/2008 on classification, labelling and packaging of substance and mixtures
EC	Identification code for each substance listed in EINECS
EINECS	European Inventory of Existing Commercial Chemical Substances
EmS	Emergency Response Procedures for Ships Carrying Dangerous Goods
EU	European Union
EuPCS	European Product Categorisation System
Flam. Liq.	Flammable liquid
IATA	International Air Transport Association
IBC	International Code For The Construction And Equipment of Ships Carrying Dangerous Chemicals
ICAO	International Civil Aviation Organization
IMDG	International Maritime Dangerous Goods
IMO	International Maritime Organization
INCI	International Nomenclature of Cosmetic Ingredients
ISO	International Organization for Standardization
IUPAC	International Union of Pure and Applied Chemistry
log Kow	Octanol-water partition coefficient
OEL	Occupational Exposure Limits
PBT	Persistent, bioaccumulative and toxic

PMT	Persistent, mobile and toxic
ppm	Parts per million
REACH	Registration, Evaluation, Authorisation and Restriction of Chemicals
RID	Regulation concerning the International Carriage of Dangerous Goods by Rail
STOT SE	Specific target organ toxicity - single exposure
UN number	Four-figure identification number of the substance or article taken from the UN Model Regulations
UVCB	Substances of unknown or variable composition, complex reaction products or biological materials
VOC	Volatile organic compounds
vPvB	Very persistent and very bioaccumulative
vPvM	Very persistent and very mobile

Training guidelines

Inform the personnel about the recommended ways of use, mandatory protective equipment, first aid and prohibited ways of handling the product.

Recommended restrictions of use

not available

Information about data sources used to compile the Safety Data Sheet

REGULATION (EC) No. 1907/2006 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL (REACH) as amended. REGULATION (EC) No. 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL as amended. Data from the manufacturer of the substance / mixture, if available - information from registration dossiers.

The changes (which information has been added, deleted or modified)

The version 3.0 replaces the SDS version from Monday, 23 January 2023. Changes were made in sections 2 and 16.

More information

Classification procedure - calculation method.

Statement

The safety data sheet provides information aimed at ensuring safety and health protection at work and environmental protection. The provided information corresponds to the current status of knowledge and experience and complies with valid legal regulations. The information should not be understood as guaranteeing the suitability and usability of the product for a particular application.