



Main

| | |
|-------------------------------|--|
| Range of product | Telemecanique Inductive proximity sensors XS |
| Series name | General purpose |
| Sensor type | Inductive proximity sensor |
| Product specific application | - |
| Sensor name | XS7 |
| Sensor design | Form 12 x 40 x 26 |
| Size | 26 mm |
| Body type | Fixed |
| Enclosure material | Plastic |
| Type of output signal | Discrete |
| Wiring technique | 3-wire |
| [Sn] nominal sensing distance | 2 Mm |
| Discrete output function | 1 NO |
| Discrete output type | PNP |
| Electrical connection | Male connector M8, 3 pins |
| [Us] rated supply voltage | 12...24 V DC |
| Switching capacity in mA | <= 100 mA with overload and short-circuit protection |
| IP degree of protection | IP67 conforming to IEC 60529 |

Complementary

| | |
|------------------------------------|------------------------------|
| Detection face | Lateral |
| Detector flush mounting acceptance | Flush mountable |
| Material | Plastic |
| Front material | Plastic |
| Operating zone | 0...1.6 Mm |
| Differential travel | 3...20% of Sr |
| Repeat accuracy | <= 10% of Sr |
| Output circuit type | DC |
| Status LED | Output state: 1 LED (yellow) |
| Supply voltage limits | 10...30 V DC |
| Switching frequency | <= 2000 Hz |
| Maximum voltage drop | <1.8 V (closed) |
| Current consumption | 0...10 mA no-load |

| | |
|------------------------|--------|
| Maximum delay response | 0.5 Ms |
| Maximum delay recovery | 1 Ms |
| Marking | CE |
| Depth | 31 Mm |
| Height | 45 Mm |
| Width | 12 Mm |

Environment

| | |
|---------------------------------------|---|
| Product certifications | CSA UL |
| Ambient air temperature for operation | -25...70 °C |
| Ambient air temperature for storage | -40...85 °C |
| Vibration resistance | 25 gn amplitude = +/- 2 mm (f = 10...55 Hz) conforming to IEC 60068-2-6 |
| Shock resistance | 50 gn for 11 ms conforming to IEC 60068-2-27 |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 29.0 G |
| Package 1 Height | 7 Cm |
| Package 1 width | 4.4 Cm |
| Package 1 Length | 3.5 Cm |
| Unit Type of Package 2 | S01 |
| Number of Units in Package 2 | 40 |
| Package 2 Weight | 1.349 Kg |
| Package 2 Height | 15 Cm |
| Package 2 width | 15 Cm |
| Package 2 Length | 40 Cm |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Product Life Status : **Commercialised**