

# SAC-5P-100,0-800/0,34 - Cable reel



1446511

<https://www.phoenixcontact.com/gb/products/1446511>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



By the meter, Cable reel, PUR halogen-free, gray RAL 7001, 5-wire, color single wire: black, brown,blue, white, gray, cable length: 100 m, highly flexible, resistant to welding sparks

## Commercial data

Item number	1446511
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AF1LAA
Product key	AF1LAA
GTIN	4046356629508
Weight per piece (including packing)	3,596 g
Weight per piece (excluding packing)	3,450 g
Customs tariff number	85444995
Country of origin	DE

# SAC-5P-100,0-800/0,34 - Cable reel



1446511

<https://www.phoenixcontact.com/gb/products/1446511>

## Technical data


### Product properties

Product type	Cable by the meter
Application	Connector
Number of positions	5
Shielded	no

### Cable/line

Cable length	100 m
--------------	-------

Gray, highly flexible PUR [800]

Dimensional drawing	
Note	Due to the extremely robust outer sheath, this cable should only be stripped in 5 cm increments.
Cable weight	38 kg/km
UL AWM Style	20549
Number of positions	5
Shielded	no
Cable type	Gray, highly flexible PUR [800]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross section	5x 0.34 mm <sup>2</sup> (Signal line)
Wire diameter incl. insulation	1.3 mm ±0.05 mm (Signal line)
External cable diameter	5.10 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	gray RAL 7001
Conductor material	Bare Cu litz wires
Material, filler	PE
Material wire insulation	PP
Single wire, color	black, brown, blue, white, gray
Overall twist	5 wires around filler to the core
Max. conductor resistance	approx. 53 Ω/km
Insulation resistance	≥ 20 MΩ*km
Nominal voltage, cable	300 V
Test voltage	2000 V
Minimum bending radius, fixed installation	4 x D

# SAC-5P-100,0-800/0,34 - Cable reel



1446511

<https://www.phoenixcontact.com/gb/products/1446511>

Minimum bending radius, flexible installation	7.5 x D
Smallest bending radius, fixed installation	21 mm
Smallest bending radius, movable installation	39 mm
Dynamic load capacity (bending)	Max. bending cycles: 10000000, Bending radius: 7,5 x D, Traversing path: 5 m, Traversing rate: 3.3 m/s, Acceleration: 5 m/s <sup>2</sup>
	Max. bending cycles: 15000000, Bending radius: 50 mm, Traversing path: 0.9 m, Traversing rate: 5 m/s, Acceleration: 30 m/s <sup>2</sup>
Dynamic load capacity (torsion)	Torsion: ±360 °/m, Torsion cycles: 1000000
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	in accordance with UL 758/1581 FT2
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	Highly resistant to acids, alkaline solutions and solvents
	Silicone-free
Special properties	Cable jacket is welding spark-resistant, recyclable, matt, low-adhesion, abrasion-resistant, flame-retardant, and self-extinguishing
	Free from silicone and cadmium
	Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-25 °C ... 80 °C (Cable, flexible installation)

# SAC-5P-100,0-800/0,34 - Cable reel



1446511

<https://www.phoenixcontact.com/gb/products/1446511>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1446511>



### UL Listed

Approval ID: FILE E 221474

	Nominal voltage U <sub>N</sub>	Nominal current I <sub>N</sub>	Cross section AWG	Cross section mm <sup>2</sup>
	125 V	4 A	-	-



### cUL Listed

Approval ID: FILE E 221474

	Nominal voltage U <sub>N</sub>	Nominal current I <sub>N</sub>	Cross section AWG	Cross section mm <sup>2</sup>
	125 V	4 A	-	-

# SAC-5P-100,0-800/0,34 - Cable reel



1446511

<https://www.phoenixcontact.com/gb/products/1446511>

## Classifications

### ECLASS

ECLASS-13.0	27061801
-------------	----------

### ETIM

ETIM 9.0	EC003249
----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# SAC-5P-100,0-800/0,34 - Cable reel



1446511

<https://www.phoenixcontact.com/gb/products/1446511>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.0 Climate Change

CO2e kg	20.069 kg CO2e
---------	----------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)