



Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

XT112S1PCM12



Telemecanique
Sensors

Telemecanique Sensors
1875 Founders Drive
Dayton, OH 45420-4017
Customer Care Center : 1-800-435-2121
Web : www.tesensors.com

Technical Information:

Max Range Adj: 2.0 mm (0.079 in)
 Circuit Type: NO + NC
 Output Mode: PNP
 Volts Type: DC
 Voltage Range: 12-30 VDC
 Max Load : 200 mA
 Shielded: Shielded
 Operating Frequency: 300 Hz
 Temp Range: -25° to 70° C (-13° to 158° F)
 NEMA Type: 4X (indoor use only)
 Standards: UL, CE Rohs

Specification:

Sensor Type: Capacitive Sensor
 Description: Proximity Sensor, Capacitive, 12 mm Barrel, 12-30 VDC, Shielded
 Body Style: Barrel
 Diameter: mm
 Face Material: PBT Plastic
 Housing Material: SS303 Stainless Steel
 Cable Length:
 Connector Type: M12
 Special Features: NO + NC outputs