



## Rotary lever

<b>Part no.</b>	<b>LS-XRL</b>
<b>Article no.</b>	<b>266126</b>
<b>Catalog No.</b>	<b>LS-XRL</b>



Powering Business Worldwide™

### Delivery programme

Basic function		Operating heads
Part group reference		LS(M)-...
Product range		Rotary lever
Design		EN 50047 Form A
For use with		Basic devices LS(M)...
<b>Notes</b> The operating head can be rotated at 90° intervals to adapt to the specified approach direction.		

### Approvals

Product Standards	IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14; CE marking
UL File No.	E29184
UL Category Control No.	NKCR
CSA File No.	12528
CSA Class No.	3211-03
North America Certification	UL listed, CSA certified

### Technical data ETIM 5.0

Sensors (EG000026) / Drive head for position switches/hinge switches (EC001483)	
Electric engineering, automation, process control engineering / Binary sensor technology, safety-related sensor technology / Position switch / Drive head for position switches (ecl@ss8-27-27-06-04 [BAA083008])	
Type of control element	Rotary lever

### Dimensions

