

## LV431877

circuit breaker Compact NSX250N - Micrologic 2.2 -  
100 A - 4 poles 4d



### Main

Product or component type	Circuit breaker
Device short name	Compact NSX250N
Circuit breaker application	Distribution
Poles description	4P
Protected poles description	3t 3t + N/2 4t
Neutral position	Left
Network type	AC
Network frequency	50/60 Hz
[In] rated current	250 A ( 40 °C )
[Ui] rated insulation voltage	800 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ue] rated operational voltage	690 V AC 50/60 Hz
Breaking capacity code	N
Breaking capacity	15 kA at 600 V AC 50/60 Hz conforming to UL 508 20 kA at 600 V AC 50/60 Hz conforming to NEMA AB1 50 kA at 480 V AC 50/60 Hz conforming to NEMA AB1 50 kA at 480 V AC 50/60 Hz conforming to UL 508 85 kA at 240 V AC 50/60 Hz conforming to UL 508 90 kA at 240 V AC 50/60 Hz conforming to NEMA AB1 Icu 10 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 Icu 35 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2 Icu 36 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 Icu 50 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 Icu 50 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 Icu 90 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] rated service breaking capacity	Ics 10 kA 660/690 V AC 50/60 Hz conforming to IEC 60947-2 Ics 35 kA 525 V AC 50/60 Hz conforming to IEC 60947-2 Ics 36 kA 500 V AC 50/60 Hz conforming to IEC 60947-2 Ics 50 kA 380/415 V AC 50/60 Hz conforming to IEC 60947-2 Ics 50 kA 440 V AC 50/60 Hz conforming to IEC 60947-2 Ics 90 kA 220/240 V AC 50/60 Hz conforming to IEC 60947-2
Suitability for isolation	Yes conforming to EN 60947-2 Yes conforming to IEC 60947-2
Utilisation category	Category A
Trip unit name	Micrologic 2.2
Trip unit technology	Electronic
Trip unit protection functions	LSol
Trip unit rating	100 A ( 40 °C )
Protection type	Instantaneous short-circuit protection

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Overload protection (long time)  
Short time short-circuit protection

Pollution degree 3 conforming to IEC 60664-1

## Complementary

Control type	Toggle
Mounting mode	Fixed
Mounting support	Backplate
Upside connection	Front
Downside connection	Front
Mechanical durability	20000 cycles
Electrical durability	10000 cycles 440 V In conforming to IEC 60947-2 10000 cycles 690 V In/2 conforming to IEC 60947-2 20000 cycles 440 V In/2 conforming to IEC 60947-2 5000 cycles 690 V In conforming to IEC 60947-2
Connection pitch	35 mm
Local signalling	LED 105 % Ir LED 90 % Ir LED ready
Neutral protection setting	0.5 x Ir 3t + N/2 1 x Ir 4t No protection 3t
Long time pick-up adjustment type Ir	Adjustable 9 settings
Long time pick-up adjustment range	0.9...1 x Io
Long time delay adjustment type	Fixed
[tr] long-time delay adjustment	11 s 7.2 x Ir 16 s 6 x Ir 400 s 1.5 x Ir
Thermal memory	20 minutes before and after tripping
Short-time pick-up adjustment type I <sub>sd</sub>	Adjustable 9 settings
[I <sub>sd</sub> ] short-time pick-up adjustment range	1.5...10 x Ir
Short-time delay adjustment type	Fixed
Instantaneous pick-up adjustment type I <sub>i</sub>	Fixed
Instantaneous pick-up adjustment range	1500 A
Height	161 mm
Width	140 mm
Depth	86 mm
Product weight	2.8 kg

## Environment

Electrical shock protection class	Class II
Standards	EN 60947-2 IEC 60947-2 NEMA AB1 UL 508
Product certifications	CSA UL
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-55...85 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0819 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

