

# CA-16S1N8A8007 - Cable connector



1619704

<https://www.phoenixcontact.com/gb/products/1619704>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: CA, straight, shielded: yes, Screw locking mechanism, No. of pos. : 16, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, cable diameter range: 6 mm ... 10 mm, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1243756

## Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Crimping connection: vibration- and temperature-resistant assembly

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1619704       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | ABRAEA        |
| Product key                          | ABRAEA        |
| GTIN                                 | 4046356822114 |
| Weight per piece (including packing) | 92.533 g      |
| Weight per piece (excluding packing) | 83.3 g        |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# CA-16S1N8A8007 - Cable connector



1619704

<https://www.phoenixcontact.com/gb/products/1619704>

## Technical data

### Notes

|                    |                                            |
|--------------------|--------------------------------------------|
| Order information: | Order 6 x Ø 1 mm crimp contacts separately |
|--------------------|--------------------------------------------|

### Product properties

|              |                                 |
|--------------|---------------------------------|
| Product type | Circular connector (cable-side) |
|--------------|---------------------------------|

### Data management status

|                  |    |
|------------------|----|
| Article revision | 05 |
|------------------|----|

### Connector

#### Connection 1

|             |        |
|-------------|--------|
| Head design | Socket |
|-------------|--------|

#### Insulating body

|                                              |                                                               |
|----------------------------------------------|---------------------------------------------------------------|
| Note                                         | Order information: Order 6 x Ø 1 mm crimp contacts separately |
| Coding                                       | N                                                             |
| Insulation body material                     | PA 6.6                                                        |
| Connection method                            | Crimp connection                                              |
| Contact switching type                       | Socket                                                        |
| Application                                  | Signal                                                        |
| Number of positions                          | 16                                                            |
| Direction of rotation                        | Standard                                                      |
| Connection profile                           | 16                                                            |
| Contact diameter                             | 1 mm                                                          |
| Signal contacts                              |                                                               |
| Litz wire cross-section Signal contacts min. | 0.08 mm <sup>2</sup>                                          |
| Litz wire cross-section Signal contacts max. | 1 mm <sup>2</sup>                                             |
| Nominal current per signal contact           | 8 A                                                           |
| Rated voltage Signal contact                 | 48 V AC                                                       |
| Rated surge voltage                          | 1.5 kV                                                        |
| Overvoltage category                         | III                                                           |
| Degree of pollution                          | 3                                                             |

#### Housing

|                                   |                                                                      |
|-----------------------------------|----------------------------------------------------------------------|
| Housing material                  | Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn) |
| Type of locking                   | Screw locking mechanism                                              |
| Pg screw connection               | none                                                                 |
| Degree of protection (plugged in) | IP67                                                                 |
| Thread type                       | M23                                                                  |

#### Seal

|                         |                |
|-------------------------|----------------|
| External cable diameter | 6 mm ... 10 mm |
|-------------------------|----------------|

# CA-16S1N8A8007 - Cable connector



1619704

<https://www.phoenixcontact.com/gb/products/1619704>

|               |     |
|---------------|-----|
| Seal material | NBR |
|---------------|-----|

## Environmental and real-life conditions

### Ambient conditions

|                                          |                   |
|------------------------------------------|-------------------|
| Ambient temperature (operation)          | -40 °C ... 125 °C |
| Ambient temperature (storage/transport)  | 15 °C ... 25 °C   |
| Permissible humidity (storage/transport) | 50 % ... 65 %     |

# CA-16S1N8A8007 - Cable connector



1619704

<https://www.phoenixcontact.com/gb/products/1619704>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1619704>

|                                                                                                                                          |                       |                       |                   |                             |
|------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|  <b>cUL Recognized</b><br>Approval ID: E335019-20141210 |                       |                       |                   |                             |
|                                                                                                                                          | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|                                                                                                                                          | 48 V                  | 3 A                   | 20 - 20           | -                           |

|                                                                                                                                         |                       |                       |                   |                             |
|-----------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|  <b>UL Recognized</b><br>Approval ID: E335019-20141210 |                       |                       |                   |                             |
|                                                                                                                                         | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|                                                                                                                                         | 48 V                  | 5 A                   | 20 - 20           | -                           |

|                         |  |  |  |  |
|-------------------------|--|--|--|--|
| <b>cULus Recognized</b> |  |  |  |  |
|-------------------------|--|--|--|--|

# CA-16S1N8A8007 - Cable connector



1619704

<https://www.phoenixcontact.com/gb/products/1619704>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27440102 |
| ECLASS-12.0 | 27440116 |
| ECLASS-13.0 | 27440116 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002635 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# CA-16S1N8A8007 - Cable connector



1619704

<https://www.phoenixcontact.com/gb/products/1619704>

## Environmental product compliance

### EU RoHS

|                                         |      |
|-----------------------------------------|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 7509f74b-e5eb-49e8-9ec3-bfba5dff878f |

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)