

Ultrane 551

DESCRIPTION AND GENERAL PROPERTIES

- **Material** Polyurethane foam
- **Length (cm)** 21-27
- **Thickness (mm)** Light Weight
- **Wrist** Knitted wrist
- **Colour/Color** Grey
- **Interior finish** Seamless textile support
- **Exterior finish** Ventilated back
- **Size / EAN** 6 7 8 9 10 11
- **Packaging** 10 pairs/bag - 100 pairs/carton
- **Complementary information** Contains traces of DMF in compliance with occupational exposure limits



PERFORMANCE RESULTS

Certification category 2



4131

Legends



MECHANICAL HAZARDS EN 388

PERFORMANCE LEVELS

0-4 0-5 0-4 0-4
 └─ Abrasion resistance
 └─ Blade cut resistance
 └─ Tear resistance
 └─ Puncture resistance



HEAT AND FIRE EN 407

PERFORMANCE LEVELS

0-4 0-4 0-4 0-4 0-4 0-4
 └─ Burning behaviour
 └─ Contact heat resistance
 └─ Convective heat resistance
 └─ Radiant heat resistant
 └─ Resistance to small drops of molten metal
 └─ Resistance to large quantities of molten metal



LOW CHEMICAL PROTECTION EN 374



MICRO-ORGANISMS EN 374



SPECIFIC CHEMICAL PROTECTION EN 374

Letter Code	Chemical product
A	Methanol
B	Acetone
C	Acetonitrile
D	Dichloromethane
E	Carbon Disulfide
F	Toluene
G	Diethylamine
H	Tetrahydrofuran
I	Ethyl acetate
J	n-Heptane
K	Sodium hydroxide 40%
L	Sulphuric acid 96%



RADIOACTIVE CONTAMINATION EN 421



COLD HAZARDS EN 511

PERFORMANCE LEVELS

0-4 0-4 0 or 1
 └─ Convective cold resistance
 └─ Contact cold resistance
 └─ Water permeability

For more details: www.mapa-pro.com

DESCRIPTION AND GENERAL PROPERTIES

- Excellent abrasion resistance: longer lasting
- Excellent tactile sensitivity, due to reduced glove thickness
- Absorption of perspiration ensured by the cellular structure of the polyurethane
- Added comfort, due to the seamless knit lining
- OEKO-TEX®

MAIN FIELDS OF USE

Automotive/mechanical industry

- Intricate assembly
- Sorting small parts
- Fitting small screws and fasteners

Electronics

- Electronic component assembly (displays, LEDs, etc.)
- High-frequency antennae riveting
- Microprocessor handling

Food industry

- Packaging

Cosmetics and Pharmaceutical industry

- Cosmetics preparation
- Medicine manufacturing

Construction Industry (Metalworkers/Locksmiths)

- Installing and repairing locks

Construction Industry (Heating engineers/Plumbers)

- Maintaining pipes, heating equipment

Construction Industry (Carpenters/Joiners)

- Laying wood, panelling or moulding

INSTRUCTIONS FOR USE

Instructions for use

- It is recommended to check that the gloves are suitable for the intended use, because the conditions of use in the workplace may differ from the tests performed in the laboratory.
- Put the gloves on dry, clean hands.

Storage conditions

Store the gloves in their original packaging protected from heat, light and humidity.

Laundering conditions

Caution : using the gloves or submitting them to a cleaning or laundering process that is not specifically recommended can alter their performance levels.

Drying conditions

- Ensure the inside of the gloves is dry before putting them on again.

LEGISLATION

This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council. This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).

- CE-Type Examination Certificate

0075/014/162/12/99/0145 ext 02/02/01

- Issued by the notified body nr

0075

C.T.C - F-69367 LYON CEDEX 07