

## FEATURES

- **Graphite material:** Offers superior thermal conductivity and chemical resistance
- **Maximum operating pressure of 20000 kPa:** Suitable for high-pressure applications
- **Maximum operating temperature of 650 °C:** Performs well in high-temperature environments
- **Rotary speed of 30 m/s:** Supports efficient operation in dynamic applications
- **5mm section:** Provides a compact and effective sealing solution

## RS PRO 8m Graphite Gland Packing, 5mm Section

RS Stock No: 606-570



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO gland packing is designed for sealing applications in industrial environments. Made from high-quality graphite, it provides excellent sealing performance under high pressure and temperature conditions. Ideal for use in pumps and valves, it ensures reliable operation and longevity.

## General Specifications

Maximum Operating Pressure	20000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	30 m/s
Section	5 mm
Sub Type	Gland Packing

## Mechanical Specifications

Length	8 m
Material	Graphite

## Operation Environment Specifications

Maximum Operating Temperature	650 °C
-------------------------------	--------

## Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------