

2350943-1 ✓ ACTIVE

enetSEAL+


TE Internal #: 2350943-1

Automotive Seals & Cavity Plugs, Panel Mount Flange, VMQ, Yellow, Cable-to-Panel, Sealable, Wire & Cable, Panel Mount

[View on TE.com >](#)



Connectors > Automotive Connectors > Seals & Cavity Plugs



Connector Seal Type: **Panel Mount Flange**

Seal Material: **VMQ**

Operating Temperature (Max): **125 °C [ 257 °F ]**

Primary Product Color: **Yellow**

Connector System: **Cable-to-Panel**

## Features

### Product Type Features

Connector Seal Type	Panel Mount Flange
Connector System	Cable-to-Panel
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

### Body Features

Seal Material	VMQ
Primary Product Color	Yellow

### Mechanical Attachment

Connector Mounting Type	Panel Mount
-------------------------	-------------

### Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-40 – 125 °C, -40 – 125 °C[-40 – 257 °F][-40 – 257 °F]

## Product Compliance



[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

 <p>TE Part # 2-2350891-1 20POS, HYBRID, PIN HSG ASSY, SLD, COD A</p>	 <p>TE Part # 1-2350891-1 20POS, HYBRID, PIN HSG ASSY, SLD, COD A</p>	 <p>TE Part # 1-2350891-2 20POS, HYBRID, PIN HSG ASSY, SLD, COD B</p>	 <p>TE Part # 1-2350891-3 20POS, HYBRID, PIN HSG, SLD, COD C</p>
--	--	--	---



## Customers Also Bought



## Documents

### Product Drawings

#### FIX RING, CONN KIT

English

### CAD Files

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2350943-1\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2350943-1\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2350943-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

2350943-1

Automotive Seals & Cavity Plugs, Panel Mount Flange, VMQ, Yellow, Cable-to-Panel,  
Sealable, Wire & Cable, Panel Mount



[Product Specifications](#)

[Application Specification](#)

English