





FAG

6416-M [🔗](#)

Deep groove ball bearing

Deep groove ball bearing 64...-M, single row,
solid brass cage

Technical information



Your current product variant

Sealing	Without	Not sealed
Cage	M	Solid brass cage, rolling element guided
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Lubricant	Without	Bearing not greased
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	80 mm	Bore diameter
D	200 mm	Outside diameter
B	48 mm	Width
C _r	173,000 N	Basic dynamic load rating, radial
C _{0r}	125,000 N	Basic static load rating, radial
C _{ur}	7,100 N	Fatigue load limit, radial
n _G	5,900 1/min	Limiting speed
n _{gr}	5,400 1/min	Reference speed
≈m	8.29 kg	Weight



Mounting dimensions

$d_{a\min}$	96 mm	Minimum diameter shaft shoulder
$D_{a\max}$	184 mm	Maximum diameter of housing shoulder
$r_{a\max}$	2.5 mm	Maximum fillet radius

Dimensions

$r_{\min}$	3 mm	Minimum chamfer dimension
D_1	162.14 mm	Shoulder diameter outer ring
d_1	117.94 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	150 °C	Operating temperature max.

Calculation factors

f_0	12.3	Calculation factor
-------	------	--------------------

Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed