

gear box straight teeth GBX - Ø 60 mm - reduction 10:1 <10 arc.min - 15 N.m

GBX060010K

EAN Code: 3606485317489

Main

Range compatibility	Lexium 62					
	Lexium 28					
	Lexium 62 ILM					
	Lexium 52					
	Lexium 32					
Gear box type	Straight teeth					
Product or component type	Planetary gearbox					
Device short name	GBX					
Product compatibility	BMH (70 mm, 1 motor stacks)					
	BSH (55 mm, 1 motor stacks)					
	BSH (55 mm, 3 motor stacks)					
	BSH (70 mm, 1 motor stacks)					
	BCH2 (60 mm, 1 motor stacks)					
	SH3					
	MH3					
	ILM					
Gearbox external diameter	60 mm					
Reduction ratio	10:1					

Complementary

Maximum torsional backlash	10 arc.min					
Torsional rigidity	2.3 N.m/arcmin					
Housing colour	Black					
Housing material	Black anodized aluminium					
Shaft material	C 45					
Additional information	Lubricated for life					
Service life in hours	30000 h at 100 rpm at 30 °C					
Mounting position	Any position					
Efficiency	98.0 %					
Maximum radial force Fr	340 N at 100 rpm, force applied at mid-distance from output shaft during 30000 hour at 30 $^{\circ}\text{C}$					
Maximum axial force Fa	450 N at 100 rpm, during 30000 hour at 30°C					
moment of inertia	0.064 kg.cm²					
Continuous output torque	15 N.m at 100 rpm at 30 °C					
Maximum output torque	24 N.m at 100 rpm at 30 °C					
Net weight	0.9 kg					
Input diameter	14.0 mm					

1 Jul 2025

No load running torque	0.05 N.m	
Reduction ratio	10	
Compatibility code	GBX	
Internal length	39.0 mm	

Environment

Noise level	58 dB at 1 m, no-load				
IP degree of protection	Shaft output: IP54				
ambient temperature for operation	-2590 °C				

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.5 cm
Package 1 Width	7.0 cm
Package 1 Length	7.0 cm
Package 1 Weight	832.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	5
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.615 kg

Logistical informations

Country of origin DE

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1163
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	7c9e597c-8ccc-4daf-95fb-5d67fc70d561
REACh Regulation	REACh Declaration
PVC free	Yes


Use Again

○ Repack and remanufacture						
Circularity Profile	No need of specific recycling operations					
Take-back	No					

GBX060010K

Dimensions Drawings

Dimensions with Servo Motor Adaptation Kit



- (1) GBK adaptation kit
- (2) GBK adaptation kit related dimensions a1, c, Ø6, Ø7, Ø8 depend on the gearbox and servo motor combination
- Ø8 shaft end adaptor in case motor shaft diameter is smaller than gearbox input coupling diameter

Values in mm

							Ø2			Ø5
55	35	30	2.5	16	5	60	40 h7	14 h7	M5 x 8	52

Values in in.

a2	а3	a4	a5	h	g	Ø1	Ø2	Ø3	Ø4	Ø5
2.16	1.38	1.18	0.10	063	0.19	2.36	1.57 h7	0.55 h7	M5 x 0.31	2.05